



LTR	DATE	REVISION	CHK	APD
A	04/19/11	502069ERA-RELEASED	OPL	



- NOTES:
1. DURING FINAL ASSEMBLY, HEX NUTS ARE INITIALLY PROVIDED FINGER TIGHTENED ONLY
 2. MATERIAL:
COVER - COVER: TPV 251-80W232
BASE: AMODEL 6133 V0, BLACK
STUDS & NUTS - M8 X 1.25 STEEL, ZINC PLATED WITH TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH (MEETS 96 HR, ASTM STD. B-117 SALT SPRAY REQ.)
 3. NO FUSE RATING INCLUDED
 4. TEMPERATURE RATING: -40°C TO 125°C

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS () ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATERIAL SPEC		
1	9	18		
2	10	19	FINISH	
3	12	20		
4	13	21	DRW	OPL
5	14	23	DATE	04/09/11
6	15	33	CHK	DATE
7	16	43	APPD	DATE
8	17	53	FINSH	GOOD WT
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MK)				
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	±0.1	±0.1	±0.2	±0.3
3RD ANGLE PROJECTION				
TITLE	3 POLE FLEX-MEGA FUSE HOLDER			
LITTELFUSE	REVISION	DRWG. NO.	OUTLINE	
	A	OL-029B3002ZXFC		

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED