

# HiPerFET™ Power MOSFETs

**IXFK 90 N 20**  
**IXFN 100 N 20**  
**IXFN 106 N 20**


$V_{DSS}$	$I_{D25}$	$R_{DS(on)}$
200 V	90 A	23 mΩ
200 V	100 A	23 mΩ
200 V	106 A	20 mΩ

N-Channel Enhancement Mode  
Avalanche Rated, High dv/dt, Low  $t_{rr}$


$t_{rr} \leq 200$  ns

Symbol	Test Conditions	Maximum Ratings		
		IXFK	IXFN	IXFN
$V_{DSS}$	$T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$	90N20 200	100N20 200	106N20 200 V
$V_{DGR}$	$T_J = 25^\circ\text{C}$ to $150^\circ\text{C}$ ; $R_{GS} = 1$ MΩ	200	200	200 V
$V_{GS}$	Continuous	±20	±20	20 V
$V_{GSM}$	Transient	±30	±30	20 V
$I_{D25}$	$T_C = 25^\circ\text{C}$ , Chip capability	90 ①	100	106 A
$I_{D80}$	$T_C = 80^\circ\text{C}$ , limited by external leads	76	-	A
$I_{DM}$	$T_C = 25^\circ\text{C}$ , pulse width limited by $T_{JM}$	360	400	424 A
$I_{AR}$	$T_C = 25^\circ\text{C}$	50	50	A
$E_{AR}$	$T_C = 25^\circ\text{C}$	30	30	30 mJ
dv/dt	$I_S \leq I_{DM}$ , $di/dt \leq 100$ A/μs, $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ\text{C}$ , $R_G = 2$ Ω	5	5	5 V/ns
$P_D$	$T_C = 25^\circ\text{C}$	500	520	W
$T_J$		-55 ... +150 °C		
$T_{JM}$		150 °C		
$T_{stg}$		-55 ... +150 °C		
$T_L$	1.6 mm (0.063 in) from case for 10 s	300	-	°C
$V_{ISOL}$	50/60 Hz, RMS $t = 1$ min $I_{ISOL} \leq 1$ mA $t = 1$ s	-	2500	V~
		-	3000	V~
$M_d$	Mounting torque	0.9/6	1.5/13	Nm/lb.in.
	Terminal connection torque	-	1.5/13	Nm/lb.in.
Weight		10	30	g

TO-264 AA



miniBLOC, SOT-227 B (IXFN)  
E153432



G = Gate  
S = Source

D = Drain  
TAB = Drain

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

### Features

- International standard packages
- JEDEC TO-264 AA, epoxy meet UL94 V-0, flammability classification
- miniBLOC with Aluminium nitride isolation
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
- Fast intrinsic Rectifier

### Applications

- DC-DC converters
- Synchronous rectification
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls
- Low voltage relays

### Advantages

- Easy to mount
- Space savings
- High power density

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ , unless otherwise specified)		
		min.	typ.	max.
$V_{DSS}$	$V_{GS} = 0$ V, $I_D = 1$ mA	200		V
$V_{GH(th)}$	$V_{DS} = V_{GS}$ , $I_D = 8$ mA	2		V
$I_{GSS}$	$V_{GS} = \pm 20$ V <sub>DC</sub> , $V_{DS} = 0$			±200 nA
$I_{DSS}$	$V_{DS} = 0.8 \cdot V_{DSS}$ , $T_J = 25^\circ\text{C}$ $V_{GS} = 0$ V, $T_J = 125^\circ\text{C}$			400 μA 2 mA
$R_{DS(on)}$	$V_{GS} = 10$ V, $I_D = 0.5 \cdot I_{D25}$ Pulse test, $t \leq 300$ μs, duty cycle $d \leq 2$ %			IXFK90N20 0.023 Ω IXFN100N20 0.023 Ω IXFN106N20 0.020 Ω


IXYS reserves the right to change limits, test conditions, and dimensions.

92804H (7/97)

Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ , unless otherwise specified)		
		min.	typ.	max.
$g_{fs}$	$V_{DS} = 10\text{ V}; I_D = 0.5 \cdot I_{D25}$ , pulse test		60	S
$C_{iss}$	$V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$		9000	pF
$C_{oss}$			1600	pF
$C_{rss}$			590	pF
$t_{d(on)}$	$V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$ $R_G = 1\ \Omega$ (External),		30	ns
$t_r$			80	ns
$t_{d(off)}$			75	ns
$t_f$			30	ns
$Q_{g(on)}$	$V_{GS} = 10\text{ V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$		380	nC
$Q_{gs}$			70	nC
$Q_{gd}$			190	nC
$R_{thJC}$	TO-264 AA		0.25	K/W
$R_{thCK}$	TO-264 AA		0.15	K/W
$R_{thJC}$	miniBLOC, SOT-227 B		0.24	K/W
$R_{thCK}$	miniBLOC, SOT-227 B		0.05	K/W


Symbol	Test Conditions	Characteristic Values ( $T_J = 25^\circ\text{C}$ , unless otherwise specified)		
		min.	typ.	max.
$I_S$	$V_{GS} = 0\text{ V}$			90 A IXFK90N20 IXFN100N20 IXFN106N20
$I_{SM}$	Repetitive; pulse width limited by $T_{JM}$			360 A IXFK90N20 IXFN100N20 424 A IXFN106N20
$V_{SD}$	$I_F = 100\text{ A}, V_{GS} = 0\text{ V}$ , Pulse test, $t \leq 300\ \mu\text{s}$ , duty cycle $d \leq 2\%$			1.5 V
$t_{rr}$	$I_F = 50\text{ A}, -di/dt = 100\text{ A}/\mu\text{s}, V_R = 100\text{ V}$			200 ns
$Q_{RM}$			3	$\mu\text{C}$
$I_{RM}$			38	A

### TO-264 AA Outline



Dim.	Millimeter		Inches	
	Min.	Max.	Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46	BSC	.215	BSC
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072


### miniBLOC, SOT-227 B




M4 screws (4x) supplied

Dim.	Millimeter		Inches	
	Min.	Max.	Min.	Max.
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	38.00	38.23	1.496	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.76	0.84	0.030	0.033
M	12.60	12.85	0.496	0.506
N	25.15	25.42	0.990	1.001
O	1.98	2.13	0.078	0.084
P	4.95	5.97	0.195	0.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.174
S	4.72	4.85	0.186	0.191
T	24.59	25.07	0.968	0.987
U	-0.05	0.1	-0.002	0.004


**Fig. 1 Output Characteristics**




**Fig. 2 Input Admittance**




**Fig. 3  $R_{DS(on)}$  vs. Drain Current**



**Fig. 4 Temperature Dependence of Drain to Source Resistance**



**Fig. 5 Drain Current vs. Case Temperature**



**Fig. 6 Temperature Dependence of Breakdown and Threshold Voltage**




Fig.7 Gate Charge Characteristic Curve




Fig.8 Capacitance Curves




Fig.9 Source Current vs. Source to Drain Voltage





Fig.10 Transient Thermal Impedance





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).