


### 1200V XPT™ IGBT GenX3™

### IXYK120N120B3 IXYX120N120B3

High-Speed IGBT  
for 10-30 kHz Switching




$$\begin{aligned} V_{CES} &= 1200V \\ I_{C110} &= 120A \\ V_{CE(sat)} &\leq 2.2V \\ t_{fi(typ)} &= 260ns \end{aligned}$$


| Symbol                        | Test Conditions                                                                           | Maximum Ratings                         |                  |
|-------------------------------|-------------------------------------------------------------------------------------------|-----------------------------------------|------------------|
| $V_{CES}$                     | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$                                           | 1200                                    | V                |
| $V_{CGR}$                     | $T_J = 25^\circ\text{C}$ to $175^\circ\text{C}$ , $R_{GE} = 1M\Omega$                     | 1200                                    | V                |
| $V_{GES}$                     | Continuous                                                                                | $\pm 20$                                | V                |
| $V_{GEM}$                     | Transient                                                                                 | $\pm 30$                                | V                |
| $I_{C25}$                     | $T_C = 25^\circ\text{C}$ (Chip Capability)                                                | 320                                     | A                |
| $I_{LRMS}$                    | Terminal Current Limit                                                                    | 160                                     | A                |
| $I_{C110}$                    | $T_C = 110^\circ\text{C}$                                                                 | 120                                     | A                |
| $I_{CM}$                      | $T_C = 25^\circ\text{C}$ , 1ms                                                            | 800                                     | A                |
| $I_A$                         | $T_C = 25^\circ\text{C}$                                                                  | 60                                      | A                |
| $E_{AS}$                      | $T_C = 25^\circ\text{C}$                                                                  | 2                                       | J                |
| <b>SSOA</b><br><b>(RBSOA)</b> | $V_{GE} = 15V$ , $T_{VJ} = 150^\circ\text{C}$ , $R_G = 1\Omega$<br>Clamped Inductive Load | $I_{CM} = 240$<br>$V_{CE} \leq V_{CES}$ | A                |
| $P_C$                         | $T_C = 25^\circ\text{C}$                                                                  | 1500                                    | W                |
| $T_J$                         |                                                                                           | -55 ... +175                            | $^\circ\text{C}$ |
| $T_{JM}$                      |                                                                                           | 175                                     | $^\circ\text{C}$ |
| $T_{stg}$                     |                                                                                           | -55 ... +175                            | $^\circ\text{C}$ |
| $T_L$                         | Maximum Lead Temperature for Soldering                                                    | 300                                     | $^\circ\text{C}$ |
| $T_{SOLD}$                    | 1.6 mm (0.062in.) from Case for 10s                                                       | 260                                     | $^\circ\text{C}$ |
| $M_d$                         | Mounting Torque (TO-264)                                                                  | 1.13/10                                 | Nm/lb.in         |
| $F_C$                         | Mounting Force (PLUS247)                                                                  | 20..120 / 4.5..27                       | N/lb             |
| <b>Weight</b>                 | TO-264P                                                                                   | 10                                      | g                |
|                               | PLUS247                                                                                   | 6                                       | g                |

| Symbol        | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified) | Characteristic Values |            |                            |
|---------------|-----------------------------------------------------------------------------|-----------------------|------------|----------------------------|
|               |                                                                             | Min.                  | Typ.       | Max.                       |
| $BV_{CES}$    | $I_C = 250\mu\text{A}$ , $V_{GE} = 0V$                                      | 1200                  |            | V                          |
| $V_{GE(th)}$  | $I_C = 1\text{mA}$ , $V_{CE} = V_{GE}$                                      | 3.0                   |            | 5.0 V                      |
| $I_{CES}$     | $V_{CE} = V_{CES}$ , $V_{GE} = 0V$<br>$T_J = 150^\circ\text{C}$             |                       |            | 25 $\mu\text{A}$<br>1.5 mA |
| $I_{GES}$     | $V_{CE} = 0V$ , $V_{GE} = \pm 20V$                                          |                       |            | $\pm 200$ nA               |
| $V_{CE(sat)}$ | $I_C = 100A$ , $V_{GE} = 15V$ , Note 1<br>$T_J = 150^\circ\text{C}$         |                       | 1.8<br>2.4 | 2.2 V<br>V                 |

TO-264P (IXYK)



PLUS247 (IXYX)



G = Gate                      E = Emitter  
C = Collector                Tab = Collector

#### Features

- Square RBSOA
- International Standard Packages
- Positive Thermal Coefficient of  $V_{ce(sat)}$
- Avalanche Rated
- High Current Handling Capability

#### Advantages

- High Power Density
- Low Gate Drive Requirement

#### Applications

- High Frequency Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts

**Symbol Test Conditions**
 $(T_J = 25^\circ\text{C Unless Otherwise Specified})$ 
**Characteristic Values**


|              |                                                                                                                                                                  | Min. | Typ. | Max.                    |
|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|------|-------------------------|
| $g_{fs}$     | $I_C = 60\text{A}, V_{CE} = 10\text{V}, \text{Note 1}$                                                                                                           | 40   | 70   | S                       |
| $C_{ies}$    | $V_{CE} = 25\text{V}, V_{GE} = 0\text{V}, f = 1\text{MHz}$                                                                                                       |      | 9800 | pF                      |
| $C_{oes}$    |                                                                                                                                                                  |      | 567  | pF                      |
| $C_{res}$    |                                                                                                                                                                  |      | 215  | pF                      |
| $Q_{g(on)}$  | $I_C = I_{C110}, V_{GE} = 15\text{V}, V_{CE} = 0.5 \cdot V_{CES}$                                                                                                |      | 400  | nC                      |
| $Q_{ge}$     |                                                                                                                                                                  |      | 70   | nC                      |
| $Q_{gc}$     |                                                                                                                                                                  |      | 190  | nC                      |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 25^\circ\text{C}</math></b><br>$I_C = 100\text{A}, V_{GE} = 15\text{V}$<br>$V_{CE} = 0.8 \cdot V_{CES}, R_G = 1\Omega$<br>Note 2  |      | 30   | ns                      |
| $t_{ri}$     |                                                                                                                                                                  |      | 54   | ns                      |
| $E_{on}$     |                                                                                                                                                                  |      | 9.7  | mJ                      |
| $t_{d(off)}$ |                                                                                                                                                                  |      | 340  | ns                      |
| $t_{fi}$     |                                                                                                                                                                  |      | 260  | ns                      |
| $E_{off}$    |                                                                                                                                                                  |      | 21.5 | mJ                      |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 150^\circ\text{C}</math></b><br>$I_C = 100\text{A}, V_{GE} = 15\text{V}$<br>$V_{CE} = 0.8 \cdot V_{CES}, R_G = 1\Omega$<br>Note 2 |      | 29   | ns                      |
| $t_{ri}$     |                                                                                                                                                                  |      | 55   | ns                      |
| $E_{on}$     |                                                                                                                                                                  |      | 14.7 | mJ                      |
| $t_{d(off)}$ |                                                                                                                                                                  |      | 420  | ns                      |
| $t_{fi}$     |                                                                                                                                                                  |      | 406  | ns                      |
| $E_{off}$    |                                                                                                                                                                  |      | 27.9 | mJ                      |
| $R_{thJC}$   |                                                                                                                                                                  |      |      | 0.10 $^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                                                  |      | 0.15 | $^\circ\text{C/W}$      |

**Notes:**


1. Pulse test,  $t \leq 300\mu\text{s}$ , duty cycle,  $d \leq 2\%$ .
2. Switching times & energy losses may increase for higher  $V_{CE}(\text{clamp})$ ,  $T_J$  or  $R_G$ .

**ADVANCE TECHNICAL INFORMATION**

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

**TO-264P Outline**


| SYM       | INCHES |       | MILLIMETERS |       |
|-----------|--------|-------|-------------|-------|
|           | MIN    | MAX   | MIN         | MAX   |
| A         | .185   | .209  | 4.70        | 5.30  |
| A1        | .102   | .118  | 2.60        | 3.00  |
| b         | .035   | .049  | 0.90        | 1.25  |
| b1        | .091   | .106  | 2.30        | 2.70  |
| b2        | .110   | .126  | 2.80        | 3.20  |
| c         | .020   | .033  | 0.50        | 0.85  |
| D         | 1.012  | 1.035 | 25.70       | 26.30 |
| D1        | .783   | .799  | 19.90       | 20.30 |
| D2        | .185   | .205  | 4.70        | 5.20  |
| E         | .776   | .799  | 19.70       | 20.30 |
| E1        | .661   | .677  | 16.80       | 17.20 |
| e         | .215   | BSC   | 5.46        | BSC   |
| L         | .768   | .807  | 19.50       | 20.50 |
| L1        | .091   | .106  | 2.30        | 2.70  |
| Q         | .228   | .244  | 5.80        | 6.20  |
| Q1        | .346   | .362  | 8.80        | 9.20  |
| $\phi R$  | .150   | .165  | 3.80        | 4.20  |
| $\phi R1$ | .071   | .087  | 1.80        | 2.20  |

**PLUS247™ Outline**


Terminals: 1 - Gate  
2,4 - Collector  
3 - Emitter

| SYM | INCHES |      | MILLIMETERS |       |
|-----|--------|------|-------------|-------|
|     | MIN    | MAX  | MIN         | MAX   |
| A   | .190   | .205 | 4.83        | 5.21  |
| A1  | .090   | .100 | 2.29        | 2.54  |
| A2  | .075   | .085 | 1.91        | 2.16  |
| b   | .045   | .055 | 1.14        | 1.40  |
| b2  | .075   | .087 | 1.91        | 2.20  |
| b4  | .115   | .126 | 2.92        | 3.20  |
| C   | .024   | .031 | 0.61        | 0.80  |
| D   | .819   | .840 | 20.80       | 21.34 |
| D1  | .650   | .690 | 16.51       | 17.53 |
| D2  | .035   | .050 | 0.89        | 1.27  |
| E   | .620   | .635 | 15.75       | 16.13 |
| E1  | .520   | .560 | 13.08       | 14.22 |
| e   | .215   | BSC  | 5.45        | BSC   |
| L   | .780   | .810 | 19.81       | 20.57 |
| L1  | .150   | .170 | 3.81        | 4.32  |
| Q   | .220   | .244 | 5.59        | 6.20  |
| R   | .170   | .190 | 4.32        | 4.83  |

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered 4,835,592 4,931,844 5,049,961 5,237,481 6,162,665 6,404,065 B1 6,683,344 6,727,585 7,005,734 B2 7,157,338B2  
by one or more of the following U.S. patents: 4,860,072 5,017,508 5,063,307 5,381,025 6,259,123 B1 6,534,343 6,710,405 B2 6,759,692 7,063,975 B2  
4,881,106 5,034,796 5,187,117 5,486,715 6,306,728 B1 6,583,505 6,710,463 6,771,478 B2 7,071,537



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).