
IXYS

Depletion Mode MOSFET


IXTA6N100D2
IXTP6N100D2
IXTH6N100D2

V_{DSX} = 1000V
$I_{D(on)}$ ≥ 6A
$R_{DS(on)}$ ≤ 2.2Ω


N-Channel




TO-263 AA (IXTA)



TO-220AB (IXTP)



TO-247 (IXTH)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSX}	T_J = 25°C to 150°C	1000	V
V_{GSX}	Continuous	±20	V
V_{GSM}	Transient	±30	V
P_D	T_C = 25°C	300	W
T_J		- 55 ... +150	°C
T_{JM}		150	°C
T_{stg}		- 55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
M_d	Mounting Torque (TO-220 & TO-247)	1.13 / 10	Nm/lb.in.
Weight	TO-263	2.5	g
	TO-220	3.0	g
	TO-247	6.0	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSX}	V_{GS} = - 5V, I_D = 250μA	1000			V
$V_{GS(off)}$	V_{DS} = 25V, I_D = 250μA	- 2.5		- 4.5	V
I_{GSX}	V_{GS} = ±20V, V_{DS} = 0V			±100	nA
$I_{DSX(off)}$	V_{DS} = V_{DSX}, V_{GS} = - 5V			5	μA
	T_J = 125°C			50	μA
$R_{DS(on)}$	V_{GS} = 0V, I_D = 3A, Note 1			2.2	Ω
$I_{D(on)}$	V_{GS} = 0V, V_{DS} = 50V, Note 1	6			A

Features

- Normally ON Mode
- International Standard Packages
- Molding Epoxies Meet UL 94 V-0 Flammability Classification

Advantages

- Easy to Mount
- Space Savings
- High Power Density

Applications

- Audio Amplifiers
- Start-Up Circuits
- Protection Circuits
- Ramp Generators
- Current Regulators
- Active Loads

© 2017 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 30V, I_D = 3A, Note 1	2.6	4.2		S
C_{iss}	V_{GS} = -10V, V_{DS} = 25V, f = 1MHz		2650		pF
C_{oss}			167		pF
C_{rss}			41		pF
$t_{d(on)}$	**Resistive Switching Times**		25		ns
t_r	V_{GS} = ±5V, V_{DS} = 500V, I_D = 3A		80		ns
$t_{d(off)}$	R_G = 2.4Ω (External)		34		ns
t_f			47		ns
$Q_{g(on)}$	V_{GS} = 5V, V_{DS} = 500V, I_D = 3A		95		nC
Q_{gs}			11		nC
Q_{gd}			51		nC
R_{thJC}				0.41	°C/W
R_{thCS}	TO-220		0.50		°C/W
	TO-247		0.21		°C/W

Safe-Operating-Area Specification


Symbol	Test Conditions	Characteristic Values Min.	Typ.	Max.	
SOA	V_{DS} = 800V, I_D = 225mA, T_C = 75°C, Tp = 5s	180			W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
V_{SD}	I_F = 6A, V_{GS} = -10V, Note 1		0.8	1.3	V
t_{rr}	I_F = 3A, -di/dt = 100A/μs		952		ns
I_{RM}	V_R = 100V, V_{GS} = -10V		16		A
Q_{RM}			7.6		μC

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.


TO-263 (IXTA) Outline



1. Gate
2. Drain
3. Source
4. Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.06	4.83	.160	.190
b	0.51	0.99	.020	.039
b2	1.14	1.40	.045	.055
c	0.40	0.74	.016	.029
c2	1.14	1.40	.045	.055
D	8.64	9.65	.340	.380
D1	8.00	8.89	.280	.320
E	9.65	10.41	.380	.405
E1	6.22	8.13	.270	.320
e	2.54	BSC	.100	BSC
L	14.61	15.88	.575	.625
L1	2.29	2.79	.090	.110
L2	1.02	1.40	.040	.055
L3	1.27	1.78	.050	.070


TO-220 (IXTP) Outline



Pins: 1 - Gate 2 - Drain
3 - Source 4 - Drain

SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.170	.190	4.32	4.83
b	.025	.040	0.64	1.02
b1	.045	.065	1.15	1.65
c	.014	.022	0.35	0.56
D	.580	.630	14.73	16.00
E	.390	.420	9.91	10.66
e	.100 BSC		2.54 BSC	
F	.045	.055	1.14	1.40
H1	.230	.270	5.85	6.85
J1	.090	.110	2.29	2.79
k	0	.015	0	0.38
L	.500	.550	12.70	13.97
L1	.110	.230	2.79	5.84
ØP	.139	.161	3.53	4.08
Q	.100	.125	2.54	3.18

TO-247 (IXTH) AD Outline



1 = Gate
2 = Drain
3 = Source

SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.185	.209	4.7	5.3
A_1	.087	.102	2.2	2.54
A_2	.059	.098	2.2	2.6
b	.040	.055	1.0	1.4
b_1	.065	.084	1.65	2.13
b_2	.113	.123	2.87	3.12
C	.016	.031	.4	.8
D	.819	.845	20.80	21.46
E	.610	.640	15.75	16.26
e	.215 BSC		5.45 BSC	
L	.780	.800	19.81	20.32
L1		.177		4.50
ØP	.140	.144	3.55	3.65
Q	.212	.244	5.4	6.2
R	.170	.216	4.32	5.49
S	.242 BSC		6.15 BSC	

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25°C




Fig. 2. Extended Output Characteristics @ T_J = 25°C




Fig. 3. Output Characteristics @ T_J = 125°C




Fig. 4. Drain Current @ T_J = 25°C




Fig. 5. Drain Current @ T_J = 100°C





Fig. 6. Dynamic Resistance vs. Gate Voltage



© 2017 IXYS CORPORATION, All Rights Reserved

Fig. 7. Normalized $R_{DS(on)}$ vs. Junction Temperature




Fig. 8. $R_{DS(on)}$ Normalized to I_D = 3A Value vs. Drain Current




Fig. 9. Input Admittance




Fig. 10. Transconductance




Fig. 11. Breakdown and Threshold Voltages vs. Junction Temperature





Fig. 12. Forward Voltage Drop of Intrinsic Diode



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Capacitance




Fig. 14. Gate Charge




Fig. 15. Forward-Bias Safe Operating Area @ T_C = 25°C




Fig. 16. Forward-Bias Safe Operating Area @ T_C = 75°C





Fig. 17. Maximum Transient Thermal Impedance



© 2017 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.