
IXYS

High Voltage Depletion Mode Power MOSFET


IXTA6N100D2HV

V_{DSX} = 1000V
$I_{D(on)}$ ≥ 6A
$R_{DS(on)}$ ≤ 2.2Ω

N-Channel



TO-263HV
(IXTA..HV)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSX}	T_J = 25°C to 150°C	1000	V
V_{GSX}	Continuous	±20	V
V_{GSM}	Transient	±30	V
P_D	T_C = 25°C	300	W
T_J		- 55 ... +150	°C
T_{JM}		150	°C
T_{stg}		- 55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
M_d	Mounting Force	10..65 / 2.2..14.6	N/lb.
Weight		2.5	g

Features

- High Voltage package
- High Blocking Voltage
- Normally ON Mode
- High Voltage package

Advantages

- Easy to Mount
- Space Savings
- High Power Density

Applications

- Audio Amplifiers
- Start-Up Circuits
- Protection Circuits
- Ramp Generators
- Current Regulators
- Active Loads

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSX}	V_{GS} = - 5V, I_D = 250μA	1000			V
$V_{GS(off)}$	V_{DS} = 25V, I_D = 250μA	- 2.5		- 4.5	V
I_{GSX}	V_{GS} = ±20V, V_{DS} = 0V			±100	nA
$I_{DSX(off)}$	V_{DS} = V_{DSX}, V_{GS} = - 5V			5	μA
	T_J = 125°C			50	μA
$R_{DS(on)}$	V_{GS} = 0V, I_D = 3A, Note 1			2.2	Ω
$I_{D(on)}$	V_{GS} = 0V, V_{DS} = 50V, Note 1	6			A

© 2019 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 30V, I_D = 3A, Note 1	2.6	4.2		S
C_{iss}	V_{GS} = -10V, V_{DS} = 25V, f = 1MHz		2650		pF
C_{oss}			167		pF
C_{rss}			41		pF
$t_{d(on)}$	**Resistive Switching Times**		25		ns
t_r	V_{GS} = ± 5V, V_{DS} = 500V, I_D = 3A		80		ns
$t_{d(off)}$	R_G = 2.4Ω (External)		34		ns
t_f			47		ns
$Q_{g(on)}$	V_{GS} = 5V, V_{DS} = 500V, I_D = 3A		95		nC
Q_{gs}			11		nC
Q_{gd}			51		nC
R_{thJC}				0.41	°C/W

Safe-Operating-Area Specification

Symbol	Test Conditions	Characteristic Values Min.	Typ.	Max.	
SOA	V_{DS} = 800V, I_D = 225mA, T_C = 75°C, Tp = 5s	180			W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
V_{SD}	I_F = 6A, V_{GS} = -10V, Note 1		0.8	1.3	V
t_{rr}	I_F = 3A, -di/dt = 100A/μs		952		ns
I_{RM}	V_R = 100V, V_{GS} = -10V		16		A
Q_{RM}			7.6		μC

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or moreof the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25°C




Fig. 2. Extended Output Characteristics @ T_J = 25°C




Fig. 3. Output Characteristics @ T_J = 125°C




Fig. 4. Drain Current @ T_J = 25°C




Fig. 5. Drain Current @ T_J = 100°C





Fig. 6. Dynamic Resistance vs. Gate Voltage



© 2019 IXYS CORPORATION, All Rights Reserved

Fig. 7. Normalized $R_{DS(on)}$ vs. Junction Temperature




Fig. 8. $R_{DS(on)}$ Normalized to I_D = 3A Value vs. Drain Current




Fig. 9. Input Admittance




Fig. 10. Transconductance




Fig. 11. Breakdown and Threshold Voltages vs. Junction Temperature





Fig. 12. Forward Voltage Drop of Intrinsic Diode



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Capacitance




Fig. 14. Gate Charge




Fig. 15. Forward-Bias Safe Operating Area @ T_C = 25°C




Fig. 16. Forward-Bias Safe Operating Area @ T_C = 75°C






Fig. 17. Maximum Transient Thermal Impedance



© 2019 IXYS CORPORATION, All Rights Reserved

TO-263HV Outline



1 = Gate
2 = Source
3 = Drain

SYM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	.170	.185	4.30	4.70
A1	.000	.008	0.00	0.20
A2	.091	.098	2.30	2.50
b	.028	.035	0.70	0.90
b2	.046	.054	1.18	1.38
C	.018	.024	0.45	0.60
C2	.049	.055	1.25	1.40
D	.354	.370	9.00	9.40
D1	.311	.327	7.90	8.30
D2	.083	.098	2.10	2.50
E	.386	.402	9.80	10.20
E1	.307	.323	7.80	8.20
e1	.200 BSC		5.08 BSC	
(e2)	.163	.174	4.13	4.43
H	.591	.614	15.00	15.60
L	.079	.102	2.00	2.60
L1	.039	.055	1.00	1.40
L3	.010 BSC		0.254 BSC	
(L4)	.071	.087	1.80	2.20



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 IXYS CORPORATION, All Rights Reserved