
IXYS

TrenchP™ Power MOSFET


IXTT76P10THV
IXTA76P10T
IXTP76P10T
IXTH76P10T

V_{DSS} = - 100V
I_{D25} = - 76A
$R_{DS(on)}$ ≤ 25mΩ


P-Channel Enhancement Mode
Avalanche Rated




TO-268HV (IXTT)




TO-263 AA (IXTA)



TO-220AB (IXTP)



TO-247 (IXTH)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	- 100	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	- 100	V
V_{GSS}	Continuous	±15	V
V_{GSM}	Transient	±25	V
I_{D25}	T_C = 25°C	- 76	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	- 230	A
I_A	T_C = 25°C	- 38	A
E_{AS}	T_C = 25°C	1	J
P_D	T_C = 25°C	298	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
M_d	Mounting Torque (TO-220 & TO-247)	1.13 /10	Nm/lb.in.
Weight	TO-263	2.5	g
	TO-220	3.0	g
	TO-268HV	4.0	g
	TO-247	6.0	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = - 250μA	-100			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = - 250μA	- 2.0		- 4.0	V
I_{GSS}	V_{GS} = ±15V, V_{DS} = 0V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			- 15	μA
	T_J = 125°C			- 750	μA
$R_{DS(on)}$	V_{GS} = -10V, $I_D = 0.5 \bullet I_{D25}$, Note 1			25	mΩ

Features

- International Standard Packages
- Avalanche Rated
- Extended FBSOA
- Fast Intrinsic Diode
- Low $R_{DS(ON)}$ and Q_G

Advantages

- Easy to Mount
- Space Savings

Applications

- High-Side Switching
- Push Pull Amplifiers
- DC Choppers
- Automatic Test Equipment
- Current Regulators
- Battery Charger Applications

© 2017 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = -10V, I_D = 0.5 • I_{D25}, Note 1	35	58		S
C_{iss}	V_{GS} = 0V, V_{DS} = - 25V, f = 1MHz		13.7		nF
C_{oss}			890		pF
C_{rss}			275		pF
$t_{d(on)}$	**Resistive Switching Times**		25		ns
t_r	V_{GS} = -10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		40		ns
$t_{d(off)}$	R_G = 1Ω (External)		52		ns
t_f			20		ns
$Q_{g(on)}$	V_{GS} = -10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		197		nC
Q_{gs}			65		nC
Q_{gd}			65		nC
R_{thJC}				0.42	°C/W
R_{thCS}	TO-220		0.50		°C/W
	TO-247		0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			- 76	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			- 304	A
V_{SD}	I_F = - 38A, V_{GS} = 0V, Note 1			-1.3	V
t_{rr}	I_F = - 38A, -di/dt = -100A/μs		70		ns
Q_{RM}	V_R = - 50V, V_{GS} = 0V		215		nC
I_{RM}			- 6		A

Note 1: Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

IXYS Reserves The Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25°C




Fig. 2. Extended Output Characteristics @ T_J = 25°C




Fig. 3. Output Characteristics @ T_J = 125°C




Fig. 4. $R_{DS(on)}$ Normalized to I_D = - 38A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = - 38A Value vs. Drain Current





Fig. 6. Maximum Drain Current vs. Case Temperature



© 2017 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance




Fig. 12. Forward-Bias Safe Operating Area




Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature




Fig. 14. Resistive Turn-on Rise Time vs. Drain Current




Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance




Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature




Fig. 17. Resistive Turn-off Switching Times vs. Drain Current






Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance




© 2017 IXYS CORPORATION, All Rights Reserved

Fig. 19. Maximum Transient Thermal Impedance




TO-268HV Outline



PINS:
1 - Gate 2 - Source
3 - Drain

SYM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.465	.476	11.80	12.10
D2	.295	.307	7.50	7.80
D3	.114	.126	2.90	3.20
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215	BSC	5.45	BSC
(e2)	.374	.386	9.50	9.80
H	.736	.752	18.70	19.10
L	.067	.079	1.70	2.00
L2	.039	.045	1.00	1.15
L3	.010	BSC	0.25	BSC
L4	.150	.161	3.80	4.10


TO-263 Outline



1 = Gate
2 = Drain
3 = Source
4 = Drain

SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.160	.190	4.06	4.83
A1	.080	.110	2.03	2.79
b	.020	.039	0.51	0.99
b2	.045	.055	1.14	1.40
c	.016	.029	0.40	0.74
c2	.045	.055	1.14	1.40
D	.340	.380	8.64	9.65
D1	.315	.350	8.00	8.89
E	.380	.410	9.65	10.41
E1	.245	.320	6.22	8.13
e	.100 BSC		2.54 BSC	
L	.575	.625	14.61	15.88
L1	.090	.110	2.29	2.79
L2	.040	.055	1.02	1.40
L3	.050	.070	1.27	1.78
L4	0	.005	0	0.13


TO-220 Outline



Pins: 1 - Gate 2 - Drain
3 - Source

SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.170	.190	4.32	4.83
b	.025	.040	0.64	1.02
b1	.045	.065	1.15	1.65
c	.014	.022	0.35	0.56
D	.580	.630	14.73	16.00
E	.390	.420	9.91	10.66
e	.100 BSC		2.54 BSC	
F	.045	.055	1.14	1.40
H1	.230	.270	5.85	6.85
J1	.090	.110	2.29	2.79
k	0	.015	0	0.38
L	.500	.550	12.70	13.97
L1	.110	.230	2.79	5.84
ØP	.139	.161	3.53	4.08
Q	.100	.125	2.54	3.18

TO-247 Outline



1 - Gate
2,4 - Drain
3 - Source

Dim.	Millimeter		Inches	
	min	max	min	max
A	4.70	5.30	0.185	0.209
A1	2.21	2.59	0.087	0.102
A2	1.50	2.49	0.059	0.098
b	0.99	1.40	0.039	0.055
b2	1.65	2.39	0.065	0.094
b4	2.59	3.43	0.102	0.135
c	0.38	0.89	0.015	0.035
D	20.79	21.45	0.819	0.845
D1	13.07	-	0.515	-
D2	0.51	1.35	0.020	0.053
E	15.48	16.24	0.610	0.640
E1	13.45	-	0.53	-
E2	4.31	5.48	0.170	0.216
e	5.45 BSC		0.215 BSC	
L	19.80	20.30	0.078	0.800
L1	-	4.49	-	0.177
Ø P	3.55	3.65	0.140	0.144
Ø P1	-	7.39	-	0.290
Q	5.38	6.19	0.212	0.244
S	6.14 BSC		0.242 BSC	

© 2017 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.