# POWR-BLOK™ Modules



**Powr-Blok™ Modules: Introduction** **1**

**Fuse Modules** **2**
2-Position ATO® Style Fuse and Circuit Breaker Module 2
4-Position ATO® Style Fuse and Circuit Breaker Module 2
7-Position ATO® Style Fuse and Circuit Breaker Module 3
4-Position MINI® Style Fuse Module 3
6-Position MINI® Style Fuse Module 4
8-Position MINI® Style Fuse Module 4
2-Position MAXI™ Style Fuse Module 5
4-Position MAXI™ Style Fuse Module 5

**Relay Modules** **6**
1-Position ISO Relay Module 6
2-Position ISO Relay Module 6
3-Position Micro Relay Module 7
1-Position 9 Pin Relay Module 7
2-Position 280 Micro Relay + 2 Position MINI® Style Fuse 8
1-Position Power Relay Module 8
2-Pin Flasher Module 9

**Specialty Modules** **10**
Blank Module 10
2-Position Blank Module 10
Power Tap Module 11
2-Stud Assembly Module 11
4-Stud Assembly Module 12
2-Position Push Button Circuit Breaker Module 12
Storage Module/Drawer Insert 13
Splash Proof Cover for: 4-Position MINI® Fuse Module 13

**Assembly/Mounting Accessories** **14**
Assembly Accessories—BLOK-LOKS™ 14
Mounting Accessories—Mounting Standoffs 14
Mounting Accessories—Mounting Module 15
Mounting Leg 15
Mounting Accessories—Flush Mounting Leg 16
Side Mounting Bracket 16

**Terminals** **17-21**

**Starter Terminals** **22**


**Terminal Loks** **23**


© 2012 Littelfuse • Transportation Products Catalog Excerpt

# POWR-BLOK™ MODULES

## Description

The Littelfuse POWR-BLOKS™ system gives you unlimited flexibility to design electrical distribution systems. It's a totally modular way to build your own junction box. POWR-BLOKS are perfect for applications where space or vehicle function demand a tailor made approach. The Littelfuse POWR-BLOKS can be modified, re-sized, reconfigured or added to at any time.




## Mechanical Strength for Any Application

POWR-BLOKS modules are molded from glass reinforced nylon for dimensional stability, excellent rigidity, high and low temperature resistance and tensile strength:

## Specifications

| | |
|---|---|
| Test | POWR-BLOKS™ Standard |
| Voltage Rating | 48VDC |
| Temperature range | -40°C to +125°C |
| Durability | Minimum 50 cycles of engagement/ disengagement |
| Drop | 1.22 meters onto wooden platform |
| Thermal Shock | 5 Cycles from -40°C to +125°C |
| Mechanical Shock | 50g in each of 3 mutually perpendicular axis |
| Fluid Compatibility | Gasoline, diesel fuel, motor oil, antifreeze, brake fluid, ATF |

## *Max. Current Indication

The information listed as Max. current indication is to be used as a guideline only. The maximum allowable rating of the fuses used depends on design criteria such as maximum current, nominal current the duration for which the circuits are energized, as well as external factors as ambient temperature. All modules should therefore be tested as an assembly, and users should make their own evaluation to determine the suitability of the product for their specific applications.

## How to use the Littelfuse POWR-BLOKS system

1. Identify the electrical system parameters
   - Space availability and requirements
   - Circuit protection components
   - Relay and flasher components
   - Components for special needs

2. Select the Littelfuse POWR-BLOKS components. Lay out the electrical panel as designed. Then determine the appropriate type and quantity of POWR-BLOKS modules, BLOCK LOKS and TERMINAL LOKS you need.

3. Build the panel by row. POWR-BLOKS can be assembled without special tools. Assemble the block from the rear by placing all modules face down on a flat surface. POWR-BLOKS should be designed by row, either going across or up and down.

4. Use BLOK LOKS to interconnect modules. BLOK LOKS are used to connect and stack POWR-BLOKS modules. Press together a row of modules and insert green BLOK LOKS until they snap into place. Repeat this procedure to interlock all assembled rows.


5. Add mounting modules. Once a POWR-BLOKS panel is assembled, add mounting modules that are most suitable for your application. Mounting options include surface mounting legs, a side mounting bracket and a mounting module with three different sized spacers.

6. Plug in terminated wiring. Wire your POWR-BLOKS panel and plug in the terminated wires, then insert the optional matching TERMINAL LOKS devices. Littelfuse TERMINAL LOKS are designed to fit special POWR-BLOKS modules and inserted in the same manner as BLOK LOKS.

The information and illustrations given in this catalogue are believed to be reliable and accurate. Littelfuse makes no warranties as to their accuracy or completeness, and disclaims any liability in connection with their use. Littelfuse's only obligations are those in the standard terms of sale for this product and Littelfuse will not be liable for any consequential or other damages arising out of the use or misuse of this product. Littelfuse reserves the right to make changes to the contents hereof without notice. It is suggested that at the time of inquiry Littelfuse Sales personnel be contacted directly for verification of published specifications and product availability.


# 2-POSITION ATO® STYLE FUSE AND CIRCUIT BREAKER MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540501Z (40 pcs.) | 60A | Type 1 or 7 | Type 4, 5 or 6 |


# 4-POSITION ATO® STYLE FUSE AND CIRCUIT BREAKER MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540502Z (20 pcs.) | 120A | Type 1 or 7 | Type 4, 5, 6 or 7 |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# 7-POSITION ATO® STYLE FUSE AND CIRCUIT BREAKER MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540503Z (20 pcs.) | 120A | Type 1 or 7 | Type 4 or 5 |


# 4-POSITION MINI® STYLE FUSE MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540532Z (40 pcs.) | 60A | Type 6 | – |


# 6-POSITION MINI® STYLE FUSE MODULE

RoHS



## Dimensions

Dimensions in mm




## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540543Z (40 pcs.) | 60A | Type 8 | – |


# 8-POSITION MINI® STYLE FUSE MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540544Z (40 pcs.) | 60A | Type 8 | – |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# 2-POSITION MAXI™ STYLE FUSE MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540549Z (40 pcs.) | 80A | Type 2 | Type 8 |


# 4-POSITION MAXI™ STYLE FUSE MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540505Z (20 pcs.) | 160A | Type 2 | Type 8 |

# 1-POSITION ISO RELAY MODULE


## Alternative for: 3 pin flasher module

RoHS



### Dimensions

Dimensions in mm





### Ratings

| Part Number | Remarks | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540506Z (40 pcs.) | – | Type 3 | Type 1 |

# 2-POSITION ISO RELAY MODULE


## Alternative for: 3 pin flasher module

RoHS



### Dimensions

Dimensions in mm





### Ratings

| Part Number | Remarks | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540536Z (20 pcs.) | – | Type 3 | Type 1 |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# 3-POSITION MICRO RELAY MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540507Z (20 pcs.) | Coil and normally closed contacts | Type 5 | Type 3 |
| 03540507Z (20 pcs.) | Normally open contacts | Type 3 | Type 2 |


# 1-POSITION 9 PIN RELAY MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540542Z (40 pcs.) | 5 “Inner” pins | Type 3 | Type 1 |
| 03540542Z (40 pcs.) | 4 “Outer” pins | Type 6 | – |


# 2-POSITION 280 MICRO RELAY + 2 POSITION MINI® STYLE FUSE

RoHS



## Dimensions

Dimensions in mm




## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540551Z (40 pcs.) | Max. current indication 30A | Type 8 | – |


# 1-POSITION POWER RELAY MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540535Z (40 pcs.) | Coil | Type 3 | Type 1 |
| 03540535Z (40 pcs.) | Contacts | Type 4 | – |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# 2-PIN FLASHER MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Max. Current Indication | Terminals (see according section) | Terminal Loks (see according section) |
|---|---|---|---|
| 03540508Z (40 pcs.) | – | Type 3 | Type 1 |


# BLANK MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540520Z (40 pcs.) | – |


# 2-POSITION BLANK MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540550Z (20 pcs.) | – |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# POWER TAP MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540539Z (40 pcs.) | M8 Tread Metric |
| 03540512Z (100 pcs.) | 1/ 4 inch - 20 thread |
| 03540513Z (100 pcs.) | 5/16 inch - 18 thread |


# 2-STUD ASSEMBLY MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540537Z (20 pcs.) | M6 Thread, Metric |


# 4-STUD ASSEMBLY MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540538Z (20 pcs.) | M6 Thread Metric |


# 2-POSITION PUSH BUTTON CIRCUIT BREAKER MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540504Z (20 pcs.) | – |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# STORAGE MODULE/DRAWER INSERT

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540521Z (20 pcs.) | Body |
| 03540522Z (20 pcs.) | Drawer |


# SPLASH PROOF COVER FOR: 4-POSITION MINI® FUSE MODULE

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540534Z (20 pcs.) | Cover |
| 03540533Z (20 pcs.) | Lock |
| 09130085Z (20 pcs.) | Seal |


# ASSEMBLY ACCESSORIES—BLOK LOKS™

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540523Z (250 pcs.) | – |


# MOUNTING ACCESSORIES—MOUNTING STANDOFFS

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540515Z (10 pcs.) | 0.75 Inch / 19mm |
| 03540516Z (10 pcs.) | 1 Inch / 25.4mm |
| 03540517Z (10 pcs.) | 1.25 Inch / 31.7mm |


© 2012 Littelfuse • Transportation Products Catalog Excerpt


# MOUNTING ACCESSORIES—MOUNTING MODULE

RoHS



## Dimensions

Dimensions in mm




## Ratings

| Part Number | Remarks |
|---|---|
| 03540514Z (40 pcs.) | – |


# MOUNTING LEG

RoHS



## Dimensions

Dimensions in mm




## Ratings

| Part Number | Remarks |
|---|---|
| 03540541Z (50 pcs.) | 2.50 Inch / 63.5mm |
| 03540518Z (50 pcs.) | 3 Inch / 76.2mm |


# MOUNTING ACCESSORIES—FLUSH MOUNTING LEG

RoHS



## Dimensions

Dimensions in mm





## Ratings

| Part Number | Remarks |
|---|---|
| 03540519Z (50 pcs.) | – |


# SIDE MOUNTING BRACKET

RoHS



## Dimensions

Dimensions in mm




## Ratings

| Part Number | Remarks |
|---|---|
| 03540540Z (50 pcs.) | – |


© 2012 Littelfuse • Transportation Products Catalog Excerpt

# TERMINAL TYPE 1

RoHS





## Terminal Loks

| Description | Wire Diam. | Type of terminal loks |
|---|---|---|
| For part number: 354501 / 354502 / 354503 | 0.50 - 2 $mm^2$ | 4 |
| For part number: 354501 / 354502 / 354503 | 0.50 - 2 & 3.3 - 5.3 $mm^2$ | 5 |
| For part number: 354501 / 354502 | 0.50 - 2 $mm^2$ | 6 |
| For part number: 354502 | 0.50 - 2 $mm^2$ | 7 |


## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-070 (Reeled per 2200 pcs)<br>0913070001 (Single per 250 pcs) | Heavy Duty + spring clip* | 0.5-0.8 $mm^2$ / 18-20AWG<br>0.5-0.8 $mm^2$ / 18-20AWG | Brass |
| 913-071 (Reeled per 2200 pcs)<br>913-071XS (Reeled per 2200 pcs) | Heavy Duty + spring clip* | 1.33-2.09 $mm^2$ / 14-16AWG<br>1.33-2.09 $mm^2$ / 14-16AWG | Brass<br>Silver plated copper |
| 0913071001 (Single per 250 pcs)<br>913-072 (Reeled per 2200 pcs) | Heavy Duty + spring clip* | 1.33-2.09 $mm^2$ / 14-16AWG<br>3.32-5.37 $mm^2$ / 10-12AWG | Brass |
| 913-072XS (Reeled per 2200 pcs)<br>0913072001 (Single per 250 pc) | Heavy Duty + spring clip* | 3.32-5.37 $mm^2$ / 10-12AWG<br>3.32-5.37 $mm^2$ / 10-12AWG | Silver plated copper<br>Brass |
| 913-058 (Reeled per 4500 pcs)<br>0913058001 (Single per 250 pcs) | Standard Duty | 0.5-0.8 $mm^2$ / 18-20AWG<br>0.5-0.8 $mm^2$ / 18-20AWG | Brass |
| 913-059 (Reeled per 4500 pcs)<br>0913059001 (Single per 250 pcs) | Standard Duty | 1.33-2.09 $mm^2$ / 14-16AWG<br>1.33-2.09 $mm^2$ / 14-16 AWG | Brass |
| 913-060 (Reeled per 4500 pcs)<br>0913060001 (Single per 250 pcs) | Standard Duty | 3.32-5.37 $mm^2$ / 10-12AWG<br>3.32-5.37 $mm^2$ / 10-12AWG | Brass |

* Spring clip material: Stainless steel

# TERMINAL TYPE 2

RoHS



## Terminal Loks


| Description | Wire Diam. | Type of terminal loks |
|---|---|---|
| For part number: 354505 | 0,50 - 2 mm² | 8 |

## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-063 (Reeled per 1200 pcs)<br>0913063001 (Single per 250 pcs) | Female 8.0 mm | 0.82-1.33 mm² / 18-16AWG<br>0.82-1.33 mm² / 18-16AWG | Silver plated brass |
| 913-064 (Reeled per 1200 pcs)<br>0913064001 (Single per 250 pcs) | Female 8.0 mm | 2.09-3.32 mm² / 14-12AWG<br>2.09-3.32 mm² / 14-12AWG | Silver plated brass |
| 913-068 (Reeled 1200 pcs)<br>0913068001 (Single per 250 pcs) | Female 8.0 mm | 5.37mm² / 10AWG<br>5.37mm² / 10AWG | Silver plated brass |

# TERMINAL TYPE 3

RoHS



## Terminal Loks

| Description | Wire Diam. | Type of terminal loks |
|---|---|---|
| For part number: 354506 / 354508 / 354535 / 354536 | – | 1 |
| For part number: 354505 | – | 2 |

## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-053 (Reeled per 2000 pcs)<br>0913053001 (Single per 250 pcs) | – | 0.5-0.8 mm² / 18-20AWG<br>0.5-0.8 mm² / 18-20AWG | Tin plated brass |
| 913-253 (Reeled per 3000 pcs) | – | 0.5-1.00 mm² (metric) | Tin plated brass |
| 913-065 (Reeled per 2100 pcs)<br>0913065001 (Single per 250 pcs) | – | 1.33-2.09 mm² / 14-16AWG<br>1.33-2.09 mm² / 14-16AWG | Tin plated brass |
| 913-265 (Reeled per 2500 pcs) | – | 1.1-2.50 mm² (metric) | Tin plated brass |
| 913-055 (Reeled per 1900 pcs)<br>0913055001 (Single per 250 pcs) | – | 3.32-5.37 mm² / 10-12AWG<br>3.32-5.37 mm² / 10-12AWG | Tin plated brass |
| 913-255 (Reeled per 15000 pcs) | – | 4.0-6.0 mm² (metric) | Tin plated brass |


© 2012 Littelfuse • Transportation Products Catalog Excerpt

# TERMINAL TYPE 4

RoHS



## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-073 (Reeled per 2000 pcs)<br>0913073001 (Single per 250 pcs) | Female | 3.0-6.0 mm²/10-12AWG<br>3.0-6.0 mm²/10-12AWG | Tin plated Brass |
| 913-074 (Reeled per 1000 pcs)<br>0913074001 (Single per 250 pcs) | Female | 6.0-10.0 mm²/8-10AWG<br>6.0-10.0 mm²/8-10AWG | Tin plated Brass |

# TERMINAL TYPE 5

RoHS



## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-067 (Reeled per 3500 pcs)<br>0913067001 (Single per 250 pcs) | Female | 0.82-1.33 mm²/16-18AWG<br>0.82-1.33 mm²/16-18AWG | Tin plated silicon bronze |
| 913-066 (Reeled per 3000 pcs)<br>0913066001 (Single per 250 pcs) | Female | 2.09-3.32 mm²/12-14AWG<br>2.09-3.32 mm²/12-14AWG | Tin plated silicon bronze |

# TERMINAL TYPE 6

RoHS




## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-772 (Reeled per 2500 pcs)<br>0913772001 (Single per 250 pcs) | Female | 0.5-0.8 mm²/18-20AWG<br>0.5-0.8 mm²/18-20AWG | Tin plated brass |
| 913-773 (Reeled per 2500 pcs)<br>0913773001 (Single per 250 pcs) | Female | 1.33-2.09 mm²/14-16AWG<br>1.33-2.09 mm²/14-16AWG | Tin plated brass |
| 913-774 (Reeled 2000 pcs)<br>0913774001 (Single per 250 pcs) | Female | 3.32-5.37 mm²/10-12AWG<br>3.32-5.37 mm²/10-12AWG | Tin plated brass |

# TERMINAL TYPE 7

RoHS



## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 09130075Z (Per 20 pcs) | Bus bar 2 position | 5.0-8.0 mm²/8-10AWG | Copper |
| 09130076Z (Per 20 pcs) | Bus bar 4 position | 5.0-8.0 mm²/8-10AWG | Copper |
| 09130077Z (Per 20 pcs) | Bus bar 7 position | 5.0-8.0 mm²/8-10AWG | Copper |


© 2012 Littelfuse • Transportation Products Catalog Excerpt

# TERMINAL TYPE 8

RoHS



## Ratings

| Part Number | Description | Wire Diam. | Material |
|---|---|---|---|
| 913-769 (Reeled per 4200 pcs)<br>0913769001 (Single per 250 pcs) | Female | 0.5-1.0 mm²<br>0.5-1.0 mm² | Part.Gold plated Brass |
| 913-770 (Reeled per 1000 pcs)<br>0913770001 (Single per 250 pcs) | Female | 1.5-2.5 mm²<br>1.5-2.5 mm² | Tin plated bronze |

# STARTER TERMINALS

RoHS



## Description

The starter terminal series are cable lugs for heavy-duty applications such as starter motors and battery connections.

## Ratings


| Part Number | mm² | Mounting Hole | Width (mm) | Material | Plating | Ref. |
|---|---|---|---|---|---|---|
| 09130633LXN (50 pcs)<br>09130633Z (1250 pcs) | 2.5-6.0 | 6.5 mm | 11 | Cu | Sn | 2906 |
| 09130634LXN (50 pcs)<br>09130634Z (600 pcs) | 6.0-15 | 8.4 mm | 15 | Cu | Sn | 2910 |
| 09130635LXN (50 pcs)<br>09130635Z (400 pcs) | 10 -25 | 8.4 mm | 15 | Cu | Sn | 2916 |
| 09130636LXN (50 pcs)<br>09130636Z (200 pcs) | 16-35 | 10.5 mm | 19 | Cu | Sn | 29025 |
| 09130637LXN (50 pcs)<br>09130637Z (150 pcs) | 25-50 | 10.5 mm | 19 | Cu | Sn | 29035 |
| 09130638LXN (50 pcs)<br>09130638Z (100 pcs) | 35-70 | 10.5 mm | 19 | Cu | Sn | 29050 |
| 09130639LXN (50 pcs)<br>09130639Z (50 pcs) | 50-95 | 13.5 mm | 22 | Cu | Sn | 29070 |
| 09130640LXN (50 pcs)<br>09130640Z (600 pcs) | 16 | 6.4 mm | 11 | Cu | Sn | 2916 HK |
| 09130641LXN (50 pcs)<br>09130641Z (300 pcs) | 25 | 8.4 mm | 15 | Cu | Sn | 29025 HK |
| 09130642LXN (50 pcs)<br>09130642Z (200 pcs) | 35 | 8.4 mm | 15 | Cu | Sn | 29035 HK (8.4) |
| 09130643LXN (50 pcs)<br>09130643Z (150 pcs) | 35 | 10.5 mm | 19 | Cu | Sn | 29035 HK (10.5) |
| 09130644LXN (50 pcs)<br>09130644Z (100 pcs) | 50 | 8.4 mm | 17 | Cu | Sn | 29050 HK (8.4) |
| 09130645LXN (50 pcs)<br>09130645Z (125 pcs) | 50 | 10.5 mm | 19 | Cu | Sn | 29050 HK (10.5) |
| 09130646LXN (50 pcs)<br>09130646Z (75 pcs) | 70 | 10.5 mm | 21 | Cu | Sn | 29070 HK |


© 2012 Littelfuse • Transportation Products Catalog Excerpt

# TERMINAL LOKS


RoHS

## Terminal Lok Type 1



03540524Z (250 pcs.)

## Terminal Lok Type 2




03540525Z (100 pcs.)

## Terminal Lok Type 3




03540526Z (100 pcs.)

## Terminal Lok Type 4




03540527Z (250 pcs.)

## Terminal Lok Type 5




03540528Z (250 pcs.)

## Terminal Lok Type 6




03540529Z (100 pcs.)

## Terminal Lok Type 7



03540530Z (100 pcs.)

## Terminal Lok Type 8



03540531Z (100 pcs.)