

# CBO, CCK, CCL SERIES LIFT TRUCK FUSES

32-125 Vdc • 1-300 A • Fast Acting & Time Delay



## Description


CBO fast acting, and CCK and CCL dual-element time-delay fuses are recommended for fork lift trucks and other similar battery operated equipment.

## Applications


Lift trucks, scissor lifts, pallet movers, and other low voltage battery operated equipment used to move hazardous materials.

## Dimensions (inches)

PART NO.	A	B	C
CCK 1-30A	3.070	2.500	0.56
CCK 35-60A	3.740	3.000	0.81
CCK 70-100A	4.460	3.500	1.06
CCK 120-200A	4.720	3.750	1.06
CCK 225-300A	4.710	3.750	1.06
CCL 30-60A	3.07	2.5	0.56
CCL 80-120A	3.49	2.75	0.81



CCK/CCL



CBO

## Specifications

**Voltage Ratings:** CBO: 32 Volts DC  
CCK: 125 Volts DC (1-300A)  
CCL: 125 Volts DC

**Ampere Range:** 1 – 300 amperes

**Interrupting Rating:** 10,000 A  
For operating characteristics contact factory

## Ordering Information

### AMPERE RATINGS CBO FAST ACTING (32 Vdc)

—	—	50	80
12	30	60	100
—	35	70	125
20	40	75	150

### AMPERE RATINGS CCK TIME-DELAY (125 Vdc)

1	20	40	75	140	200
2	25	50	80	150	225
10	30	60	100	160	250
15	35	70	120	175	300

### AMPERE RATINGS CCL TIME-DELAY (125 Vdc)

30	40	60	100	—
35	50	80	120	—

SERIES	TYPE	VOLT DC	AMP	CATALOG NUMBER	ORDERING NUMBER
CBO	FAST ACTING	32	10	CBO010	OCBO010.V
CCK	TIME-DELAY	125	120	CCK120	OCCK120.V
CCL	TIME-DELAY	125	120	CCL120	OCCL120.V