

FRED Module

$$V_{RRM} = 1200 \text{ V}$$


$$I_{FAV} = 2 \times 60 \text{ A}$$

$$t_{rr} = 50 \text{ ns}$$

Fast Recovery Epitaxial Diode
 Low Loss and Soft Recovery
 Parallel legs


Part number

DSEI2x61-12P



Backside: isolated

 E72873



Features / Advantages:

- Planar passivated chips
- Low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: ECO-PAC1


- Isolation Voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Height: 9 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Fast Diode				Ratings				
Symbol	Definition	Conditions		min.	typ.	max.	Unit	
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				1200	V	
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				1200	V	
I _R	reverse current, drain current	V _R = 1200 V	T _{VJ} = 25°C			2.2	mA	
		V _R = 960 V	T _{VJ} = 125°C			14	mA	
V _F	forward voltage drop	I _F = 60 A	T _{VJ} = 25°C			2.41	V	
		I _F = 120 A				2.76	V	
		I _F = 60 A	T _{VJ} = 150°C			2.05	V	
		I _F = 120 A				2.56	V	
I _{FAV}	average forward current	T _C = 45°C rectangular d = 0.5	T _{VJ} = 150°C			60	A	
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 150°C		1.58	V	
r _F	slope resistance					7.9	mΩ	
R _{thJC}	thermal resistance junction to case					0.7	K/W	
R _{thCH}	thermal resistance case to heatsink				0.10		K/W	
P _{tot}	total power dissipation	T _C = 25°C				180	W	
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		450	A	
C _J	junction capacitance	V _R = 600 V f = 1 MHz		T _{VJ} = 25°C	31		pF	
I _{RM}	max. reverse recovery current	} I _F = 60 A; V _R = 540 V -di _F /dt = 300 A/μs		T _{VJ} = 25 °C	13		A	
				T _{VJ} = 100 °C	20		A	
t _{rr}	reverse recovery time			T _{VJ} = 25 °C	190		ns	
				T _{VJ} = 100 °C	380		ns	

Package ECO-PAC1			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal			100	A
T_{VJ}	virtual junction temperature		-40		150	°C
T_{op}	operation temperature		-40		125	°C
T_{stg}	storage temperature		-40		125	°C
Weight				19		g
M_D	mounting torque		1.4		2	Nm
$d_{Spp/App}$	creepage distance on surface / striking distance through air	terminal to terminal	6.0			mm
$d_{Spb/Apb}$		terminal to backside	10.0			mm
V_{ISOL}	isolation voltage	t = 1 second	3000			V
		t = 1 minute	2500			V





Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DSEI2x61-12P	DSEI2x61-12P	Box	25	490806

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 150^{\circ}\text{C}$

			Fast Diode	
$V_{0\max}$	threshold voltage	1.58		V
$R_{0\max}$	slope resistance *	6.6		mΩ




Fast Diode


Fig. 1 Forward current I_F versus max. forward voltage drop V_F




Fig. 2 Typ. reverse recov. charge Q_r versus $-di_F/dt$




Fig. 3 Typ. peak reverse current I_{RM} versus $-di_F/dt$




Fig. 4 Dynamic parameters Q_r , I_{RM} versus T_{VJ}




Fig. 5 Typ. recovery time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. peak forward voltage V_{FR} and t_{fr} versus di_F/dt




Fig. 7 Transient thermal impedance junction to case

Constants for Z_{thJC} calculation:

i	R_{thi} (K/W)	t_i (s)
1	0.120	0.0100
2	0.045	0.0020
3	0.105	0.0500
4	0.160	0.0500
5	0.270	0.3500