



## 316 Series PICO®II, Very Fast-Acting Fuse



### Agency Approvals

Agency	Agency File Number	Ampere Range
	2007010207241295	0.50mA–5A

### Electrical Characteristics

% of Ampere Rating	Opening Time
100%	4 Hours, <b>Min.</b>
200%	5 Seconds, <b>Max.</b>
275%	0.30 Seconds, <b>Max.</b>
400%	0.03 Seconds, <b>Max.</b>
1000%	0.004 Seconds, <b>Max.</b>

### Description

The 316 Series PICO® II Very Fast-Acting Fuse is designed to meet an extensive array of performance characteristics in a space-saving subminiature package while complying with the requirements of CCC.

### Features

- CCC certified Axial Lead Fuse
- Available in ratings of 0.50A, 1.00A, 2.00A, 3.15A and 5.00 amperes
- Fully compatible with Lead-free solder alloys and higher temperature profiles associated with Lead-free assembly
- RoHS compliant

### Applications

Secondary protection for space constrained applications

- Flat-panel Display TV
- LCD monitor
- LCD backlight inverter
- Office machines
- Power supply
- Audio/Video system
- Lighting system
- Medical equipment

### Additional Information



Datasheet




Resources



Samples


### Electrical Characteristics

Ampere Rating (A)	Amp Code	Max Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I <sup>2</sup> t (A <sup>2</sup> sec)	Max Voltage Drop (mV)	Agency Approvals
0.50	.500	125	50A @ 125VAC 50A @ 125VDC	0.280	0.0598	0.202	 X
1.00	001.	125		0.128	0.256	0.186	X
2.00	002.	125		0.0473	0.405	0.158	X
3.15	3.15	125		0.0290	1.190	0.160	X
5.00	005.	125		0.0155	4.140	0.110	X

Notes:

1. Cold resistance measured at less than 10% of rated current at 23°C.
2. Agency Approval Table Key: X=Approved or Certified, P=Pending and Blank=Not Approved
3. Have special electrical characteristic needs? Contact Littelfuse to learn more about application specific options.

**Temperature Derating Curve**



Note:  
1. Derating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

**Soldering Parameters**

**Recommended Process Parameters:**


Wave Parameter	Lead-Free Recommendation
<b>Preheat:</b> (Depends on Flux Activation Temperature)	(Typical Industry Recommendation)
Temperature Minimum:	100° C
Temperature Maximum:	150° C
Preheat Time:	60-180 seconds
<b>Solder Pot Temperature:</b>	260° C Maximum
<b>Solder Dwell Time:</b>	10 Seconds, Maximum

**Recommended Hand-Solder Parameters:**

Solder Iron Temperature: 350° C +/- 5° C  
Heating Time: 5 seconds max.

**Note: These devices are not recommended for IR or Convection Reflow process.**

**Average Time Current Curves**




## Product Characteristics


<b>Materials</b>	Body: Ceramic Leads: Tin-coated Copper Encapsulated: Epoxy-Coated body
<b>Product Marking</b>	Body: Brand Logo, Current Rating Certification mark
<b>Lead Pull Force</b>	MIL-STD-202, Method 211, Test Condition A (will withstand a 7lbs. axial pull test)
<b>Solderability</b>	MIL-STD-202, Method 208

<b>Operating Temperature</b>	-55°C to +125°C with proper de-rating
<b>Shock</b>	MIL-STD-202, Method 213, Test Condition 1 (100G's peak for millisecond)
<b>Vibration</b>	MIL-STD-202F, Method 201A (10-55 Hz); Method 204, Test Condition C
<b>Moisture Resistance</b>	MIL-STD-202, Method 106

## Dimensions



## Part Numbering System



## Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
*T1: 52.4mm (2.062") Axial Lead Tape and Reel or Ammo Pack	EIA 296	5000	NAT1 = 5000 Ammo Pack T1 NRT1 = 5000 Tape & Reel T1

Notes: \* T1 dimension is defined as the length of the component between the two tapes. The full component length is 62.7mm (2.468").