
IXYS

TrenchP™ Power MOSFETs


IXTA120P065T
IXTP120P065T
IXTH120P065T

V_{DSS} = - 65V
I_{D25} = - 120A
$R_{DS(on)}$ ≤ 10mΩ


P-Channel Enhancement Mode
Avalanche Rated




TO-263 AA (IXTA)



TO-220AB (IXTP)



TO-247 (IXTH)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	- 65	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	- 65	V
V_{GSS}	Continuous	±15	V
V_{GSM}	Transient	±25	V
I_{D25}	T_C = 25°C	- 120	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	- 360	A
I_A	T_C = 25°C	- 60	A
E_{AS}	T_C = 25°C	1	J
P_D	T_C = 25°C	298	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6mm (0.062 in.) from Case for 10s	300	°C
T_{SOLD}	Plastic Body for 10s	260	°C
M_d	Mounting Torque (TO-220 & TO-247)	1.13/10	Nm/lb.in.
Weight	TO-263	2.5	g
	TO-220	3.0	g
	TO-247	6.0	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = - 250μA	- 65			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = - 250μA	- 2.0		- 4.0	V
I_{GSS}	V_{GS} = ± 15V, V_{DS} = 0V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			- 10	μA
	T_J = 125°C			- 750	μA
$R_{DS(on)}$	V_{GS} = -10V, $I_D = 0.5 \bullet I_{D25}$, Note 1			10	mΩ

Features

- International Standard Packages
- Avalanche Rated
- Extended FBSOA
- Fast Intrinsic Diode
- Low $R_{DS(ON)}$ and Q_G

Advantages

- Easy to Mount
- Space Savings
- High Power Density

Applications

- High-Side Switching
- Push Pull Amplifiers
- DC Choppers
- Automatic Test Equipment
- Current Regulators
- Battery Charger Applications

© 2013 IXYS CORPORATION, All Rights Reserved


Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = -10V, I_D = 0.5 • I_{D25}, Note 1	45	75		S
C_{iss}	V_{GS} = 0V, V_{DS} = - 25V, f = 1MHz		13.2		nF
C_{oss}			1345		pF
C_{rss}			505		pF
$t_{d(on)}$	**Resistive Switching Times**		31		ns
t_r	V_{GS} = -10V, V_{DS} = - 33V, I_D = - 50A		28		ns
$t_{d(off)}$	R_G = 1Ω (External)		38		ns
t_f			21		ns
$Q_{g(on)}$	V_{GS} = -10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		185		nC
Q_{gs}			55		nC
Q_{gd}			58		nC
R_{thJC}				0.42	°C/W
R_{thCS}	(TO-220)		0.50		°C/W
	(TO-247)		0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			- 120	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			- 480	A
V_{SD}	I_F = - 60A, V_{GS} = 0V, Note 1			-1.3	V
t_{rr}	I_F = - 60A, -di/dt = -100A/μs		53		ns
Q_{RM}	V_R = - 33V, V_{GS} = 0V		77		nC
I_{RM}			- 2.9		A


Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

TO-247 Outline



SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.185	.209	4.7	5.3
A_1	.087	.102	2.2	2.54
A_2	.059	.098	2.2	2.6
b	.040	.055	1.0	1.4
b_1	.065	.084	1.65	2.13
b_2	.113	.123	2.87	3.12
C	.016	.031	.4	.8
D	.819	.845	20.80	21.46
E	.610	.640	15.75	16.26
e	.215 BSC		5.45 BSC	
L	.780	.800	19.81	20.32
L1		.177		4.50
øP	.140	.144	3.55	3.65
Q	.212	.244	5.4	6.2
R	.170	.216	4.32	5.49
S	.242 BSC		6.15 BSC	


TO-220 Outline



Pins: 1 - Gate 2 - Drain
3 - Source 4 - Drain

SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.170	.190	4.32	4.83
b	.025	.040	0.64	1.02
b1	.045	.065	1.15	1.65
c	.014	.022	0.35	0.56
D	.580	.630	14.73	16.00
E	.390	.420	9.91	10.66
e	.100 BSC		2.54 BSC	
F	.045	.055	1.14	1.40
H1	.230	.270	5.85	6.85
J1	.090	.110	2.29	2.79
k	0	.015	0	0.38
L	.500	.550	12.70	13.97
L1	.110	.230	2.79	5.84
øP	.139	.161	3.53	4.08
Q	.100	.125	2.54	3.18

TO-263 Outline



Dim.	Millimeter Min.	Millimeter Max.	Inches Min.	Inches Max.
A	4.06	4.83	.160	.190
b	0.51	0.99	.020	.039
b2	1.14	1.40	.045	.055
c	0.40	0.74	.016	.029
c2	1.14	1.40	.045	.055
D	8.64	9.65	.340	.380
D1	8.00	8.89	.280	.320
E	9.65	10.41	.380	.405
E1	6.22	8.13	.270	.320
e	2.54	BSC	.100	BSC
L	14.61	15.88	.575	.625
L1	2.29	2.79	.090	.110
L2	1.02	1.40	.040	.055
L3	1.27	1.78	.050	.070
L4	0	0.13	0	.005

IXYS Reserves The Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 125ºC




Fig. 4. $R_{DS(on)}$ Normalized to I_D = - 60A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = - 60A Value vs. Drain Current





Fig. 6. Maximum Drain Current vs. Case Temperature



© 2013 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance





Fig. 12. Forward-Bias Safe Operating Area



IXYS Reserves The Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature




Fig. 14. Resistive Turn-on Rise Time vs. Drain Current




Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance




Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature




Fig. 17. Resistive Turn-off Switching Times vs. Drain Current






Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance



© 2013 IXYS CORPORATION, All Rights Reserved

Fig. 19. Maximum Transient Thermal Impedance





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.