
IXYS

PolarHT™ Power MOSFET

IXTK 140N20P

V_{DSS} = 200 V
I_{D25} = 140 A
$R_{DS(on)}$ ≤ 18 mΩ


N-Channel Enhancement Mode
Avalanche Rated



Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25° C to 175° C	200	V
V_{DGR}	T_J = 25° C to 175° C; R_{GS} = 1 MΩ	200	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25° C	140	A
$I_{D(RMS)}$	External lead current limit	75	A
I_{DM}	T_C = 25° C, pulse width limited by T_{JM}	280	A
I_{AR}	T_C = 25° C	60	A
E_{AR}	T_C = 25° C	100	mJ
E_{AS}	T_C = 25° C	4	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤100 A/μs, $V_{DD} \le V_{DSS}$, T_J ≤150° C, R_G = 4 Ω	10	V/ns
P_D	T_C = 25° C	800	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.062 in.) from case for 10 s	300	°C
T_{SOLD}	Plastic body for 10 s	260	°C
M_d	Mounting torque	1.13/10	Nm/lb.in.
Weight		10	g

Symbol	Test Conditions (T_J = 25° C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0 V, I_D = 250 μA	200			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 500μA	2.5		5.0	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0 V			25	μA
	T_J = 150° C			250	μA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 0.5 I_{D25}			18	mΩ
	V_{GS} = 15 V, I_D = 140A		14		mΩ
	Pulse test, t ≤300 μs, duty cycle d ≤ 2 %				

TO-264 (IXTK)



G = Gate D = Drain
S = Source TAB = Drain

Features

- International standard package
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect

Advantages

- Easy to mount
- Space savings
- High power density


© 2006 IXYS All rights reserved

Symbol	Test Conditions (T_J = 25° C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS}= 10 V; I_D = 0.5 I_{D25}, pulse test	50	84		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		7500		pF
C_{oss}			1800		pF
C_{rss}			280		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 60 A R_G = 3.3 Ω (External)		30		ns
t_r			35		ns
$t_{d(off)}$			150		ns
t_f			90		ns
$Q_{g(on)}$	V_{GS}= 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		240		nC
Q_{gs}			50		nC
Q_{gd}			100		nC
R_{thJC}				0.18	° C/W
R_{thCK}			0.15		° C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25° C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0 V			140	A
I_{SM}	Repetitive			280	A
V_{SD}	I_F = I_S, V_{GS} = 0 V, Pulse test, t ≤300 µs, duty cycle d≤ 2 %			1.5	V
t_{rr}	I_F = 25 A, -di/dt = 100 A/µs		180		ns
Q_{RM}	V_R = 100 V, V_{GS} = 0 V		3.5		µC

TO-264 (IXTK) Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or moreof the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478 B2

Fig. 1. Output Characteristics @ 25°C




Fig. 2. Extended Output Characteristics @ 25°C




Fig. 3. Output Characteristics @ 150°C




Fig. 4. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Drain Current





Fig. 6. Drain Current vs. Case Temperature



© 2006 IXYS All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Source Current vs. Source-To-Drain Voltage




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Forward-Bias Safe Operating Area



IXYS reserves the right to change limits, test conditions, and dimensions.

Fig. 13. Maximum Transient Thermal Resistance



© 2006 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.