# Class RK5 Fuses
## FLNR_ID Series

250 V ac • Dual Element • Time Delay • 35–600 A • Indicating



## Description

The FLNR_ID Indicator™ series sets the standard for general purpose indicating fuses. The patented state-of-the-art, solid-state design provides maximum reliability and superior performance characteristics. The dual-element design ensures advanced short-circuit and overload protection. This series offers visual blown fuse indication at a glance. The use of indicator fuses reduces downtime and nuisance opening, increases safety, and saves money by cutting down on lost production time. These fuses are also available in a non-indicating version, see FLNR series.

## Features & Benefits

| FEATURES | BENEFITS |
|---|---|
| **Dual-element design** | Provides advanced short-circuit and overload protection |
| **Current limiting** | Restricts fault current to provide a high degree of circuit protection |
| **Visual Blown Fuse Indication** | Indication window turns black allowing fast and easy identification of blown fuse |

## Applications

- Service entrance switches
- Transformers
- Switchboard mains and feeders
- Motor control central mains and motor branch circuits
- All general purpose circuits

## Specifications

| | |
|---|---|
| **Voltage Rating** | Ac: 250 V<br>Dc: 125 V |
| **Ampere Range** | 35–600 A |
| **Interrupting Ratings** | Ac: 200 kA rms symmetrical; 300 kA rms symmetrical (Littelfuse self-certified)<br>Dc: 20 kA |
| **Applicable Standards** | UL 248-12, Class RK5 |
| **Country of Origin** | Mexico |


©2022 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: 08/01/2022

## Certification & Compliance

| | |
|---|---|
| **UL** | UL Listed (File: E81895) |
| **CSA** | CSA Certified (File: LR29862) |

## Accessories

LFR25 series fuse holder

## Ordering Information

| AMPERE | CATALOG NUMBER | PRODUCT MARKING | PACK QUANTITY | ORDERING NUMBER | UPC | AGENCY APPROVALS | |
|---|---|---|---|---|---|---|---|
| | | | | | | UL | CSA |
| 35 | FLNR035ID | FLNR 35ID | 10 | FLNR035.TXID | 07945802380 | • | • |
| 40 | FLNR040ID | FLNR 40ID | 10 | FLNR040.TXID | 07945802381 | • | • |
| 45 | FLNR045ID | FLNR 45ID | 10 | FLNR045.TXID | 07945802382 | • | • |
| 50 | FLNR050ID | FLNR 50ID | 10 | FLNR050.TXID | 07945802383 | • | • |
| 60 | FLNR060ID | FLNR 60ID | 10 | FLNR060.TXID | 07945802384 | • | • |
| 70 | FLNR070ID | FLNR 70ID | 5 | FLNR070.VXID | 07945802385 | • | • |
| 80 | FLNR080ID | FLNR 80ID | 5 | FLNR080.VXID | 07945802386 | • | • |
| 90 | FLNR090ID | FLNR 90ID | 5 | FLNR090.VXID | 07945802387 | • | • |
| 100 | FLNR100ID | FLNR 100ID | 5 | FLNR100.VXID | 07945802388 | • | • |
| 110 | FLNR110ID | FLNR 110ID | 1 | FLNR110.XXID | 07945802389 | • | • |
| 125 | FLNR125ID | FLNR 125ID | 1 | FLNR125.XXID | 07945802390 | • | • |
| 150 | FLNR150ID | FLNR 150ID | 1 | FLNR150.XXID | 07945802391 | • | • |
| 175 | FLNR175ID | FLNR 175ID | 1 | FLNR175.XXID | 07945802392 | • | • |
| 200 | FLNR200ID | FLNR 200ID | 1 | FLNR200.XXID | 07945802393 | • | • |
| 225 | FLNR225ID | FLNR 225ID | 1 | FLNR225.XXID | 07945802394 | • | • |
| 250 | FLNR250ID | FLNR 250ID | 1 | FLNR250.XXID | 07945802395 | • | • |
| 300 | FLNR300ID | FLNR 300ID | 1 | FLNR300.XXID | 07945802396 | • | • |
| 350 | FLNR350ID | FLNR 350ID | 1 | FLNR350.XXID | 07945802397 | • | • |
| 400 | FLNR400ID | FLNR 400ID | 1 | FLNR400.XXID | 07945802398 | • | • |
| 450 | FLNR450ID | FLNR 450ID | 1 | FLNR450.XXID | 07945802399 | • | • |
| 500 | FLNR500ID | FLNR 500ID | 1 | FLNR500.XXID | 07945802400 | • | • |
| 600 | FLNR600ID | FLNR 600ID | 1 | FLNR600.XXID | 07945802401 | • | • |


©2022 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: 08/01/2022

## Dimensions





FIG. 1





FIG. 2

| AMPS | FIGURE NUMBER | DIMENSIONS INCHES (MM) | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| | | A | B | C | D | E | F | G | H | J | K |
| 35–60 | 1 | 3.00 (76.2) | 0.76 (19.2) | 0.63 (15.9) | 0.81 (20.7) | 0.09 (2.4) | 0.19 (4.7) | 0.63 (15.9) | - | - | - |
| 70–100 | 2 | 5.88 (149.2) | 1 (25.1) | 1.06 (27.0) | 1.03 (26.2) | 0.13 (3.2) | 0.75 (19.1) | - | 0.25 (6.4) | 0.28 (7.1) | 0.50 (12.7) |
| 110–200 | 2 | 7.13 (181) | 1.50 (37.9) | 1.47 (37.3) | 1.54 (39.0) | 0.19 (4.8) | 1.13 (28.6) | - | 0.44 (11.1) | 0.28 (7.1) | 0.69 (17.5) |
| 225–400 | 2 | 8.63 (219.1) | 2 (50.4) | 1.94 (49.2) | 2.00 (50.8) | 0.25 (6.4) | 1.63 (41.3) | - | 0.63 (15.9) | 0.41 (10.3) | 0.94 (23.8) |
| 450–600 | 2 | 10.38 (263.5) | 2.50 (63.1) | 2.38 (60.3) | 2.54 (64.6) | 0.25 (6.4) | 2 (50.8) | - | 0.75 (19.1) | 0.53 (13.5) | 1.13 (28.6) |

## Current-Limiting Effects of FLNR_ID Fuses

| SHORT CIRCUIT CURRENT* | APPARENT RMS SYMMETRICAL CURRENT FOR VARIOUS FUSE RATINGS | | | | | |
|---|---|---|---|---|---|---|
| | 30 A | 60 A | 100 A | 200 A | 400 A | 600 A |
| 5,000 | 1,400 | 2,100 | 3,100 | 5,000 | 5,000 | 5,000 |
| 10,000 | 1,550 | 2,500 | 3,900 | 6,500 | 9,500 | 10,000 |
| 15,000 | 2,000 | 3,150 | 4,400 | 7,250 | 10,500 | 14,000 |
| 20,000 | 2,250 | 3,400 | 5,000 | 8,250 | 12,000 | 16,000 |
| 25,000 | 2,400 | 3,750 | 5,250 | 9,000 | 12,500 | 16,500 |
| 30,000 | 2,550 | 4,100 | 5,600 | 9,500 | 13,500 | 18,000 |
| 35,000 | 2,650 | 4,300 | 5,800 | 9,750 | 14,000 | 19,000 |
| 40,000 | 2,800 | 4,400 | 6,250 | 10,250 | 15,000 | 20,000 |
| 50,000 | 3,000 | 5,000 | 6,500 | 10,500 | 16,000 | 21,000 |
| 60,000 | 3,200 | 5,250 | 7,000 | 11,500 | 17,000 | 23,000 |
| 80,000 | 3,400 | 5,750 | 7,500 | 12,500 | 19,000 | 25,500 |
| 100,000 | 3,850 | 6,000 | 8,000 | 13,500 | 21,000 | 27,500 |
| 150,000 | 4,100 | 7,000 | 9,000 | 15,200 | 24,000 | 31,500 |
| 200,000 | 4,300 | 7,500 | 9,750 | 16,500 | 26,000 | 34,000 |

*Prospective RMS Symmetrical Amperes Short-Circuit Current

*Note: Data Derived from Peak Let-Thru Curves*


**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at **www.littelfuse.com/product-disclaimer.**




©2022 Littelfuse, Inc.
Specifications are subject to change without notice.


Revised: 08/01/2022