


### 451/453 Series Fuse



#### Agency Approvals

| Agency | Agency File Number  | Ampere Range  |
|--------|---|---|
|        | E10480  | 6.3A - 20A  |
|        | 29862   | 0.062A - 15A  |
|        | J50446731   | 1A, 1.25A, 2A, 2.5A, 3.15A, 4A, 5A, 7A, 8A, 10A, 12A, 20A |
|        | NBK030205-E10480A<br>NBK030205-E10480B<br>NBK101105-E184655 | 1A-1.6A<br>2A-5A<br>6.3A - 10A                            |
|        | E10480  | 0.062A - 5A   |
|        | NA  | 1A, 1.25A, 2A, 2.5A, 3.15A, 4A, 5A, 7A, 8A, 10A, 12A, 20A |

#### Electrical Characteristics for Series

| % of Ampere Rating | Ampere Rating | Opening Time     |
|--------------------|---------------|------------------|
| 100%               | 0.062 – 20    | 4 hours, Minimum |
| 200%               | 0.062 – 10    | 5 sec., Maximum  |
|                    | 12 – 20       | 20 sec., Maximum |

#### Additional Information



Datasheet  
451 Series



Resources  
451 Series



Samples  
451 Series



Datasheet  
453 Series



Resources  
453 Series



Samples  
453 Series

#### Description

The Nano<sup>2</sup> SMF Fuse is a very small, Wire-in-Air (WIA) square shape surface mount fuse that was designed for secondary side circuit over-current protection applications. These fuses are designed for PCB using surface mount technology.







#### Features

- Very fast-acting
- Small size
- Wide range of current rating available (0.062A to 20A)
- Wide operating temperature range
- RoHS compliant and Halogen Free
- UL Listed and Recognized to UL/CSA/NMX UL 248-1 and UL/CSA/NMX UL 248-14 (see Agency Approvals)
- Conforms to DENAN's Appendix 3
- Conforms to EN 60127-1 and EN 60127-7

#### Applications


- Notebook PC
- LCD/PDPTV
- LCD monitor
- LCD/PDP panel
- LCD backlight inverter
- Portable DVD player
- Power supply
- Networking
- PC server
- Cooling fan system
- Storage system
- Telecom system
- Wireless basestation
- White goods
- Game console
- Office Automation equipment
- Battery charging circuit protection
- Industrial equipment

### Electrical Specifications by Item

| Ampere Rating (A) | Amp Code | Max Voltage Rating (V) | Interrupting Rating   | Nominal Cold Resistance (Ohms) | Nominal Melting I²t (A²sec) | Agency Approvals  |   |   |   |   |   |
|-------------------|----------|------------------------|---|--------------------------------|-----------------------------|---|---|---|---|---|---|
|                   |          |                        |   |                                |                             |  |  |  |  |  |  |
| .062              | .062     | 125                    | 50A @125VAC/VDC<br>300A @32VDC<br>PSE: 100A @100VAC                   | 5.5000                         | 0.00019                     | -   | x   | -   | x   | -   | -   |
| .080              | .080     | 125                    |   | 4.0500                         | 0.00033                     | -   | x   | -   | x   | -   | -   |
| .100              | .100     | 125                    |   | 3.1000                         | 0.00138                     | -   | x   | -   | x   | -   | -   |
| .125              | .125     | 125                    |   | 1.7000                         | 0.00286                     | -   | x   | -   | x   | -   | -   |
| .160              | .160     | 125                    |   | 1.2157                         | 0.0048                      | -   | x   | -   | x   | -   | -   |
| .200              | .200     | 125                    |   | 0.8372                         | 0.0089                      | -   | x   | -   | x   | -   | -   |
| .250              | .250     | 125                    |   | 0.5765                         | 0.0158                      | -   | x   | -   | x   | -   | -   |
| .315              | .315     | 125                    |   | 0.3918                         | 0.0311                      | -   | x   | -   | x   | -   | -   |
| .375              | .375     | 125                    |   | 0.4541                         | 0.0442                      | -   | x   | -   | x   | -   | -   |
| .400              | .400     | 125                    |   | 0.4233                         | 0.0551                      | -   | x   | -   | x   | -   | -   |
| .500              | .500     | 125                    |   | 0.3046                         | 0.0824                      | -   | x   | -   | x   | -   | -   |
| .630              | .630     | 125                    |   | 0.2022                         | 0.1381                      | -   | x   | -   | x   | -   | -   |
| .750              | .750     | 125                    |   | 0.1444                         | 0.2143                      | -   | x   | -   | x   | -   | -   |
| .800              | .800     | 125                    |   | 0.1355                         | 0.2654                      | -   | x   | -   | x   | -   | -   |
| 1.00              | 001.     | 125                    |   | 0.0780                         | 0.6029                      | -   | x   | x   | x   | x   | x   |
| 1.25              | 1.25     | 125                    |   | 0.0780                         | 0.664                       | -   | x   | x   | x   | x   | x   |
| 1.50              | 01.5     | 125                    |   | 0.0630                         | 0.853                       | -   | x   | x   | x   | -   | -   |
| 1.60              | 01.6     | 125                    |   | 0.0580                         | 1.060                       | -   | x   | x   | x   | -   | -   |
| 2.00              | 002.     | 125                    | 50A @125VAC/VDC<br>10,000A @75VDC<br>300A @32VDC<br>PSE: 100A @100VAC | 0.0367                         | 0.530                       | -   | x   | x   | x   | x   | x   |
| 2.50              | 02.5     | 125                    |   | 0.0286                         | 1.029                       | -   | x   | x   | x   | x   | x   |
| 3.00              | 003.     | 125                    |   | 0.0227                         | 1.650                       | -   | x   | x   | x   | -   | -   |
| 3.15              | 3.15     | 125                    |   | 0.0215                         | 1.920                       | -   | x   | x   | x   | x   | x   |
| 3.50              | 03.5     | 125                    |   | 0.0200                         | 2.469                       | -   | x   | x   | x   | -   | -   |
| 4.00              | 004.     | 125                    |   | 0.0160                         | 3.152                       | -   | x   | x   | x   | x   | x   |
| 5.00              | 005.     | 125                    |   | 0.0125                         | 5.566                       | -   | x   | x   | x   | x   | x   |
| 6.30              | 06.3     | 125                    | 50A @125VAC/VDC<br>400A @32VDC<br>PSE: 100A @100VAC                   | 0.0096                         | 9.170                       | x   | x   | x   | -   | -   | -   |
| 7.00              | 007.     | 125                    |   | 0.0090                         | 10.32                       | x   | x   | x   | -   | x   | x   |
| 8.00              | 008.     | 125                    |   | 0.0077                         | 20.23                       | x   | x   | x   | -   | x   | x   |
| 10.0              | 010.     | 125                    | 35A @125 VAC/<br>50A @125 VDC<br>400A @32 VDC<br>PSE: 100A @100VAC    | 0.0056                         | 26.46                       | x   | x   | x   | -   | x   | x   |
| 12.0              | 012.     | 65                     | 150A @65VDC<br>100A @65VAC<br>400A @32VDC                             | 0.0049                         | 47.97                       | x   | x   | -   | -   | x   | x   |
| 15.0              | 015.     | 65                     |   | 0.0037                         | 97.82                       | x   | x   | -   | -   | -   | -   |
| 20.0              | 020.     | 65                     |   | 0.00244                        | 154                         | x   | -   | -   | -   | x   | x   |


**Notes:**  
 - I²t calculated at 8ms.  
 - Resistance is measured at 10% of rated current, 25°C

**Temperature Re-rating Curve**



**Note:**  
1. Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation.


**Average Time Current Curves**



**Soldering Parameters**

|  |                                    |                         |
|--|------------------------------------|-------------------------|
| <b>Reflow Condition</b>  |                                    | Pb – Free assembly      |
| <b>Pre Heat</b>  | - Temperature Min ( $T_{s(min)}$ ) | 150°C                   |
|  | - Temperature Max ( $T_{s(max)}$ ) | 200°C                   |
|  | - Time (Min to Max) ( $t_s$ )      | 60 – 180 secs           |
| <b>Average ramp up rate (Liquidus Temp (<math>T_L</math>) to peak)</b> |                                    | 5°C/second max.         |
| <b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>      |                                    | 5°C/second max.         |
| <b>Reflow</b>  | - Temperature ( $T_L$ ) (Liquidus) | 217°C                   |
|  | - Temperature ( $t_L$ )            | 60 – 150 seconds        |
| <b>Peak Temperature (<math>T_p</math>)</b>                             |                                    | 260 <sup>+0/-5</sup> °C |
| <b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>   |                                    | 20 – 40 seconds         |
| <b>Ramp-down Rate</b>  |                                    | 5°C/second max.         |
| <b>Time 25°C to peak Temperature (<math>T_p</math>)</b>                |                                    | 8 minutes max.          |
| <b>Do not exceed</b>   |                                    | 260°C                   |

**Wave Soldering Parameters** 260°C Peak Temperature, 10 seconds max.




### Product Characteristics


|  |   |
|--|---|
| <b>Materials</b>                             | <b>Body:</b> Ceramic<br><b>Terminations:</b><br>Gold-Plated Caps / Sn-dipped Silver Plated Caps (451 RoHS/HF series)<br>Silver-plated Caps (451MR RoHS ratings below 375mA and 453 RoHS Series) |
| <b>Product Marking</b>                       | Brand, Ampere Rating  |
| <b>Operating Temperature</b>                 | -55°C to 125°C  |
| <b>Moisture Sensitivity Level</b>            | Level 1, J-STD-020  |
| <b>Solderability</b>                         | MIL-STD-202, Method 208   |
| <b>Insulation Resistance (after Opening)</b> | MIL-STD-202, Method 302, Test Condition A (10,000 ohms minimum)   |

|                                     |   |
|-------------------------------------|---|
| <b>Thermal Shock</b>                | MIL-STD-202, Method 107, Test Condition B, 5 cycles, -65°C / +125°C, 15 minutes @ each extreme                              |
| <b>Mechanical Shock</b>             | MIL-STD-202, Method 213, Test I: Deenergized. 100G's pk amplitude, sawtooth wave 6ms duration, 3 cycles XYZ+xyz = 18 shocks |
| <b>Vibration</b>                    | MIL-STD-202, Method 201: 0.03" amplitude, 10-55 Hz in 1 min. 2hrs each XYZ=6hrs   |
| <b>Moisture Resistance</b>          | MIL-STD-202, Method 106, 10 cycles  |
| <b>Salt Spray</b>                   | MIL-STD-202, Method 101, Test Condition B (48hrs)   |
| <b>Resistance to Soldering Heat</b> | MIL-STD-202, Method 210, Test condition B (10 sec at 260°C)   |

### Dimensions



### Part Numbering System



**NOTE:** "L" suffix applies to 451 series only  
 - 453 series is available only as RoHS compliant version and does not require "L" suffix. Please do not include "L" suffix within 453 series ordering instructions.

### Packaging

| Packaging Option   | Packaging Specification        | Quantity | Quantity & Packaging Code |
|--------------------|--------------------------------|----------|---------------------------|
| 12mm Tape and Reel | EIA RS-481-2 (IEC 286, part 3) | 5000     | NR                        |
| 12mm Tape and Reel | EIA RS-481-2 (IEC 286, part 3) | 1000     | MR                        |

**Disclaimer Notice** - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).