IXYS


Preliminary Technical Information

GigaMOS™ Power MOSFET


IXFK160N30T
IXFX160N30T

V_{DSS} = 300V
I_{D25} = 160A
$R_{DS(on)}$ ≤ 19mΩ
t_{rr} ≤ 200ns


N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Diode



TO-264 (IXFK)



PLUS247 (IXFX)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	300	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	300	V
V_{GSS}	Continuous	± 20	V
V_{GSM}	Transient	± 30	V
I_{D25}	T_C = 25°C	160	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	440	A
I_A	T_C = 25°C	80	A
E_{AS}	T_C = 25°C	5	J
dV/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$	20	V/ns
P_D	T_C = 25°C	1390	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	Plastic Body for 10s	260	°C
M_d	Mounting Torque (TO-264)	1.13/10	Nm/lb.in
F_C	Mounting Force (PLUS247)	20..120 /4.5..27	N/lb
Weight	TO-264	10	g
	PLUS247	6	g

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 3mA	300			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 8mA	3.0		5.0	V
I_{GSS}	V_{GS} = ± 20V, V_{DS} = 0V			± 200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			50	μA
	T_J = 125°C			3	mA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 80A, Note 1			19	mΩ

Features

- International Standard Packages
- High Current Handling Capability
- Fast Intrinsic Diode
- Avalanche Rated
- Low $R_{DS(on)}$

Advantages

- Easy to Mount
- Space Savings
- High Power Density

Applications

- DC-DC Converters
- Battery Chargers
- Switched-Mode and Resonant-Mode Power Supplies
- DC Choppers
- AC Motor Drives
- Uninterruptible Power Supplies
- High Speed Power Switching Applications

© 2009 IXYS CORPORATION, All rights reserved

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10V, I_D = 60A, Note 1	90	150		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		24.5		nF
C_{oss}			1825		pF
C_{rss}			45		pF
R_{Gi}	Gate Input Resistance		1.1		Ω
$t_{d(on)}$	**Resistive Switching Times**		34		ns
t_r	V_{GS} = 15V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		68		ns
$t_{d(off)}$	R_G = 1Ω (External)		90		ns
t_f			23		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		376		nC
Q_{gs}			140		nC
Q_{gd}			56		nC
R_{thJC}				0.09	°C/W
R_{thCS}			0.15		°C/W

Source-Drain Diode


Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			160	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			640	A
V_{SD}	I_F = 60A, V_{GS} = 0V, Note 1			1.4	V
t_{rr}	I_F = 80A, -di/dt = 100A/μs			200	ns
Q_{RM}	V_R = 75V, V_{GS} = 0V		1.09		μC
I_{RM}			13		A

Note 1: Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.


TO-264 AA Outline



Terminals: 1 - Gate
2 - Drain
3 - Source
4 - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

PLUS 247™ Outline



Terminals: 1 - Gate
2 - Drain
3 - Source

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.83	5.21	.190	.205
A_1	2.29	2.54	.090	.100
A_2	1.91	2.16	.075	.085
b	1.14	1.40	.045	.055
b_1	1.91	2.13	.075	.084
b_2	2.92	3.12	.115	.123
C	0.61	0.80	.024	.031
D	20.80	21.34	.819	.840
E	15.75	16.13	.620	.635
e	5.45 BSC		.215 BSC	
L	19.81	20.32	.780	.800
L1	3.81	4.32	.150	.170
Q	5.59	6.20	.220	0.244
R	4.32	4.83	.170	.190

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 125ºC




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 80A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 80A Value vs. Drain Current





Fig. 6. Maximum Drain Current vs. Case Temperature



© 2009 IXYS CORPORATION, All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance





Fig. 12. Forward-Bias Safe Operating Area



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature




Fig. 14. Resistive Turn-on Rise Time vs. Drain Current




Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance




Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature




Fig. 17. Resistive Turn-off Switching Times vs. Drain Current






Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance



© 2009 IXYS CORPORATION, All rights reserved

Fig. 19. Maximum Transient Thermal Impedance





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.