
IXYS

PolarHT™ Power MOSFET

IXTQ 64N25P
IXTT 64N25P

V_{DSS} = 250 V
I_{D25} = 64 A
$R_{DS(on)}$ ≤ 49 mΩ


N-Channel Enhancement Mode
Avalanche Rated




Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25° C to 150° C	250	V
V_{DGR}	T_J = 25° C to 150° C; R_{GS} = 1 MΩ	250	V
V_{GSS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25° C	64	A
I_{DM}	T_C = 25° C, pulse width limited by T_{JM}	160	A
I_{AR}	T_C = 25° C	60	A
E_{AR}	T_C = 25° C	40	mJ
E_{AS}	T_C = 25° C	1.0	J
dv/dt	$I_S \le I_{DM}$, di/dt ≤100 A/μs, $V_{DD} \le V_{DSS}$, T_J ≤150° C, R_G = 4 Ω	10	V/ns
P_D	T_C = 25° C	400	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.062 in.) from case for 10 s	300	°C
T_{SOLD}	Plastic body for 10 s	260	°C
M_d	Mounting torque (TO-3P)	1.13/10	Nm/lb.in.
Weight	TO-3P	5.5	g
	TO-268	5.0	g

Symbol	Test Conditions (T_J = 25° C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0 V, I_D = 250 μA	250			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 250μA	2.5		5.0	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$			25	μA
	V_{GS} = 0 V, T_J = 125° C			250	μA
$R_{DS(on)}$	V_{GS} = 10 V, $I_D = 0.5\ I_{D25}$ Pulse test, t ≤300 μs, duty cycle d ≤ 2 %			49	mΩ

TO-3P (IXTQ)



TO-268 (IXTT)



G = Gate D = Drain
S = Source TAB = Drain

Features

- International standard packages
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect

Advantages

- Easy to mount
- Space savings
- High power density


© 2006 IXYS All rights reserved

Symbol	Test Conditions	Characteristic Values (T_J = 25° C, unless otherwise specified) Min.	Typ.	Max.	
g_{fs}	V_{DS}= 10 V; I_D = 0.5 I_{D25}, pulse test	20	30		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		3450		pF
C_{oss}			640		pF
C_{rss}			155		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = I_{D25} R_G = 4 Ω (External)		21		ns
t_r			23		ns
$t_{d(off)}$			60		ns
t_f			20		ns
$Q_{g(on)}$	V_{GS}= 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		105		nC
Q_{gs}			24		nC
Q_{gd}			53		nC
R_{thJC}				0.31	°C/W
R_{thCS}	(TO-3P)		0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions	Characteristic Values (T_J = 25° C, unless otherwise specified) Min.	Typ.	Max.	
I_S	V_{GS} = 0 V			64	A
I_{SM}	Repetitive			160	A
V_{SD}	I_F = I_S, V_{GS} = 0 V, Pulse test, t ≤300 µs, duty cycle d≤ 2 %			1.5	V
t_{rr}	I_F = 25 A, -di/dt = 100 A/µs		200		ns
Q_{RM}	V_R = 100 V, V_{GS} = 0 V		3.0		µC

TO-3P (IXTQ) Outline




1 – GATE
2 – DRAIN (COLLECTOR)
3 – SOURCE (EMITTER)
4 – DRAIN (COLLECTOR)

SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.185	.193	4.70	4.90
A1	.051	.059	1.30	1.50
A2	.057	.065	1.45	1.65
b	.035	.045	0.90	1.15
b2	.075	.087	1.90	2.20
b4	.114	.126	2.90	3.20
c	.022	.031	0.55	0.80
D	.780	.791	19.80	20.10
D1	.665	.677	16.90	17.20
E	.610	.622	15.50	15.80
E1	.531	.539	13.50	13.70
e	.215 BSC		5.45 BSC	
L	.779	.795	19.80	20.20
L1	.134	.142	3.40	3.60
øP	.126	.134	3.20	3.40
øP1	.272	.280	6.90	7.10
S	.193	.201	4.90	5.10

All metal area are tin plated.

TO-268 (IXTT) Outline



SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or moreof the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478 B2

Fig. 1. Output Characteristics @ 25ºC




Fig. 2. Extended Output Characteristics @ 25ºC




Fig. 3. Output Characteristics @ 125ºC




Fig. 4. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to 0.5 I_{D25} Value vs. I_D





Fig. 6. Drain Current vs. Case Temperature



© 2006 IXYS All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Source Current vs. Source-To-Drain Voltage




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Forward-Bias Safe Operating Area



IXYS reserves the right to change limits, test conditions, and dimensions.

Fig. 13. Maximum Transient Thermal Resistance



© 2006 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.