
Thyristor

V_{RRM}	=	1600 V
I_{TAV}	=	30 A
V_T	=	1.28 V

AC Controlling
1~ full-controlled


Part number

MMO62-16io6



Backside: isolated

E72873



Features / Advantages:

- Thyristor for line frequency
- Planar passivated chip
- Long-term stability

Applications:

- Line rectifying 50/60 Hz
- Softstart AC motor control
- DC Motor control
- Power converter
- AC power control
- Lighting and temperature control

Package: SOT-227B (minibloc)

- Isolation Voltage: 3000 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate: Copper internally DCB isolated
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2020 IXYS all rights reserved


Thyristor

Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
$V_{RSM/DSM}$	*max. non-repetitive reverse/forward blocking voltage*		T_{VJ} = 25°C			1700	V
$V_{RRM/DRM}$	*max. repetitive reverse/forward blocking voltage*		T_{VJ} = 25°C			1600	V
$I_{R/D}$	*reverse current, drain current*	$V_{R/D}$ = 1600 V	T_{VJ} = 25°C			100	µA
		$V_{R/D}$ = 1600 V	T_{VJ} = 125°C			4	mA
V_T	*forward voltage drop*	I_T = 30 A	T_{VJ} = 25°C			1.29	V
		I_T = 60 A				1.60	V
		I_T = 30 A	T_{VJ} = 125°C			1.28	V
		I_T = 60 A				1.68	V
I_{TAV}	*average forward current*	T_C = 95°C	T_{VJ} = 150°C			30	A
I_{RMS}	*RMS forward current per phase*	180° sine				66	A
V_{T0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 150°C			0.87	V
r_T	*slope resistance* }					13.6	mΩ
R_{thJC}	*thermal resistance junction to case*					0.9	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.2		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			140	W
I_{TSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			400	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			430	A
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			340	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			365	A
I^2t	*value for fusing*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			800	A²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			770	A²s
		t = 10 ms; (50 Hz), sine	T_{VJ} = 150°C			580	A²s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			555	A²s
C_J	*junction capacitance*	V_R = 400 V f = 1 MHz	T_{VJ} = 25°C		22		pF
P_{GM}	*max. gate power dissipation*	t_P = 30 µs	T_C = 150°C			10	W
		t_P = 300 µs				5	W
P_{GAV}	*average gate power dissipation*					0.5	W
$(di/dt)_{cr}$	*critical rate of rise of current*	T_{VJ} = 150°C; f = 50 Hz	repetitive, I_T = 90 A			100	A/µs
		t_P = 200 µs; di_G/dt = 0.3 A/µs;					
		I_G = 0.3 A; V = ⅔ V_{DRM}	non-repet., I_T = 30 A			500	A/µs
$(dv/dt)_{cr}$	*critical rate of rise of voltage*	V = ⅔ V_{DRM}	T_{VJ} = 150°C			1000	V/µs
		R_{GK} = ∞; method 1 (linear voltage rise)					
V_{GT}	*gate trigger voltage*	V_D = 6 V	T_{VJ} = 25°C			1.5	V
			T_{VJ} = -40°C			1.6	V
I_{GT}	*gate trigger current*	V_D = 6 V	T_{VJ} = 25°C			100	mA
			T_{VJ} = -40°C			150	mA
V_{GD}	*gate non-trigger voltage*	V_D = ⅔ V_{DRM}	T_{VJ} = 150°C			0.2	V
I_{GD}	*gate non-trigger current*					5	mA
I_L	*latching current*	t_p = 10 µs	T_{VJ} = 25°C			150	mA
		I_G = 0.3 A; di_G/dt = 0.3 A/µs					
I_H	*holding current*	V_D = 6 V R_{GK} = ∞	T_{VJ} = 25°C			100	mA
t_{gd}	*gate controlled delay time*	V_D = ½ V_{DRM}	T_{VJ} = 25°C			2	µs
		I_G = 0.3 A; di_G/dt = 0.3 A/µs					
t_q	*turn-off time*	V_R = 100 V; I_T = 20A; V = ⅔ V_{DRM}	T_{VJ} = 125 °C		150		µs
		di/dt = 10 A/µs dv/dt = 15 V/µs t_p = 200 µs					

© 2020 IXYS all rights reserved

Package SOT-227B (minibloc)					Ratings			
Symbol	**Definition**	**Conditions**			**min.**	**typ.**	**max.**	**Unit**
I_{RMS}	*RMS current*	per terminal					150	A
T_{VJ}	*virtual junction temperature*				-40		150	°C
T_{op}	*operation temperature*				-40		125	°C
T_{stg}	*storage temperature*				-40		150	°C
Weight						30		g
M_D	*mounting torque*				1.1		1.5	Nm
M_T	*terminal torque*				1.1		1.5	Nm
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	10.5	3.2			mm
$d_{Spb/Apb}$			*terminal to backside*	8.6	6.8			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA		3000			V
		t = 1 minute			2500			V


Product Marking



Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MMO62-16io6	MMO62-16io6	Tube	10	459437

Equivalent Circuits for Simulation

** on die level* T_{VJ} = 150°C




Thyristor


$V_{0\,max}$	*threshold voltage*	0.87	V
$R_{0\,max}$	*slope resistance **	11.8	mΩ

© 2020 IXYS all rights reserved

Outlines SOT-227B (minibloc)



Dim.	Millimeter		Inches	
	min	max	min	max
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	37.80	38.23	1.488	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.74	0.84	0.029	0.033
M	12.50	13.10	0.492	0.516
N	25.15	25.42	0.990	1.001
O	1.95	2.13	0.077	0.084
P	4.95	6.20	0.195	0.244
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.167
S	4.55	4.85	0.179	0.191
T	24.59	25.25	0.968	0.994
U	-0.05	0.10	-0.002	0.004
V	3.20	5.50	0.126	0.217
W	19.81	21.08	0.780	0.830
Z	2.50	2.70	0.098	0.106



© 2020 IXYS all rights reserved

Thyristor




Fig. 1 Forward characteristics




Fig. 2 Surge overload current




Fig. 3 I^2t versus time (1-10 ms)




Fig. 4 Gate trigger characteristics




Fig. 5 Gate controlled delay time




Fig. 6 Max. forward current at case temperature




Fig. 7a Power dissipation versus direct output current
Fig. 7b and ambient temperature




Fig. 8 Transient thermal impedance junction to case

© 2020 IXYS all rights reserved