
MDSR-10 10.2mm Sub-miniature Reed Switch




Agency Approvals

Agency	Agency File Number	Ampere-Turns Range
c UL us	E47258 E471070	10-25 AT

Note: Contact Littelfuse for specific agency approval ratings.

Dimensions

Dimensions in mm (inch)



Description

The MDSR-10 Reed Switch is a sub-miniature, normally open switch with a 10.16mm long x 1.80mm diameter (0.400" x 0.071") glass envelope, capable of switching 200Vdc at 10W. It has high insulation resistance of 10^{12} ohms minimum and low contact resistance of less than 120 milli-ohms. This reed switch is also available in a surface mount version, that is, MDSM-10.

Features

- Sub-miniature normally open switch
- Capable of switching 200Vdc or 0.5A at up to 10W
- 10^{12} Ohms insulation resistance
- Available sensitivity range 10-25 AT

Benefits

- Hermetically sealed switch contacts are not affected by and have no effect on their external environment
- Low space requirement
- Zero operating power required for contact
- Excellent for switching microcontroller logic level loads

Applications

- Reed Relays (particularly suited to ATE type applications)
- Security Systems
- Limit Switching
- Office Equipments

Switch Type

Contact Form	A (SPST-NO)
Materials	Body: Glass Leads: Tin-plated Ni-Fe wire

Note: SPST-NO = Single-pole, single-throw, normally open

Electrical Ratings

Contact Rating [1]		W/VA - max.	10
Voltage [3]	Switching [2]	Vdc - max. Vac - max.	200 140
	Breakdown [4]	Vdc - min.	250
Current [3]	Switching [2]	Adc - max. Aac - max.	0.50 0.35
	Carry	Adc - max.	1.00
Resistance	Contact, Initial Insulation	Ω - max. Ω - min.	0.120 10^{12}
Capacitance	Contact	pF - typ.	0.2
Temperature	Operating Storage [5]	°C °C	-40 to +125 -65 to +125

Notes:

1. Contact rating - Product of the switching voltage and current should never exceed the wattage rating. Contact Littelfuse for additional load/life information.
2. When switching inductive and/or capacitive loads, the effects of transient voltages and/or currents should be considered. Refer to Application Notes AN108A and AN107 for details.
3. Electrical Load Life Expectancy - Contact Littelfuse with voltage, current values along with type of load.
4. Breakdown Voltage - per MIL-STD-202, Method 301.
5. Storage Temperature - Long time exposure at elevated temperature may degrade solderability of the leads.

© 2020 Littelfuse

Specifications are subject to change without notice.


MDSR-10 10.2mm Sub-miniature Reed Switch

Product Characteristics

Operating Characteristics		
Operate Time [1]		0.5ms - max.
Release Time [1]		0.1ms - max.
Shock [2]	11ms 1/2 sine wave	100G - max.
Vibration [2]	50-2000 Hertz	30G - max.
Resonant Frequency		8.5kHz - typ.
Magnetic Characteristics		
Pull-In Range [3]	Ampere Turns	10-25
Rating Sensitivity [4]	Ampere Turns	15
Test Coil		L4989

Notes:
1. Operate (including bounce)/Release Time - per EIA/NARM RS-421-A,diode suppressed coil (Coil II).
2. Shock and Vibration - per EIA/NARM RS-421-A and MIL-STD-202.
3. Pull-In Range - Contact Littelfuse for narrower AT ranges available.
4. Rating Sensitivity - The value at which contact ratings and operating characteristics are determined. Derating may be required below this value.
5. Custom modifications of forming and/or cutting of reed switches are available. Please contact Littelfuse.

Drop-Out vs. Pull-In Chart



Note: Chart represents the range of Drop-Out, min to max for a given Pull-In value.

Part Numbering System

MDSR-10-10-15

Series

AT Range
10-25 AT
10-15 AT
15-20 AT
20-25 AT

Example:
10-15 AT product is
MDSR-10-10-15

Note: These AT values are the before-modification values of the bare reed switch.

Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width
Bulk	Bulk	1000	N/A	N/A

© 2020 Littelfuse Revised: BO.12/08/20
Specifications are subject to change without notice.