

COOLMOS® * Power MOSFET

I_{D25} = 35 A
V_{DSS} = 600 V
$R_{DS(on)\ max}$ = 0.1 Ω

N-Channel Enhancement Mode
Low R_{DSon}, High V_{DSS} MOSFET
Ultra low gate charge



TO-247 AD



MOSFET				
Symbol	**Conditions**		**Maximum Ratings**	
V_{DSS}	T_{VJ} = 25°C		600	V
V_{GS}			± 20	V
I_{D25}	T_C = 25°C		35	A
I_{D90}	T_C = 90°C		25	A
E_{AS}	single pulse	I_D = 11 A; T_C = 25°C	800	mJ
E_{AR}	repetitive		1.2	mJ
dV/dt	MOSFET dV/dt ruggedness V_{DS} = 0...480 V		50	V/ns

Symbol	**Conditions**		**Characteristic Values** (T_{VJ} = 25°C, unless otherwise specified)			
			min.	**typ.**	**max.**	
R_{DSon}	V_{GS} = 10 V; I_D = 18 A			90	100	mΩ
$V_{GS(th)}$	V_{DS} = V_{GS}; I_D = 1.2 mA		2.5	3	3.5	V
I_{DSS}	V_{DS} = 600 V; V_{GS} = 0 V	T_{VJ} = 25°C			5	µA
		T_{VJ} = 125°C		50		µA
I_{GSS}	V_{GS} = ± 20 V; V_{DS} = 0 V				100	nA
C_{iss}	V_{GS} = 0 V; V_{DS} = 100 V			2800		pF
C_{oss}	f = 1 MHz			130		pF
Q_g	V_{GS} = 0 to 10 V; V_{DS} = 400 V; I_D = 18 A			60	80	nC
Q_{gs}				14		nC
Q_{gd}				20		nC
$t_{d(on)}$	V_{GS} = 10 V; V_{DS} = 400 V			10		ns
t_r	I_D = 18 A; R_G = 3.3 Ω			5		ns
$t_{d(off)}$				60		ns
t_f				5		ns
R_{thJC}					0.35	K/W

Features

- fast COOLMOS® * power MOSFET 4th generation
  - High blocking capability
  - Lowest resistance
  - Avalanche rated for unclamped inductive switching (UIS)
  - Low thermal resistance due to reduced chip thickness
- Enhanced total power density

Applications

- Switched mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)
- Power factor correction (PFC)
- Welding
- Inductive heating
- PDP and LCD adapter

*COOLMOS® is a trademark of Infineon Technologies AG.

IXYS reserves the right to change limits, test conditions and dimensions.

20090209c

© 2009 IXYS All rights reserved

Source-Drain Diode

Symbol	Conditions	Characteristic Values (T_{VJ} = 25°C, unless otherwise specified) min.	typ.	max.	
I_S	V_{GS} = 0 V			18	A
V_{SD}	I_F = 18 A; V_{GS} = 0 V		0.9	1.2	V
t_{rr}	I_F = 18 A; -di_F/dt = 100 A/µs; V_R = 400 V		450		ns
Q_{RM}			12		µC
I_{RM}			70		A


Component


Symbol	Conditions	Maximum Ratings	
T_{VJ}	operating	-55...+150	°C
T_{stg}		-55...+150	°C
M_d	mounting torque	0.8 ... 1.2	Nm

Symbol	Conditions	Characteristic Values min.	typ.	max.	
R_{thCH}	with heatsink compound		0.25		K/W
Weight			6		g

© 2009 IXYS All rights reserved

TO-247 AD Outline





Symbol	Inches		Millimeters	
	min	max	min	max
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215 BSC		5.46 BSC	
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
ØP	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	0.242 BSC		6.14 BSC	
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
ØP1	-	0.291	-	7.39




Fig. 1 Power dissipation




Fig. 2 Typ. output characteristics




Fig. 3 Typ. output characteristics

© 2009 IXYS All rights reserved




Fig. 4 Typ. drain-source on-state resistance characteristics of IGBT




Fig. 5 Drain-source on-state resistance




Fig. 6 Typ. transfer characteristics




Fig. 7 Forward characteristic of reverse diode




Fig. 8 Typ. gate charge




Fig. 9 Typ. capacitances




Fig. 10 Avalanche energy




Fig. 11 Drain-source breakdown voltage




Fig. 12 Max. transient thermal impedance

IXYS reserves the right to change limits, test conditions and dimensions.

© 2009 IXYS All rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.