
IXYS

Q3-Class HiperFET™ Power MOSFET


IXFN40N110Q3

V_{DSS} = 1100V
I_{D25} = 35A
$R_{DS(on)}$ ≤ 260mΩ

N-Channel Enhancement Mode
Fast Intrinsic Rectifier



miniBLOC
E153432



G = Gate D = Drain
S = Source

Either Source Terminal S can be used as the Source Terminal or the Kelvin Source (Gate Return) Terminal.

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	1100	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	1100	V
V_{GSS}	Continuous	±30	V
V_{GSM}	Transient	±40	V
I_{D25}	T_C = 25°C	35	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	100	A
I_A	T_C = 25°C	40	A
E_{AS}	T_C = 25°C	4	J
dv/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$	50	V/ns
P_D	T_C = 25°C	960	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
V_{ISOL}	50/60 Hz, RMS, t = 1minute	2500	V~
	$I_{ISOL} \le$ 1mA, t = 1s	3000	V~
M_d	Mounting Torque for Base Plate	1.5/13	Nm/lb.in
	Terminal Connection Torque	1.3/11.5	Nm/lb.in
Weight		30	g

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 3mA	1100			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 8mA	3.5		6.5	V
I_{GSS}	V_{GS} = ±30V, V_{DS} = 0V			±200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			50	μA
	T_J = 125°C			3	mA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 20A, Note 1			260	mΩ

Features

- International Standard Package
- Low Intrinsic Gate Resistance
- miniBLOC with Aluminum Nitride Isolation
- Low Package Inductance
- Fast Intrinsic Rectifier
- Low $R_{DS(on)}$ and Q_G

Advantages

- High Power Density
- Easy to Mount
- Space Savings

Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- Temperature and Lighting Controls

© 2020 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 20V, I_D = 20A, Note 1	14	24		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		14		nF
C_{oss}			984		pF
C_{rss}			120		pF
R_{Gi}	Gate Input Resistance		0.18		Ω
$t_{d(on)}$	**Resistive Switching Times**		47		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 20A		68		ns
$t_{d(off)}$	R_G = 0.5Ω (External)		74		ns
t_f			26		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 20A		300		nC
Q_{gs}			95		nC
Q_{gd}			143		nC
R_{thJC}				0.13	°C/W
R_{thCS}			0.05		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			40	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			160	A
V_{SD}	I_F = I_S, V_{GS} = 0V, Note 1			1.4	V
t_{rr}	I_F = 20A, -di/dt = 100A/μs		434		ns
Q_{RM}	V_R = 100V, V_{GS} = 0V		4.1		μC
I_{RM}			18.8		A

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25°C




Fig. 2. Extended Output Characteristics @ T_J = 25°C




Fig. 3. Output Characteristics @ T_J = 125°C




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 20A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 20A Value vs. Drain Current





Fig. 6. Maximum Drain Current vs. Case Temperature



© 2020 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Forward-Bias Safe Operating Area




IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Maximum Transient Thermal Impedance



© 2020 IXYS CORPORATION, All Rights Reserved

SOT-227 Outline



SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	1.224	1.260	31.10	32.00
B	.303	.327	7.70	8.30
C	.161	.173	4.10	4.40
D	.161	.173	4.10	4.40
E	.161	.173	4.10	4.40
F	.587	.598	14.90	15.20
G	1.181	1.201	30.00	30.50
H	1.488	1.508	37.80	38.30
J	.461	.484	11.70	12.30
L	.030	.033	0.75	0.85
M	.492	.512	12.50	13.00
N	.984	1.004	25.00	25.50
O	.075	.087	1.90	2.20
S	.181	.193	4.60	4.90
U	.000	.005	0.00	0.13

1. NUT MATERIAL:
   STANDARD – Low carbon steel with Ni plating.
   OPTIONAL: – Brass Nut is available.
   PART NUMBER–BN
2. ALL METAL SURFACE ARE PRE NI PLATED EXCEPT TRIM AREA.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2020 IXYS CORPORATION, All Rights Reserved