
IXYS

IXTH 13N110

MegaMOS™FET


N-Channel Enhancement Mode

V_{DSS} = 1100 V
I_{D25} = 13 A
$R_{DS(on)}$ = 0.92 Ω



Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	1100	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	1100	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C	13	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	52	A
P_D	T_C = 25°C	360	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
M_d	Mounting torque	1.13/10	Nm/lb.in.
Weight		6	g
Maximum lead temperature for soldering 1.6 mm (0.062 in.) from case for 10 s		300	°C

TO-247 AD



G = Gate, D = Drain,
S = Source, TAB = Drain

OBSOLETE

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
V_{DSS}	V_{GS} = 0 V, I_D = 3 mA	1100			V
$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250 µA	2		4.5	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0			±100	nA
I_{DSS}	V_{DS} = 0.8 • V_{DSS} T_J = 25°C V_{GS} = 0 V T_J = 125°C			500 3	µA mA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 0.5 • I_{D25} Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %		0.80	0.92	Ω

Features

- International standard package JEDEC TO-247 AD
- Low $R_{DS(on)}$ HDMOS™ process
- Rugged polysilicon gate cell structure
- Fast switching times

Applications

- Switch-mode and resonant-mode power supplies
- Motor controls
- Uninterruptible Power Supplies (UPS)
- DC choppers

Advantages

- Easy to mount with 1 screw (isolated mounting screw hole)
- Space savings
- High power density

IXYS reserves the right to change limits, test conditions, and dimensions.

92781F (3/98)


© 2000 IXYS All rights reserved

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
g_{fs}	V_{DS} = 10 V; I_D = 6.5 A, pulse test		10		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		5650		pF
C_{oss}			400		pF
C_{rss}			150		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 I_{D25} R_G = 1 Ω, (External)		24		ns
t_r			21		ns
$t_{d(off)}$			80		ns
t_f			36		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 I_{D25}		195		nC
Q_{gs}			28		nC
Q_{gd}			85		nC
R_{thJC}				0.35	K/W
R_{thCK}			0.25		K/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values min.	typ.	max.	
I_S	V_{GS} = 0 V			13	A
I_{SM}	Repetitive; pulse width limited by T_{JM}			52	A
V_{SD}	$I_F = I_S$, V_{GS} = 0 V, Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			1.5	V
t_{rr}	$I_F = I_S$, -di/dt = 100 A/µs, V_R = 100 V		850		ns

TO-247 AD Outline



Terminals: 1 - Gate 2 - Drain
3 - Source Tab - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
∅P	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

OBSOLETE

© 2000 IXYS All rights reserved

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents:
4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715
4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.