IXYS


Preliminary Technical Information

TrenchT2™ Power MOSFET


IXTH260N055T2

V_{DSS} = 55V
I_{D25} = 260A
$R_{DS(on)}$ ≤ 3.3mΩ

N-Channel Enhancement Mode
Avalanche Rated



TO-247



G = Gate D = Drain
S = Source TAB = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 175°C	55	V
V_{DGR}	T_J = 25°C to 175°C, R_{GS} = 1MΩ	55	V
V_{GSM}	Transient	± 20	V
I_{D25}	T_C = 25°C	260	A
I_{LRMS}	Lead Current Limit, RMS	160	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	780	A
I_A	T_C = 25°C	100	A
E_{AS}	T_C = 25°C	600	mJ
P_D	T_C = 25°C	480	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +175	°C
T_L	1.6mm (0.062in.) from case for 10s	300	°C
T_{sold}	Plastic body for 10 seconds	260	°C
M_d	Mounting torque	1.13 / 10	Nm/lb.in.
Weight		6	g

Symbol	Test Conditions (T_J = 25°C unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 250μA	55			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 250μA	2.0		4.0	V
I_{GSS}	V_{GS} = ± 20V, V_{DS} = 0V			±200	nA
I_{DSS}	$V_{DS} = V_{DSS}$			5	μA
	V_{GS} = 0V T_J = 150°C			150	μA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 50A, Notes 1, 2			3.3	mΩ

Features

- International standard package
- 175°C Operating Temperature
- High current handling capability
- Avalanche rated
- Low $R_{DS(on)}$

Advantages

- Easy to mount
- Space savings
- High power density

Applications

- Automotive
  - Motor Drives
  - 12V Battery
  - ABS Systems
- DC/DC Converters and Off-line UPS
- Primary- Side Switch
- High Current Switching Applications

© 2008 IXYS CORPORATION, All rights reserved


Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10V, I_D = 60A, Note 1	55	94		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		10.8		nF
C_{oss}			1460		pF
C_{rss}			215		pF
$t_{d(on)}$	**Resistive Switching Times**		20		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 100A		27		ns
$t_{d(off)}$	R_G = 2Ω (External)		36		ns
t_f			24		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		140		nC
Q_{gs}			52		nC
Q_{gd}			32		nC
R_{thJC}				0.31	°C/W
R_{thCH}			0.21		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			260	A
I_{SM}	Repetitive, Pulse width limited by T_{JM}			1000	A
V_{SD}	I_F = 100A, V_{GS} = 0V, Note 1			1.3	V
t_{rr}	I_F = 130A, V_{GS} = 0V		60		ns
I_{RM}	-di/dt = 100A/μs		3.4		A
Q_{RM}	V_R = 27V		102		nC

Note 1: Pulse test, t ≤ 300μs; duty cycle, d ≤ 2%.

TO-247 (IXTH) Outline



Terminals: 1 - Gate 2 - Drain

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
ØP	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216

PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ 25ºC




Fig. 2. Extended Output Characteristics @ 25ºC




Fig. 3. Output Characteristics @ 150ºC




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 130A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 130A Value vs. Drain Current





Fig. 6. Drain Current vs. Case Temperature



© 2008 IXYS CORPORATION, All rights reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance





Fig. 12. Forward-Bias Safe Operating Area



IXYS reserves the right to change limits, test conditions, and dimensions.

Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature




Fig. 14. Resistive Turn-on Rise Time vs. Drain Current




Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance




Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature




Fig. 17. Resistive Turn-off Switching Times vs. Drain Current






Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance



© 2008 IXYS CORPORATION, All rights reserved

Fig. 19. Maximum Transient Thermal Impedance



IXYS reserves the right to change limits, test conditions, and dimensions.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.