
59065 5/16" Plastic Threaded Barrel Sensor + 57065 Actuator




Agency Approvals

Agency	Agency File Number
c UL us	E61760

Note: Contact Littelfuse for specific agency approval ratings.

Dimensions

Dimensions in mm (inch)



Different cable options available.

Description

The 59065 is a small plastic barrel sensor with a 5/16" x 24 thread, 38.1mm (1.500") long with a choice of normally open, normally open high voltage, normally closed or change over contacts. It is capable of switching up to 265Vac/300Vdc at 10VA. It functions best with the 57065 actuator.

Note: The 57065 Actuator is sold separately.

Features

- Two-part magnetically operated proximity sensor
- Threaded barrel with retaining nuts
- Available as M8 (57070/59070) or 5/16 (57065/59065) size options
- Customer defined sensitivity option
- Choice of cable length and connector

Benefits

- Simple installation and adjustment using supplied retaining nuts
- Operates through non-ferrous materials such as wood, plastic or aluminium
- Excellent for switching micro-controller logic level loads
- No standby power requirement

Applications

- Position and Limit Sensing
- Security System Switch
- Industrial Process Control
- Linear Actuators

© 2017 Littelfuse Revised: 02/12/17
Specifications are subject to change without notice.

59065 5/16" Plastic Threaded Barrel Sensor + 57065 Actuator

Electrical Ratings


Contact Type			Normally Open	Normally Open HighVoltage	Change Over	Normally Closed
Switch Type			1	2	3	4
Contact Rating [1]		VA/Watt - max.	10	10	5	5
Voltage [4]	Switching [2] Breakdown [3]	Vdc - max. Vac - max. Vdc - min.	200 140 250	300 265 400	175 120 200	175 120 200
Current [4]	Switching [2] Carry	Adc - max. Aac - max. Adc - max.	0.5 0.35 1.2	0.4 0.30 1.4	0.25 0.18 1.5	0.25 0.18 1.5
Resistance [5]	Contact, Initial Insulation	Ω - max. Ω - min.	0.2 10^{10}	0.2 10^{10}	0.2 10^{9}	0.2 10^{9}
Capacitance	Contact	pF - typ.	0.3	0.2	0.3	0.3
Temperature	Operating	°C	-40 to +105	-20 to +105	-40 to +105	-40 to +105
Product Characteristics						
Operate Time [6]		ms - max.	1.0	1.0	3.0	3.0
Release Time [6]		ms - max.	1.0	1.0	3.0	3.0
Shock [7]	11ms ½ sine	G - max.	100	100	50	50
Vibration [7]	50-2000 Hz	G - max.	30	30	30	30


Notes:
1. Contact rating - Product of the switching voltage and current should never exceed the wattage rating. Contact Littelfuse for additional load/life information.
2. When switching inductive and/or capacitive loads, the effects of transient voltages and/or currents should be considered. Refer to Application Notes AN108A and AN107 for details.
3. Breakdown Voltage - per MIL-STD-202, Method 301.
4. Electrical Load Life Expectancy - Contact Littelfuse with voltage, current values along with type of load.
5. This resistance value is for 11.81mm wire length. Resistance changes when wire lengthens.
6. Operate (including bounce)/Release Time - per EIA/NARM RS-421-A, diode suppressed coil (Coil II).
7. Shock and Vibration - per EIA/NARM RS-421-A and MIL-STD-202.
8. For custom modifications to the wire length or size, or adding a special connector, please contact Littelfuse.

Sensitivity Options (Using 57065 Actuator)

Select Option		S		T		U		V	
Switch Type		Pull-In AT Range	Activate Distance–D mm (inch) Average	Pull-In AT Range	Activate Distance–D mm (inch) Average	Pull-In AT Range	Activate Distance–D mm (inch) Average	Pull-In AT Range	Activate Distance–D mm (inch) Average
1	Normally Open	12-18	8.4 (.330)	17-23	6.6 (.260)	22-28	5.1 (.200)	27-33	4.0 (.157)
2	High Voltage	–	–	17-23	6.6 (.260)	22-28	5.1 (.200)	27-33	4.0 (.157)
3	Change Over	15-20	6.5 (.255)	20-25	4.9 (.193)	25-30	3.7 (.146)	–	–
4	Normally Closed	15-20	6.5 (.255)	20-25	4.9 (.193)	25-30	3.7 (.146)	–	–

Note:
1. Pull-In AT Range: These AT values are the bare reed switch AT before modification.
2. The activation distance is average value on the final sensor assembly.



Schematics	Switch Type
	1 and 2
	3
	4

© 2017 Littelfuse Revised: 02/12/17
Specifications are subject to change without notice.




Littelfuse
Expertise Applied | Answers Delivered

59065 5/16" Plastic Threaded Barrel Sensor + 57065 Actuator

Cable Length Specification

Cable Type: 24 AWG 7/32 PVC 105°C UL1430/UL1569	
Select Option	**Cable Length mm (inch)**
02	300 (11.81)

Termination Specification

Termination Options		
Select Option	**Description (Two-wire versions illustrated)**	
A	Tinned leads (6.4±0.76)mm	
F	Untinned leads (6.4±0.76)mm	
E	JST type XHP 2.5mm pitch	

Part Numbering System

Sensor: **59065 - X - X - XX - X**

- **Series**
- **Switch Type** 1, 2, 3, or 4
- **Sensitivity** S, T, U, or V
- **Cable Length** 02
- **Termination** A, F, or E

Actuator: **57065 - 000**

- **Series**
- **Standard Actuator** 000

Note: The 57065 Actuator is sold separately.

Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width
Bulk	Bulk	500	N/A	N/A

© 2017 Littelfuse Revised: 02/12/17
Specifications are subject to change without notice.