

XPT IGBT Module

$$V_{CES} = 1200\text{ V}$$


$$I_{C25} = 120\text{ A}$$

$$V_{CE(sat)} = 1,9\text{ V}$$

Boost Chopper


Part number

MIXA80R1200VA



Backside: isolated

 E72873



Features / Advantages:

- Easy paralleling due to the positive temperature coefficient of the on-state voltage
- Rugged XPT design (Xtreme light Punch Through) results in:
 - short circuit rated for 10 μ sec.
 - very low gate charge
 - low EMI
 - square RBSOA @ 3x I_c
- Thin wafer technology combined with the XPT design results in a competitive low $V_{CE(sat)}$
- SONIC™ diode
 - fast and soft reverse recovery
 - low operating forward voltage

Applications:

- AC motor drives
- Solar inverter
- Medical equipment
- Uninterruptible power supply
- Air-conditioning systems
- Welding equipment
- Switched-mode and resonant-mode power supplies
- Inductive heating, cookers
- Pumps, Fans

Package: V1-A-Pack

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Height: 17 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Terms .Conditions of usage:

The data contained in this product data sheet is exclusively intended for technically trained staff. The user will have to evaluate the suitability of the product for the intended application and the completeness of the product data with respect to his application. The specifications of our components may not be considered as an assurance of component characteristics. The information in the valid application- and assembly notes must be considered. Should you require product information in excess of the data given in this product data sheet or which concerns the specific application of your product, please contact the sales office, which is responsible for you.

Due to technical requirements our product may contain dangerous substances. For information on the types in question please contact the sales office, which is responsible for you.

Should you intend to use the product in aviation, in health or life endangering or life support applications, please notify. For any such application we urgently recommend


- to perform joint risk and quality assessments;

- the conclusion of quality agreements;

- to establish joint measures of an ongoing product survey, and that we may make delivery dependent on the realization of any such measures.

IGBT				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V _{CES}	collector emitter voltage	T _{VJ} = 25°C				1200	V
V _{GES}	max. DC gate voltage					±20	V
V _{GEM}	max. transient gate emitter voltage					±30	V
I _{C25}	collector current	T _C = 25°C				120	A
I _{C80}		T _C = 80°C				84	A
P _{tot}	total power dissipation	T _C = 25°C				390	W
V _{CE(sat)}	collector emitter saturation voltage	I _C = 75 A; V _{GE} = 15 V	T _{VJ} = 25°C T _{VJ} = 125°C		1,9 2,2	2,2	V V
V _{GE(th)}	gate emitter threshold voltage	I _C = 6 mA; V _{GE} = V _{CE}	T _{VJ} = 25°C	5,4	5,9	6,5	V
I _{CES}	collector emitter leakage current	V _{CE} = V _{CES} ; V _{GE} = 0 V	T _{VJ} = 25°C T _{VJ} = 125°C			0,2	mA mA
I _{GES}	gate emitter leakage current	V _{GE} = ±20 V				500	nA
Q _{G(on)}	total gate charge	V _{CE} = 600 V; V _{GE} = 15 V; I _C = 75 A			230		nC
t _{d(on)}	turn-on delay time	inductive load V _{CE} = 600 V; I _C = 75 A V _{GE} = ±15 V; R _G = 10 Ω	T _{VJ} = 125°C		70		ns
t _r	current rise time				40		ns
t _{d(off)}	turn-off delay time				250		ns
t _f	current fall time				100		ns
E _{on}	turn-on energy per pulse				6,8		mJ
E _{off}	turn-off energy per pulse				8,3		mJ
RBSOA	reverse bias safe operating area	V _{GE} = ±15 V; R _G = 10 Ω	T _{VJ} = 125°C				
I _{CM}		V _{CEma} = 1200 V				225	A
SCSOA	short circuit safe operating area	V _{CEma} = 1200 V	T _{VJ} = 125°C				
t _{SC}	short circuit duration	V _{CE} = 900 V; V _{GE} = ±15 V				10	μs
I _{SC}	short circuit current	R _G = 10 Ω; non-repetitive			300		A
R _{thJC}	thermal resistance junction to case					0,32	K/W
R _{thCH}	thermal resistance case to heatsink				0,20		K/W
Diode							
V _{RRM}	max. repetitive reverse voltage	T _{VJ} = 25°C				1200	V
I _{F25}	forward current	T _C = 25°C				135	A
I _{F80}		T _C = 80°C				90	A
V _F	forward voltage	I _F = 100 A	T _{VJ} = 25°C T _{VJ} = 125°C			2,30	V V
I _R	reverse current	V _R = V _{RRM}	T _{VJ} = 25°C T _{VJ} = 125°C			0,3	mA mA
Q _{rr}	reverse recovery charge	V _R = 600 V -di _F /dt = 1600 A/μs I _F = 100 A; V _{GE} = 0 V	T _{VJ} = 125°C		12,5		μC
I _{RM}	max. reverse recovery current				105		A
t _{rr}	reverse recovery time				350		ns
E _{rec}	reverse recovery energy				4		mJ
R _{thJC}	thermal resistance junction to case					0,4	K/W
R _{thCH}	thermal resistance case to heatsink				0,20		K/W

Package V1-A-Pack				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I _{RMS}	RMS current	per terminal				100	A
T _{VJ}	virtual junction temperature			-40		150	°C
T _{op}	operation temperature			-40		125	°C
T _{stg}	storage temperature			-40		125	°C
Weight					37		g
M _D	mounting torque			2		2,5	Nm
d _{Spp/App}	creepage distance on surface striking distance through air	terminal to terminal		6,0			mm
d _{Spb/Apb}		terminal to backside		12,0			mm
V _{ISOL}	isolation voltage	t = 1 second	50/60 Hz, RMS; I _{ISOL} ≤ 1 mA	3600			V
		t = 1 minute		3000			V



Part description


M = Module
 I = IGBT
 X = XPT IGBT
 A = Gen 1 / std
 80 = Current Rating [A]
 R = Boost Chopper
 1200 = Reverse Voltage [V]
 VA = V1-A-Pack

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MIXA80R1200VA	MIXA80R1200VA	Blister	24	510585

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 150^\circ\text{C}$



$V_{0\max}$ threshold voltage

$R_{0\max}$ slope resistance *

IGBT

1,1

17,9

Diode



1,09

9,1







V

mΩ

Outlines V1-A-Pack



IGBT



Diode




Fig. 7 Typ. Forward current versus V_F




Fig. 8 Typ. reverse recov.charge Q_{rr} vs. di/dt




Fig. 9 Typ. peak reverse current I_{RM} vs. di/dt




Fig. 10 Typ. recovery time t_{rr} versus di/dt




Fig. 11 Typ. recovery energy E_{rec} versus di/dt




Fig. 12 Typ. transient thermal impedance