
GEN2 SiC Schottky Diode

LSIC2SD120E15CC, 1200 V, 15 A, TO-247-3L

LSIC2SD120E15CC




Description

This series of silicon carbide (SiC) Schottky diodes has negligible reverse recovery current, high surge capability, and a maximum operating junction temperature of 175 °C. These diodes series are ideal for applications where improvements in efficiency, reliability, and thermal management are desired.

Features

- Positive temperature coefficient for safe operation and ease of paralleling
- 175 °C maximum operating junction temperature
- Excellent surge capability
- Extremely fast, temperature-independent switching behavior
- Dramatically reduced switching losses compared to Si bipolar diodes

Circuit Diagram TO247-3L



Applications

- Boost diodes in PFC or DC/DC stages
- Switch-mode power supplies
- Uninterruptible power supplies
- Solar inverters
- Industrial motor drives
- EV charging stations

Environmental

- Littelfuse "RoHS" logo = RoHS conform
- Littelfuse "HF" logo = HF Halogen Free
- Littelfuse "PB-free" logo = Pb-free lead plating

Maximum Ratings

Characteristics	Symbol	Conditions	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	-	1200	V
DC Blocking Voltage	V_R	T_J = 25 °C	1200	V
Continuous Forward Current (Per Leg/Device)	I_F	T_C = 25 °C	24.5/49	A
		T_C = 135 °C	12/24	
		T_C = 154 °C	8/16	
Non-Repetitive Forward Surge Current (Per Leg)	I_{FSM}	T_C = 25 °C, T_P = 10 ms, Half sine pulse	65	A
Power Dissipation (Per Leg/Device)	P_{Tot}	T_C = 25 °C	125/250	W
		T_C = 110 °C	54/108	
Operating Junction Temperature	T_J	-	-55 to 175	°C
Storage Temperature	T_{STG}	-	-55 to 150	°C
Soldering Temperature	T_{sold}	-	260	°C

© 2019 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: January 7, 2020 11:01 PM

GEN2 SiC Schottky Diode

LSIC2SD120E15CC, 1200 V, 15 A, TO-247-3L

Electrical Characteristics (Per Leg)

Characteristics	Symbol	Conditions	Value			Unit
			Min.	Typ.	Max.	
Forward Voltage	V_F	I_F = 8 A, T_J = 25 °C	-	1.5	1.8	V
		I_F = 8 A, T_J = 175 °C	-	2.2	-	
Reverse Current	I_R	V_R = 1200 V, T_J = 25 °C	-	<1	100	µA
		V_R = 1200 V, T_J = 175 °C	-	10		
Total Capacitance	C	V_R = 1 V, f =1 MHz	-	454	-	pF
		V_R = 400 V, f = 1 MHz	-	45	-	
		V_R = 800 V, f = 1 MHz	-	33	-	
Total Capacitive Charge	Q_C	V_R = 800 V, $Q_c = \int_0^{V_R} C(V)dV$	-	47	-	nC

Footnote: T_J = +25 °C unless otherwise specified

Thermal Characteristics

Characteristics	Symbol	Conditions	Value			Unit
			Min.	Typ.	Max.	
Thermal Resistance (Per Device/Leg)	$R_{\theta JC}$	-	-	1.2/0.6	-	°C/W

Figure 1: Typical Foward Characteristics (Per Leg)





Figure 2: Typical Reverse Characteristics (Per Leg)



© 2019 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: January 7, 2020 11:01 PM

Figure 3: Power Derating (Per Leg)




Figure 4: Current Derating (Per Leg)




Figure 5: Capacitance vs. Reverse Voltage (Per Leg)





Figure 6: Capacitive Charge vs. Reverse Voltage (Per Leg)



© 2019 Littelfuse, Inc.
Specifications are subject to change without notice.

Figure 7: Stored Energy vs. Reverse Voltage (Per Leg)







Figure 8: Transient Thermal Impedance (Per Device)



Package Dimensions TO-247-3L



Recommended Hole Pattern Layout



Symbol	Millimeters		
	Min	Nom	Max
A	4.80	5.03	5.20
A1	2.25	2.38	2.54
A2	1.85	1.98	2.11
b	0.99	-	1.40
b2	1.65	-	2.39
b4	2.59	-	3.43
c	0.38	0.64	0.89
D	20.80	20.96	21.34
D1	13.50	-	-
D2	0.51	1.19	1.35
e	5.44 BSC		
E	15.75	15.90	16.13
E1	13.06	14.02	14.15
E2	4.19	4.32	4.83
L	19.81	20.19	20.57
L1	3.81	4.19	4.45
øP	3.55	3.61	3.66
øP1	7.06	7.19	7.32
Q	5.49	5.61	6.20
S	6.05	6.17	6.30


Notes:
1. Dimensions are in millimeters
2. Dimension D, E do not include mold flash. Mold flash shall not exceed 0.127 mm per side measured at outer most extreme of plastic body.
3. øP to have a maximum draft angle of 38.1 mm to the top of the part with a maximum hole diameter of 3.912 mm.

© 2019 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: January 7, 2020 11:01 PM

GEN2 SiC Schottky Diode

LSIC2SD120E15CC, 1200 V, 15 A, TO-247-3L

Part Numbering and Marking System





SIC	= SiC
2	= Gen2
SD	= Schottky Diode
120	= Voltage Rating (1200 V)
E	= TO-247-3L
15	= Current Rating (15 A)
CC	= Common Cathode
YY	= Year
WW	= Week
E	= Special Code
ZZZZZZ-ZZ	= Lot Number

Packing Options

Part Number	Marking	Packing Mode	M.O.Q
LSIC2SD120E15CC	SIC2SD120E15CC	Tube (30pcs)	450

Packing Specification TO-247-3L





NOTE:

1. All pin plug holes are considered critical dimension
2. Tolerance is to be ±0.010 unless otherwise specified
3. Dimension are in inch (and millimeters).

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2019 Littelfuse, Inc.
Specifications are subject to change without notice.
Revised: January 7, 2020 11:01 PM