

## USP3275 Thermistor Probe




### Description

Littelfuse offers Stainless probe housings suitable for a wide range of temperature sensing applications. If the dimensions on this product won't work for your requirements, please contact us for further assistance.

### Features

- Pointed Probe Tip
- Teflon Insulated Lead Wire
- 105°C Max Operating Temperature


### Dimensions



Dimensions in inches.

A	B	C	D
0.250" ±0.070" Strip	10.00" ±0.100"	0.188" ±0.005"	45.0" ±2.00"

### Part Numbering System



**Note:** Not all combinations of Part Number codes are available. Contact Littelfuse for details.

### Specifications

Part Number	Resistance Ohms @25°C	Resistance Tol. ± % @ 25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP3275	10000	5	J	-4.4	3892	-55 to +105

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)