IXYS

GenX3™ 1200V IGBTs

IXGH32N120A3
IXGT32N120A3

V_{CES} = 1200V
I_{C110} = 32A
$V_{CE(sat)}$ ≤ 2.35V

Ultra-Low Vsat PT IGBTs for up to 3 kHz Switching



TO-268 (IXGT)



TO-247 (IXGH)



G = Gate C = Collector
E = Emitter Tab = Collector

Symbol	Test Conditions	Maximum Ratings	
V_{CES}	T_J = 25°C to 150°C	1200	V
V_{CGR}	T_J = 25°C to 150°C, R_{GE} = 1MΩ	1200	V
V_{GES}	Continuous	±20	V
V_{GEM}	Transient	±30	V
I_{C25}	T_C = 25°C	75	A
I_{C110}	T_C = 110°C	32	A
I_{CM}	T_C = 25°C, 1ms	230	A
I_A	T_C = 25°C	20	A
E_{AS}	T_C = 25°C	120	mJ
SSOA	V_{GE} = 15V, T_J = 125°C, R_G = 20Ω	I_{CM} = 150	A
(RBSOA)	Clamped Inductive Load	$V_{CE} \leq 0.8 \bullet V_{CES}$	
P_C	T_C = 25°C	300	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6mm (0.063in) from Case for 10s	300	°C
T_{SOLD}	Plastic Body for 10s	260	°C
M_d	Mounting Torque (TO-247)	1.13/10	Nm/lb.in.
Weight	TO-247	6.0	g
	TO-268	4.0	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{CES}	I_C = 250μA, V_{GE} = 0V	1200			V
$V_{GE(th)}$	I_C = 250μA, V_{CE} = V_{GE}	3.0		5.0	V
I_{CES}	V_{CE} = V_{CES}, V_{GE} = 0V			50	μA
	T_J = 125°C			1	mA
I_{GES}	V_{CE} = 0V, V_{GE} = ±20V			±100	nA
$V_{CE(sat)}$	I_C = I_{C110}, V_{GE} = 15V, Note 1			2.35	V
	I_C = 400A, V_{GE} = 30V, Note 1		11		V

Features

- Optimized for Low Conduction Losses
- International Standard Packages

Advantages

- High Power Density
- Low Gate Drive Requirement

Applications

- Power Inverters
- Capacitor Discharge
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts
- Inrush Current Protection Circuits

© 2011 IXYS CORPORATION, All rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.
g_{fs}	I_C = 50A, V_{CE} = 10V, Note 1	14	20	S
$I_{C(on)}$	V_{CE} = 10V, V_{GE} = 15V, Note 1		94	A
C_{ies}	V_{CE} = 25V, V_{GE} = 0V, f = 1MHz		2150	pF
C_{oes}			130	pF
C_{res}			14	pF
Q_g	I_C = 50A, V_{GE} = 15V, V_{CE} = 0.5 • V_{CES}		89	nC
Q_{ge}			15	nC
Q_{gc}			34	nC
$t_{d(on)}$	**Resistive Switching Times, T_J = 25°C**		39	ns
t_r	V_{GE} = 20V, V_{CE} = 0.8 • V_{CES}, I_C = 100A		200	ns
$t_{d(off)}$	R_G = 10Ω (External)		140	ns
t_f			1240	ns
R_{thJC}				0.42 °C/W
R_{thCK}	TO-247		0.21	°C/W

Note 1. Pulse test, t ≤ 300µs, duty cycle, d ≤ 2%.

TO-247 AD Outline



Terminals: 1 - Gate 2 - Collector
3 - Emitter

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.7	5.3	.185	.209
A_1	2.2	2.54	.087	.102
A_2	2.2	2.6	.059	.098
b	1.0	1.4	.040	.055
b_1	1.65	2.13	.065	.084
b_2	2.87	3.12	.113	.123
C	.4	.8	.016	.031
D	20.80	21.46	.819	.845
E	15.75	16.26	.610	.640
e	5.20	5.72	0.205	0.225
L	19.81	20.32	.780	.800
L1		4.50		.177
∅P	3.55	3.65	.140	.144
Q	5.89	6.40	0.232	0.252
R	4.32	5.49	.170	.216
S	6.15 BSC		242 BSC	

TO-268 Outline



Terminals: 1 - Gate 2, 4 - Collector
3 - Emitter

SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.193	.201	4.90	5.10
A1	.106	.114	2.70	2.90
A2	.001	.010	0.02	0.25
b	.045	.057	1.15	1.45
b2	.075	.083	1.90	2.10
C	.016	.026	0.40	0.65
C2	.057	.063	1.45	1.60
D	.543	.551	13.80	14.00
D1	.488	.500	12.40	12.70
E	.624	.632	15.85	16.05
E1	.524	.535	13.30	13.60
e	.215 BSC		5.45 BSC	
H	.736	.752	18.70	19.10
L	.094	.106	2.40	2.70
L1	.047	.055	1.20	1.40
L2	.039	.045	1.00	1.15
L3	.010 BSC		0.25 BSC	
L4	.150	.161	3.80	4.10

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC



Fig. 2. Extended Output Characteristics @ T_J = 25ºC



Fig. 3. Output Characteristics @ T_J = 125ºC



Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature



Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage



Fig. 6. Input Admittance



© 2011 IXYS CORPORATION, All rights Reserved

Fig. 7. Transconductance



Fig. 8. Dependence of BV_{CES} & $V_{(th)GE}$ on Junction Temperature



Fig. 9. Single-Pulsed Avalanche Energy vs. Junction Temperature



Fig. 10. Resistive Turn-on Rise Time vs. Gate Voltage



Fig. 11. Gate Charge



Fig. 12. Capacitance



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Resistive Turn-on Switching Times vs. Gate Resistance



Fig. 14. Resistive Turn-on Rise Time vs. Junction Temperature



Fig. 15. Resistive Turn-on Rise Time vs. Collector Current



Fig. 16. Resistive Turn-off Switching Times vs. Gate Resistance



Fig. 17. Resistive Turn-off Switching Times vs. Junction Temperature



Fig. 18. Resistive Turn-off Switching Times vs. Collector Current



© 2011 IXYS CORPORATION, All rights Reserved

Fig. 19. Reverse-Bias Safe Operating Area



Fig. 20. Maximum Transient Thermal Impedance



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.