


## Polar™ Power MOSFET HiPerFET™

### IXFR32N100P

N-Channel Enhancement Mode  
Avalanche Rated  
Fast Intrinsic Diode




$$\begin{aligned} V_{DSS} &= 1000V \\ I_{D25} &= 18A \\ R_{DS(on)} &\leq 340m\Omega \\ t_{rr} &\leq 300ns \end{aligned}$$

| Symbol        | Test Conditions                                                    | Maximum Ratings |            |
|---------------|--------------------------------------------------------------------|-----------------|------------|
| $V_{DSS}$     | $T_J = 25^\circ C$ to $150^\circ C$                                | 1000            | V          |
| $V_{DGR}$     | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GS} = 1M\Omega$          | 1000            | V          |
| $V_{GSS}$     | Continuous                                                         | $\pm 30$        | V          |
| $V_{GSM}$     | Transient                                                          | $\pm 40$        | V          |
| $I_{D25}$     | $T_C = 25^\circ C$                                                 | 18              | A          |
| $I_{DM}$      | $T_C = 25^\circ C$ , pulse width limited by $T_{JM}$               | 75              | A          |
| $I_{AR}$      | $T_C = 25^\circ C$                                                 | 16              | A          |
| $E_{AS}$      | $T_C = 25^\circ C$                                                 | 1.5             | J          |
| $dV/dt$       | $I_S \leq I_{DM}$ , $V_{DD} \leq V_{DSS}$ , $T_J \leq 150^\circ C$ | 15              | V/ns       |
| $P_D$         | $T_C = 25^\circ C$                                                 | 320             | W          |
| $T_J$         |                                                                    | -55 ... +150    | $^\circ C$ |
| $T_{JM}$      |                                                                    | 150             | $^\circ C$ |
| $T_{stg}$     |                                                                    | -55 ... +150    | $^\circ C$ |
| $T_L$         | Maximum lead temperature for soldering                             | 300             | $^\circ C$ |
| $T_{SOLD}$    | Plastic body for 10s                                               | 260             | $^\circ C$ |
| $V_{ISOL}$    | 50/60 Hz, RMS, 1 minute                                            | 2500            | V~         |
| $F_C$         | Mounting force                                                     | 20..120/4.5..27 | N/lb.      |
| <b>Weight</b> |                                                                    | 5               | g          |

ISOPLUS247 (IXFR)

E153432



G = Gate      D = Drain  
S = Source

### Features

- Silicon chip on Direct-Copper-Bond substrate
  - High power dissipation
  - Isolated mounting surface
  - 2500V electrical isolation
- Low drain to tab capacitance(<30pF)
- Low  $R_{DS(on)}$  HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Fast intrinsic Rectifier

### Applications

- Switched-mode and resonant-mode power supplies
- DC-DC converters
- Laser Drivers
- AC and DC motor controls
- Robotics and servo controls

### Advantages


- Easy assembly
- Space savings
- High power density

| Symbol       | Test Conditions<br>( $T_J = 25^\circ C$ , unless otherwise specified) | Characteristic Values |      |                      |
|--------------|-----------------------------------------------------------------------|-----------------------|------|----------------------|
|              |                                                                       | Min.                  | Typ. | Max.                 |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 3mA$                                           | 1000                  |      | V                    |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 1mA$                                       | 3.5                   |      | 6.5 V                |
| $I_{GSS}$    | $V_{GS} = \pm 30V$ , $V_{DS} = 0V$                                    |                       |      | $\pm 200$ nA         |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$<br>$V_{GS} = 0V$ $T_J = 125^\circ C$               |                       |      | 50 $\mu A$<br>2.5 mA |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 16A$ , Note 1                                 |                       |      | 340 m $\Omega$       |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ unless otherwise specified)                                                             | Characteristic Values |      |                         |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------|-----------------------|------|-------------------------|
|              |                                                                                                                                       | Min.                  | Typ. | Max.                    |
| $g_{fs}$     | $V_{DS} = 20\text{V}, I_D = 16\text{A}$ , Note 1                                                                                      | 13                    | 21   | S                       |
| $C_{iss}$    | $V_{GS} = 0\text{V}, V_{DS} = 25\text{V}, f = 1\text{MHz}$                                                                            |                       | 14.2 | nF                      |
| $C_{oss}$    |                                                                                                                                       |                       | 815  | pF                      |
| $C_{rss}$    |                                                                                                                                       |                       | 60   | pF                      |
| $R_{Gi}$     | Gate input resistance                                                                                                                 |                       | 1.50 | $\Omega$                |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 16\text{A}$<br>$R_G = 1\Omega$ (External) |                       | 50   | ns                      |
| $t_r$        |                                                                                                                                       |                       | 55   | ns                      |
| $t_{d(off)}$ |                                                                                                                                       |                       | 76   | ns                      |
| $t_f$        |                                                                                                                                       |                       | 43   | ns                      |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 16\text{A}$                                                                   |                       | 225  | nC                      |
| $Q_{gs}$     |                                                                                                                                       |                       | 85   | nC                      |
| $Q_{gd}$     |                                                                                                                                       |                       | 94   | nC                      |
| $R_{thJC}$   |                                                                                                                                       |                       |      | 0.39 $^\circ\text{C/W}$ |
| $R_{thCS}$   |                                                                                                                                       | 0.15                  |      | $^\circ\text{C/W}$      |

| Source-Drain Diode                                   |                                                                                                 | Characteristic Values |      |               |
|------------------------------------------------------|-------------------------------------------------------------------------------------------------|-----------------------|------|---------------|
| $T_J = 25^\circ\text{C}$ unless otherwise specified) |                                                                                                 | Min.                  | Typ. | Max.          |
| $I_S$                                                | $V_{GS} = 0\text{V}$                                                                            |                       |      | 32 A          |
| $I_{SM}$                                             | Repetitive, pulse width limited by $T_{JM}$                                                     |                       |      | 128 A         |
| $V_{SD}$                                             | $I_F = I_S, V_{GS} = 0\text{V}$ , Note 1                                                        |                       |      | 1.5 V         |
| $t_{rr}$                                             | $I_F = 16\text{A}, -di/dt = 100\text{A}/\mu\text{s}$<br>$V_R = 100\text{V}, V_{GS} = 0\text{V}$ |                       | 2.2  | 300 ns        |
| $Q_{RM}$                                             |                                                                                                 |                       |      | $\mu\text{C}$ |
| $I_{RM}$                                             |                                                                                                 |                       |      | A             |

## ISOPLUS247 (IXFR) Outline



| SYM | INCHES   |      | MILLIMETERS |       |
|-----|----------|------|-------------|-------|
|     | MIN      | MAX  | MIN         | MAX   |
| A   | .190     | .205 | 4.83        | 5.21  |
| A1  | .090     | .100 | 2.29        | 2.54  |
| A2  | .075     | .085 | 1.91        | 2.16  |
| b   | .045     | .055 | 1.14        | 1.40  |
| b1  | .075     | .084 | 1.91        | 2.13  |
| b2  | .115     | .123 | 2.92        | 3.12  |
| C   | .024     | .031 | 0.61        | 0.80  |
| D   | .819     | .840 | 20.80       | 21.34 |
| E   | .620     | .635 | 15.75       | 16.13 |
| e   | .215 BSC |      | 5.45 BSC    |       |
| L   | .780     | .800 | 19.81       | 20.32 |
| L1  | .150     | .170 | 3.81        | 4.32  |
| Q   | .220     | .244 | 5.59        | 6.20  |
| R   | .170     | .190 | 4.32        | 4.83  |
| S   | .520     | .540 | 13.21       | 13.72 |
| T   | .620     | .640 | 15.75       | 16.26 |
| U   | .065     | .080 | 1.65        | 2.03  |

- 1 - GATE
- 2 - DRAIN (COLLECTOR)
- 3 - SOURCE (EMITTER)
- 4 - NO CONNECTION


NOTE: This drawing will meet all dimensions requirement of JEDEC outline TO-247AD except screw hole.

Note 1: Pulse test,  $t \leq 300\mu\text{s}$ ; duty cycle,  $d \leq 2\%$ .


IXYS reserves the right to change limits, test conditions, and dimensions.

|                                                                                  |           |           |           |           |              |              |              |              |              |             |
|----------------------------------------------------------------------------------|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: | 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
|                                                                                  | 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
|                                                                                  | 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |


**Fig. 1. Output Characteristics  
@ 25°C**




**Fig. 2. Extended Output Characteristics  
@ 25°C**




**Fig. 3. Output Characteristics  
@ 125°C**




**Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 16A$  Value  
vs. Junction Temperature**









**Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 16A$  Value  
vs. Drain Current**



**Fig. 6. Maximum Drain Current vs.  
Case Temperature**



**Fig. 7. Input Admittance**

**Fig. 8. Transconductance**

**Fig. 9. Forward Voltage Drop of Intrinsic Diode**

**Fig. 10. Gate Charge**

**Fig. 11. Capacitance**

**Fig. 12. Maximum Transient Thermal Impedance**




---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).