
IXYS

X3-Class HiPerFET™ Power MOSFET


IXFK400N15X3
IXFX400N15X3

V_{DSS} = 150V
I_{D25} = 400A
$R_{DS(on)}$ ≤ 3mΩ


N-Channel Enhancement Mode
Avalanche Rated



TO-264K (IXFK)



PLUS247 (IXFX)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	150	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	150	V
V_{GSS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C (Chip Capability)	400	A
$I_{L(RMS)}$	External Lead Current Limit	160	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	900	A
I_A	T_C = 25°C	200	A
E_{AS}	T_C = 25°C	3.5	J
dv/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$	50	V/ns
P_D	T_C = 25°C	1250	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering 1.6 mm (0.062 in.) from Case for 10s	300	°C
M_d	Mounting Torque (TO-264K)	1.13/10	Nm/lb.in
F_C	Mounting Force (PLUS247)	20..120 /4.5..27	N/lb
Weight	TO-264K	10	g
	PLUS247	6	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 3mA	150			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 8mA	2.5		4.5	V
I_{GSS}	V_{GS} = ±20V, V_{DS} = 0V			±200	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			25	μA
	T_J = 125°C			1.5	mA
$R_{DS(on)}$	V_{GS} = 10V, $I_D = 0.5 \bullet I_{D25}$, Note 1			3	mΩ

Features

- International Standard Packages
- Low $R_{DS(ON)}$ and Q_G
- Avalanche Rated
- Low Package Inductance

Advantages

- High Power Density
- Easy to Mount
- Space Savings

Applications

- Switch-Mode and Resonant-Mode Power Supplies
- DC-DC Converters
- PFC Circuits
- AC and DC Motor Drives
- Robotics and Servo Controls

© 2023 Littelfuse, Inc.

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max	
g_{fs}	V_{DS} = 10V, I_D = 60A, Note 1	85	145		S
R_{Gi}	Gate Input Resistance		2.15		Ω
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		23.7		nF
C_{oss}			3730		PF
C_{rss}			140		pF
	Effective Output Capacitance				
$C_{o(er)}$	Energy related; V_{GS} = 0V, V_{DS} = 0.8 • V_{DSS}		2200		pF
$C_{o(tr)}$	Time related; V_{GS} = 0V, V_{DS} = 0.8 • V_{DSS}		5330		pF
$t_{d(on)}$	**Resistive Switching Times**		36		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		30		ns
$t_{d(off)}$	R_G = 1Ω (External)		210		ns
t_f			19		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		365		nC
Q_{gs}			103		nC
Q_{gd}			87		nC
R_{thJC}				0.10	°C/W
R_{thCS}			0.15		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max	
I_S	V_{GS} = 0V			400	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			1600	A
V_{SD}	I_F = 100A, V_{GS} = 0V, Note 1			1.4	V
t_{rr}	I_F = 150A, -di/dt = 100A/μs		132		ns
Q_{RM}	V_R = 100V		580		nC
I_{RM}			8.8		A

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

Littelfuse reserves the right to change limits, test conditions, and dimensions.

LF MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123B1 6,306,728B1 6,404,065B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478B2 7,005,734B2 7,063,975B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 125ºC




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 200A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 200A Value vs. Drain Current





Fig. 6. Normalized Breakdown & Threshold Voltages vs. Junction Temperature



© 2023 Littelfuse, Inc.

Fig. 7. Maximum Drain Current vs. Case Temperature




Fig. 8. Input Admittance




Fig. 9. Transconductance




Fig. 10. Forward Voltage Drop of Intrinsic Diode




Fig. 11. Gate Charge





Fig. 12. Capacitance



Littelfuse reserves the right to change limits, test conditions, and dimensions.

Fig. 13. Output Capacitance Stored Energy




Fig. 14. Forward-Bias Safe Operating Area






Fig. 15. Maximum Transient Thermal Impedance



© 2023 Littelfuse, Inc.


TO-264K Outline



1 - Gate
2,4 - Drain
3 - Source

SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.189	0.205	4.80	5.20
A1	0.098	0.122	2.50	3.10
b	0.035	0.049	0.90	1.25
b1	0.091	0.106	2.30	2.70
b2	0.110	0.126	2.80	3.20
c	0.020	0.033	0.50	0.85
D	1.016	1.031	25.80	26.20
E	0.780	0.795	19.80	20.20
e	0.203	0.226	5.15	5.75
L	0.768	0.807	19.50	20.50
L1	0.094	0.102	2.40	2.60
ØP	0.118	0.134	3.00	3.40
Q	0.228	0.244	5.80	6.20
Q1	0.346	0.362	8.80	9.20
E1	0.701	0.717	17.80	18.20
D1	0.811	0.827	20.60	21.00
G	0.087	0.102	2.20	2.60
ØR	0.079		2.00	
ØR1	0.039		1.00	

PLUS247™ Outline



1 - Gate
2,4 - Drain
3 - Source

SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.190	.205	4.83	5.21
A1	.090	.100	2.29	2.54
A2	.075	.085	1.91	2.16
b	.045	.055	1.14	1.40
b2	.075	.087	1.91	2.20
b4	.115	.126	2.92	3.20
C	.024	.031	0.61	0.80
D	.819	.840	20.80	21.34
D1	.650	.690	16.51	17.53
D2	.035	.050	0.89	1.27
E	.620	.635	15.75	16.13
E1	.520	.560	13.08	14.22
e	.215 BSC		5.45 BSC	
L	.780	.810	19.81	20.57
L1	.150	.170	3.81	4.32
Q	.220	.244	5.59	6.20
R	.170	.190	4.32	4.83

Littelfuse reserves the right to change limits, test conditions, and dimensions.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2023 Littelfuse, Inc.