
XPT IGBT

V_{CES} = 1200V
I_{C25} = 58A
$V_{CE(sat)}$ = 1.8V


Copack

Part number

IXA33IF1200HB



Backside: collector



Features / Advantages:

- Easy paralleling due to the positive temperature coefficient of the on-state voltage
- Rugged XPT design (Xtreme light Punch Through) results in:
  - short circuit rated for 10 µsec.
  - very low gate charge
  - low EMI
  - square RBSOA @ 3x Ic
- Thin wafer technology combined with the XPT design results in a competitive low VCE(sat)
- SONIC™ diode
  - fast and soft reverse recovery
  - low operating forward voltage

Applications:

- AC motor drives
- Solar inverter
- Medical equipment
- Uninterruptible power supply
- Air-conditioning systems
- Welding equipment
- Switched-mode and resonant-mode power supplies
- Inductive heating, cookers
- Pumps, Fans

Package: TO-247

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0


© 2010 IXYS all rights reserved

IGBT				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V_{CES}	*collector emitter voltage*		T_{VJ} = 25°C			1200	V
V_{GES}	*max. DC gate voltage*					±20	V
V_{GEM}	*max. transient gate emitter voltage*					±30	V
I_{C25}	*collector current*		T_C = 25°C			58	A
I_{C80}			T_C = 80°C			34	A
P_{tot}	*total power dissipation*		T_C = 25°C			250	W
$V_{CE(sat)}$	*collector emitter saturation voltage*	I_C = 25A; V_{GE} = 15 V	T_{VJ} = 25°C		1.8	2.1	V
			T_{VJ} = 125°C		2.1		V
$V_{GE(th)}$	*gate emitter threshold voltage*	I_C = 1mA; V_{GE} = V_{CE}	T_{VJ} = 25°C	5.4	5.9	6.5	V
I_{CES}	*collector emitter leakage current*	V_{CE} = V_{CES}; V_{GE} = 0 V	T_{VJ} = 25°C			0.1	mA
			T_{VJ} = 125°C		0.1		mA
I_{GES}	*gate emitter leakage current*	V_{GE} = ±20 V				500	nA
$Q_{G(on)}$	*total gate charge*	V_{CE} = 600 V; V_{GE} = 15 V; I_C = 25 A			76		nC
$t_{d(on)}$	*turn-on delay time*				70		ns
t_r	*current rise time*				40		ns
$t_{d(off)}$	*turn-off delay time*	inductive load	T_{VJ} = 125°C		250		ns
t_f	*current fall time*	V_{CE} = 600 V; I_C = 25 A			100		ns
E_{on}	*turn-on energy per pulse*	V_{GE} = ±15 V; R_G = 39 Ω			2.5		mJ
E_{off}	*turn-off energy per pulse*				3		mJ
RBSOA	*reverse bias safe operating area*	V_{GE} = ±15 V; R_G = 39 Ω	T_{VJ} = 125°C				
I_{CM}		V_{CEmax} = 1200 V				75	A
SCSOA	*short circuit safe operating area*	V_{CEmax} = 900 V					
t_{SC}	*short circuit duration*	V_{CE} = 900 V; V_{GE} = ±15 V	T_{VJ} = 125°C			10	µs
I_{SC}	*short circuit current*	R_G = 39 Ω; non-repetitive			100		A
R_{thJC}	*thermal resistance junction to case*					0.5	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.25		K/W
Diode							
V_{RRM}	*max. repetitive reverse voltage*		T_{VJ} = 25°C			1200	V
I_{F25}	*forward current*		T_C = 25°C			60	A
I_{F80}			T_C = 80°C			33	A
V_F	*forward voltage*	I_F = 30A	T_{VJ} = 25°C			2.20	V
			T_{VJ} = 125°C		1.95		V
I_R	*reverse current*	V_R = V_{RRM}	T_{VJ} = 25°C			*	mA
	* not applicable, see Ices value above		T_{VJ} = 125°C		*		mA
Q_{rr}	*reverse recovery charge*	V_R = 600 V			3.5		µC
I_{RM}	*max. reverse recovery current*	-di_F/dt = -600 A/µs	T_{VJ} = 125°C		30		A
t_{rr}	*reverse recovery time*	I_F = 30A; V_{GE} = 0 V			350		ns
E_{rec}	*reverse recovery energy*				0.9		mJ
R_{thJC}	*thermal resistance junction to case*					0.7	K/W
R_{thCH}	*thermal resistance case to heatsink*				0.25		K/W

© 2010 IXYS all rights reserved

Package TO-247			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
I_{RMS}	*RMS current*	per terminal			70	A
T_{VJ}	*virtual junction temperature*		-40		150	°C
T_{op}	*operation temperature*		-40		125	°C
T_{stg}	*storage temperature*		-40		150	°C
Weight				6		g
M_D	*mounting torque*		0.8		1.2	Nm
F_C	*mounting force with clip*		20		120	N

Product Marking




Part number

I = IGBT
X = XPT IGBT
A = Gen 1 / std
33 = Current Rating [A]
IF = Copack
1200 = Reverse Voltage [V]
HB = TO-247AD (3)

Ordering	Part Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	IXA33IF1200HB	IXA33IF1200HB	Tube	30	508562


Equivalent Circuits for Simulation ** on die level* T_{VJ} = 150 °C




		IGBT	Diode	
$V_{0\,max}$	*threshold voltage*	1.1	1.25	V
$R_{0\,max}$	*slope resistance **	55	28.3	mΩ

© 2010 IXYS all rights reserved

Outlines TO-247



Sym.	Inches		Millimeter	
	min.	max.	min.	max.
A	0.185	0.209	4.70	5.30
A1	0.087	0.102	2.21	2.59
A2	0.059	0.098	1.50	2.49
D	0.819	0.845	20.79	21.45
E	0.610	0.640	15.48	16.24
E2	0.170	0.216	4.31	5.48
e	0.215 BSC		5.46 BSC	
L	0.780	0.800	19.80	20.30
L1	-	0.177	-	4.49
Ø P	0.140	0.144	3.55	3.65
Q	0.212	0.244	5.38	6.19
S	0.242 BSC		6.14 BSC	
b	0.039	0.055	0.99	1.40
b2	0.065	0.094	1.65	2.39
b4	0.102	0.135	2.59	3.43
c	0.015	0.035	0.38	0.89
D1	0.515	-	13.07	-
D2	0.020	0.053	0.51	1.35
E1	0.530	-	13.45	-
Ø P1	-	0.29	-	7.39



© 2010 IXYS all rights reserved

IGBT




Fig. 1 Typ. output characteristics




Fig. 2 Typ. output characteristics




Fig. 3 Typ. tranfer characteristics




Fig. 4 Typ. turn-on gate charge




Fig. 5 Typ. switching energy vs. collector current




Fig. 6 Typ. switching energy vs. gate resistance

© 2010 IXYS all rights reserved

Diode




Fig. 7 Typ. Forward current versus V_F




Fig. 8 Typ. reverse recov.charge Q_{rr} vs. di/dt




Fig. 9 Typ. peak reverse current I_{RM} vs. di/dt




Fig. 10 Typ. recovery time t_{rr} versus di/dt




Fig.11 Typ. recovery energy E_{rec} versus di/dt




Fig. 12 Typ. transient thermal impedance

© 2010 IXYS all rights reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.