


LSIC2SD065A08A 650 V, 8 A SiC Schottky Barrier Diode




Agency Approvals and Environmental

Environmental Approvals



Circuit Diagram TO-220-2L



Product Summary

| Characteristic | Value | Unit |
|------------------------------------|-------|------|
| V_{RRM} | 650 | V |
| $I_F (T_c \leq 135^\circ\text{C})$ | 11 | A |
| $Q_C (V_R: 0 - 400\text{ V})$ | 28 | nC |

Features

- AEC-Q101 qualified
- Positive temperature coefficient for safe operation and ease of paralleling
- 175 °C maximum operating junction temperature
- Excellent surge capability
- Extremely fast, temperature-independent switching behavior
- Dramatically reduced switching losses compared to Si bipolar diodes
- RoHS compliant, lead-free, and halogen-free

Applications

- Boost diodes in PFC or DC/DC stages
- Switch-mode power supplies
- Solar inverters
- Uninterruptable power supplies
- Industrial motor drives
- Battery chargers
- High speed rectifier

- 1. Maximum Ratings.....3
- 2. Thermal Characteristics3
- 3. Electrical Characteristics ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified)3
- 4. Performance Curves4
- 5. Diode V_F Model for Simulation5
- 6. Package Dimensions6
- 7. Part Numbering and Marking.....7
- 8. Packing Options7
- 9. Packing Specifications7

1. Maximum Ratings

| Characteristic | Symbol | Conditions | Value | Unit |
|--------------------------------------|---------------|---|------------|------------------|
| Repetitive Peak Reverse Voltage | V_{RRM} | - | 650 | V |
| DC Blocking Voltage | V_R | - | 650 | V |
| Continuous Forward Current | I_F | $T_C = 25\text{ }^\circ\text{C}$ | 24 | A |
| | | $T_C = 135\text{ }^\circ\text{C}$ | 11 | |
| | | $T_C = 152\text{ }^\circ\text{C}$ | 8 | |
| Non-repetitive Forward Surge Current | I_{FSM} | $T_C = 25\text{ }^\circ\text{C}$, $t_p = 10\text{ ms}$, Half sine pulse | 40 | A |
| I^2t | $\int I^2 dt$ | $T_C = 25\text{ }^\circ\text{C}$, $t_p = 10\text{ ms}$, Half sine pulse | 8 | A ² s |
| Power Dissipation | P_{Tot} | $T_C = 25\text{ }^\circ\text{C}$ | 88 | W |
| | | $T_C = 110\text{ }^\circ\text{C}$ | 38 | |
| Operating Junction Temperature | T_J | - | -55 to 175 | $^\circ\text{C}$ |
| Storage Temperature | T_{STG} | - | -55 to 150 | $^\circ\text{C}$ |
| Lead Temperature for Soldering | T_{SOLD} | - | 260 | $^\circ\text{C}$ |
| Mounting Torque | M_D | M3 or 6-32 screw | 1.0 | Nm |
| | | | 8.8 | In-lb |

2. Thermal Characteristics

| Characteristic | Symbol | Value | Unit |
|----------------------------|-----------------|-------|--------------------|
| Maximum Thermal Resistance | $R_{th,Jc,max}$ | 1.7 | $^\circ\text{C/W}$ |

3. Electrical Characteristics ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified)

| Characteristic | Symbol | Conditions | Value | | | Unit |
|---------------------------|--------|--|-------|------|-----|---------------|
| | | | Min | Typ | Max | |
| Forward Voltage | V_F | $I_F = 8\text{ A}$, $T_J = 25\text{ }^\circ\text{C}$ | - | 1.5 | 1.8 | V |
| | | $I_F = 8\text{ A}$, $T_J = 175\text{ }^\circ\text{C}$ | - | 1.75 | - | |
| Reverse Current | I_R | $V_R = 650\text{ V}$, $T_J = 25\text{ }^\circ\text{C}$ | - | <1 | 100 | μA |
| | | $V_R = 650\text{ V}$, $T_J = 175\text{ }^\circ\text{C}$ | - | 15 | - | |
| Total Capacitance | C | $V_R = 1\text{ V}$, $f = 1\text{ MHz}$ | - | 415 | - | pF |
| | | $V_R = 200\text{ V}$, $f = 1\text{ MHz}$ | - | 56 | - | |
| | | $V_R = 400\text{ V}$, $f = 1\text{ MHz}$ | - | 41 | - | |
| Total Capacitive Charge | Q_C | $V_R = 400\text{ V}$, $Q_C = \int C(V) dV$ | - | 28 | - | nC |
| Capacitance Stored Energy | E_C | $V_R = 400\text{ V}$ | - | 3.3 | - | μJ |

4. Performance Curves

Figure 1. Typical Forward Characteristics




Figure 2. Typical Reverse Characteristics




Figure 3. Power Derating




Figure 4. Current Derating




Figure 5. Capacitance vs. Reverse Voltage




Figure 6. Capacitive Charge vs. Reverse Voltage




Figure 7. Stored Energy vs. Reverse Voltage






Figure 8. Transient Thermal Impedance



5. Diode V_F Model for Simulation



$$V_F(T_J) = V_0 + IR_0$$

$$V_0 = -1.17 \times 10^{-3} \cdot T_J + 1.03 \times 10^0$$


$$R_0 = 1.28 \times 10^{-6} \cdot T_J^2 + 6.61 \times 10^{-5} \cdot T_J + 6.02 \times 10^{-2}$$

Notes:

- T_J is junction temperature in °C
- Range valid from 25 °C to 175 °C
- Model represents performance of a typical part

6. Package Dimensions

TO-220-2L Package




| Symbol | Millimeters | | |
|--------|-------------|-------|-------|
| | Min | Nom | Max |
| A | 4.30 | 4.50 | 4.70 |
| A1 | 1.25 | 1.30 | 1.40 |
| A2 | 2.20 | 2.40 | 2.60 |
| b | 0.70 | 0.80 | 0.90 |
| b2 | 1.17 | 1.27 | 1.37 |
| c | 0.45 | 0.50 | 0.60 |
| D | 15.50 | 15.70 | 15.90 |
| D1 | 9.00 | 9.20 | 9.40 |
| D2 | (12.70) | | |
| E* | 9.70 | 9.90 | 10.10 |
| E1 | (8.00) | | |
| E2 | (0.60) | | |
| E3 | 9.70 | 9.90 | 10.10 |
| e | 2.54 BSC | | |
| e1 | 5.08 BSC | | |
| H1 | 6.30 | 6.50 | 6.70 |
| L | 12.88 | 13.08 | 13.28 |
| L1 | (3.00) | | |
| L2 | - | - | 0.80 |
| øP | 3.50 | 3.60 | 3.70 |
| Q | 2.70 | 2.80 | 2.90 |

Notes:

- These dimensions do not include protrusions of the mold.
- The “()” mark is the reference.
- The “L2” symbol is a protrusion of the mold.

7. Part Numbering and Marking




- Sic = SiC Diode
- 2 = Gen2
- SD = Schottky Diode
- 065 = Voltage Rating (650 V)
- A = TO-220-2L
- 08 = Current Rating (8 A)
- A = AEC-Q101 Qualified
- YY = Year
- WW = Week
- X = Special Code
- ZZZZZ-ZZ = Lot Number

8. Packing Options

| Part Number | Marking | Packing Mode | M.O.Q. |
|----------------|---------------|---------------|--------|
| LSIC2SD065A08A | SIC2SD065A08A | Tube (50 pcs) | 1000 |

9. Packing Specifications

Tube for TO-220-2L



NOTE]

- TUBE
 - MATERIAL : PVC / PET (WITH ANTISTATIC COATING)
 - COLOR : TRANSPARENCY, RED, YELLOW
 - MARKING #A : BLACK COLOR, LETTER STYLE : Arial
 - Tube Surface Resistance : $10^9 \sim 10^{11} \Omega$ /square
 - ESD (Electro Static Discharge) : less than 100 [volts], 6 Months
 - CAMBAR : 1.5 MAX
- PIN
 - COLOR : GREEN (ONE PIN MUST BE INSERTED IN LEFT-SIDE OF "ANTISTATIC-" AND ANOTHER PIN IS FREE.)

For additional information please visit www.Littelfuse.com/powersemi

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation.

Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics