
OBSOLETE

IXYS
INTEGRATED CIRCUITS DIVISION



LDA203

Dual Optocouplers, Unidirectional Input Single-Transistor Output

Parameter	Rating	Units
Breakdown Voltage - BV_{CEO}	30	V_P
Current Transfer Ratio - CTR (Typ)	300	%
Saturation Voltage - $V_{CE(sat)}$	0.5	V
Input Control Current - I_F	1	mA

Description

LDA203 is a dual unidirectional-input optocoupler with single-transistor outputs. Current transfer ratios range from 33% to 1000% with a typical value of 300%.

Features

- 100mA Continuous Load Rating
- $3750V_{rms}$ Input/Output Isolation
- Unidirectional Input
- Small 8-Pin Package
- Tape & Reel Version Available

Approvals

- UL Recognized Component: File E76270
- CSA Certified Component: Certificate # 1175739
- TUV EN 62368-1: Certificate # B 082667 0008


Ordering Information

Part Number	Description
LDA203	8-Pin DIP (50/tube)
LDA203S	8-Pin Surface Mount (50/tube)
LDA203STR	8-Pin Surface Mount (1000/Reel)

Applications

- Telecom Switching
- Tip/Ring Circuits
- Modem Switching (Laptop, Notebook, Pocket Size)
- Loop Detect
- Ringing Detect
- Current Sensing

Pin Configuration



OBSOLETE

Absolute Maximum Ratings @ 25ºC

Parameter	Ratings	Units
Breakdown Voltage	30	V_P
Reverse Input Voltage	5	V
Input Control Current	100	mA
Peak (10ms)	1	A
Power Dissipation		
Input (each) [1]	150	mW
Phototransistor (each) [2]	150	mW
Isolation Voltage, Input to Output	3750	V_{rms}
Operational Temperature, Ambient	-40 to +85	ºC
Storage Temperature	-40 to +125	ºC

[1] Derate linearly 1.33mW / ºC
[2] Derate linearly 2mW / ºC

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Typical values are characteristic of the device at +25°C, and are the result of engineering evaluations. They are provided for information purposes only, and are not part of the manufacturing testing requirements.


Electrical Characteristics @ 25ºC


Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics						
Phototransistor Breakdown Voltage	I_C = 10µA	BV_{CEO}	30	85	-	V
Phototransistor Dark Current	V_{CEO} = 5V, I_F = 0mA	I_{CEO}	-	10	500	nA
Saturation Voltage	I_C = 2mA, I_F = 1mA	$V_{CE(sat)}$	-	0.3	0.5	V
Current Transfer Ratio	I_F = 1mA, V_{CE} = 0.5V	CTR	33	300	1000	%
Output Capacitance	25V, f =1MHz	C_{OUT}	-	6	-	pF
Input Characteristics						
Input Control Current	I_C = 0.33mA, V_{CE} = 0.5V	I_F	-	-	1	mA
Input Voltage Drop	I_F = 5mA	V_F	0.9	1.2	1.4	V
Reverse Input Current	V_R = 5V	I_R	-	-	10	µA
Common Characteristics						
Capacitance, Input to Output	-	$C_{I/O}$	-	3	-	pF

Switching Characteristics @ 25ºC

Characteristic	Symbol	Test Condition	Typ	Units
Turn-On Time	t_{on}	V_{CC}=5V, I_F=2mA, R_L=1KΩ	7	µs
Turn-Off Time	t_{off}		20	

Switching Time Test Circuit







OBSOLETE

PERFORMANCE DATA*


LED Voltage vs. Current (Linear)




LED Voltage vs. Current (Log)




LED Forward Voltage vs. Temperature




Typical CTR vs. LED Forward Current (V_{CE}=5V)




Typical Collector Current vs. Collector Voltage




I_{CE} Current vs. Temperature (V_{CE}=5V)




Saturation Voltage vs. Temperature (I_F=2mA, I_C=1mA)




Blocking Voltage vs. Temperature




Collector Leakage Current vs. Temperature



Turn-On Time vs. Load Resistance (V_{CC}=5V)



Turn-Off Time vs. Load Resistance (V_{CC}=5V)



OBSOLETE

* Unless otherwise noted, data presented in these graphs is typical of device operation at 25ºC.

Manufacturing Information

Moisture Sensitivity

All plastic encapsulated semiconductor packages are susceptible to moisture ingression. IXYS Integrated Circuits classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, **IPC/JEDEC J-STD-020**, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a **Moisture Sensitivity Level (MSL)** classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification
LDA203S	MSL 1

ESD Sensitivity

This product is ESD Sensitive, and should be handled according to the industry standard **JESD-625**.

Soldering Profile

Provided in the table below is the **IPC/JEDEC J-STD-020** Classification Temperature (T_C) and the maximum total dwell time (t_P) in all reflow processes that the body temperature of these surface mount devices may be (T_C - 5)°C or greater. The device's body temperature must not exceed the Classification Temperature at any time during reflow soldering processes.

Device	Classification Temperature (T_c)	Dwell Time (t_P)	Max Reflow Cycles
LDA203S	250°C	30 seconds	3

For through-hole devices, the maximum pin temperature and maximum dwell time through all solder waves is provided in the table below. Dwell time is the interval beginning when the pins are initially immersed into the solder wave until they exit the solder wave. For multiple waves, the dwell time is from entering the first wave until exiting the last wave. During this time, pin temperatures must not exceed the maximum temperature given in the table below. Body temperature of the device must not exceed the limit shown in the table below at any time during the soldering process.

Device	Maximum Pin Temperature	Maximum Body Temperature	Maximum Dwell Time	Wave Cycles
LDA203	260°C	250°C	10 seconds*	1

*Total cumulative duration of all waves.

Board Wash


IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to halide flux or solvents.

Pb RoHS e3


OBSOLETE

Mechanical Dimensions

LDA203




LDA203S



OBSOLETE

LDA203STR Tape & Reel



NOTES:
1. Dimensions carry tolerances of EIA Standard 481-2
2. Tape complies with all "Notes" for constant dimensions listed on page 5 of EIA-481-2

OBSOLETE

For additional information please visit our website at: https://www.ixysic.com

IXYS
A Littelfuse Technology

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications.
Read complete Disclaimer Notice at https://www.littelfuse.com/disclaimer-electronics.

Specification: DS-LDA203-ROBS
©Copyright 2023, Littelfuse, Inc.
All rights reserved. Printed in USA.
2/7/2023