

LSIC2SD120A10A
1200 V, 10 A SiC Schottky Barrier Diode



Agency Approvals and Environmental

Environmental Approvals
RoHS HF

Circuit Diagram TO-220-2L



Product Summary

Characteristic	Value	Unit
V_{RRM}	1200	V
I_F ($T_C \leq 135$ °C)	15	A
Q_C (V_R: 0 – 800 V)	56	nC

Features

- AEC-Q101 qualified
- Positive temperature coefficient for safe operation and ease of paralleling
- 175 °C maximum operating junction temperature
- Excellent surge capability
- Extremely fast, temperature-independent switching behavior
- Dramatically reduced switching losses compared to Si bipolar diodes
- RoHS compliant, lead-free, and halogen-free

Applications

- Boost diodes in PFC or DC/DC stages
- Switch-mode power supplies
- Solar inverters
- Uninterruptable power supplies
- Industrial motor drives
- Battery chargers
- High speed rectifier

Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021

1. Maximum Ratings....3
2. Thermal Characteristics....3
3. Electrical Characteristics (T_J = 25 °C unless otherwise specified)....3
4. Performance Curves....4
5. Diode V_F Model for Simulation....5
6. Package Dimensions....6
7. Part Numbering and Marking....6
8. Packing Options....6
9. Packing Specifications....7

Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021

1. Maximum Ratings

Characteristic	Symbol	Conditions	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	-	1200	V
DC Blocking Voltage	V_R	-	1200	V
Continuous Forward Current	I_F	T_C = 25 °C	32	A
		T_C = 135 °C	15	
		T_C = 154 °C	10	
Non-repetitive Forward Surge Current	I_{FSM}	T_C = 25 °C, t_p = 10 ms, Half sine pulse	80	A
I^2t	$\int I^2dt$	T_C = 25 °C, t_p = 10 ms, Half sine pulse	32	A^2s
Power Dissipation	P_{Tot}	T_C = 25 °C	150	W
		T_C = 110 °C	65	
Operating Junction Temperature	T_J	-	-55 to 175	°C
Storage Temperature	T_{STG}	-	-55 to 150	°C
Lead Temperature for Soldering	T_{SOLD}	-	260	°C
Mounting Torque	M_D	M3 or 6-32 screw	1.0	Nm
			8.8	in-lb

2. Thermal Characteristics

Characteristic	Symbol	Value	Unit
Maximum Thermal Resistance	$R_{th,JC,\ max}$	1.0	°C/W

3. Electrical Characteristics (T_J = 25 °C unless otherwise specified)

Characteristic	Symbol	Conditions	Value			Unit
			Min	Typ	Max	
Forward Voltage	V_F	I_F = 10 A, T_J = 25 °C	-	1.5	1.8	V
		I_F = 10 A, T_J = 175 °C	-	2	-	
Reverse Current	I_R	V_R = 1200 V, T_J = 25 °C	-	<1	100	µA
		V_R = 1200 V, T_J = 175 °C	-	4	-	
Total Capacitance	C	V_R = 1 V, f = 1 MHz	-	580	-	pF
		V_R = 400 V, f = 1 MHz	-	53	-	
		V_R = 800 V, f = 1 MHz	-	40	-	
Total Capacitive Charge	Q_C	V_R = 800 V, $Q_C = \int C(V)\,dV$	-	56	-	nC
Capacitance Stored Energy	E_C	V_R = 800 V		12.8		µJ

Littelfuse Expertise Applied | Answers Delivered
IXYS A Littelfuse Technology
Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021

4. Performance Curves

Figure 1. Typical Forward Characteristics




Figure 2. Typical Reverse Characteristics




Figure 3. Power Derating




Figure 4. Current Derating




Figure 5. Capacitance vs. Reverse Voltage





Figure 6. Capacitive Charge vs. Reverse Voltage



Littelfuse Expertise Applied | Answers Delivered
IXYS A Littelfuse Technology
Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021

Figure 7. Stored Energy vs. Reverse Voltage






Figure 8. Transient Thermal Impedance



5. Diode V_F Model for Simulation



$$V_F(T_J) = V_0 + IR_0$$
$$V_0 = -1.11 \times 10^{-3} \cdot T_J + 1.01 \times 10^{0}$$
$$R_0 = 1.61 \times 10^{-6} \cdot T_J^2 + 1.50 \times 10^{-4} \cdot T_J + 4.35 \times 10^{-2}$$


Notes:

- T_J is junction temperature in °C
- Range valid from 25 °C to 175 °C
- Model represents performance of a typical part

Littelfuse Expertise Applied | Answers Delivered
IXYS A Littelfuse Technology
Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021


6. Package Dimensions

TO-220-2L Package



Symbol	Millimeters		
	Min	Nom	Max
A	4.30	4.45	4.70
A1	1.14	1.27	1.40
A2	2.20	-	2.74
b	0.69	-	0.90
b2	1.17	-	1.62
c	0.36	-	0.60
D	14.90	-	15.90
D1	8.62	-	9.40
D2	12.50	-	12.95
E	9.70	10.18	10.36
E1	7.57	7.61	8.30
e1	-	2.54	-
e	5.03	5.08	5.13
H1	6.30	6.55	6.80
L	12.88	13.50	14.00
L1	2.39	-	3.25
øP	3.50	3.84	3.96
Q	2.65	-	3.05
R	-	-	0.25

7. Part Numbering and Marking



Sic	= SiC Diode
2	= Gen2
SD	= Schottky Diode
120	= Voltage Rating (1200 V)
A	= TO-220-2L
10	= Current Rating (10 A)
A	= AEC-Q101 Qualified
YY	= Year
WW	= Week
X	= Special Code
ZZZZZZ-ZZ	= Lot Number


8. Packing Options

Part Number	Marking	Packing Mode	M.O.Q.
LSIC2SD120A10A	SIC2SD120A10A	Tube (50 pcs)	1000

Littelfuse Expertise Applied | Answers Delivered
IXYS A Littelfuse Technology
Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021

9. Packing Specifications

Tube for TO-220-2L



NOTE]

TUBE
- MATERIAL : PVC / PET (WITH ANTISTATIC COATING)
- COLOR : TRANSPARENCY, RED, YELLO
- MARKING #A : BLACK COLOR, LETTER STYLE : Arial
- Tube Surface Resistance :10^{8}~10^{11}Ω/square
- ESD (Electro Static Discharge) : less than 100 [volts], 6 Months
- CAMBAR : 1.5 MAX

PIN
- COLOR : GREEN (ONE PIN MUST BE INSERTED IN LEFT-SIDE OF "□ANTISTATIC~" AND ANOTHER PIN IS FREE.)

For additional information please visit www.Littelfuse.com/powersemi

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation.

Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics

Specifications are subject to change without notice.
Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.
© 2021 Littelfuse, Inc.
Revised: 8/31/2021