IXYS


Preliminary Technical Information

TrenchT2™ GigaMOS™ Power MOSFET


IXTN550N055T2

V_{DSS} = 55V
I_{D25} = 550A
$R_{DS(on)}$ ≤ 1.30mΩ

N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Diode



miniBLOC, SOT-227
E153432



G = Gate D = Drain
S = Source

Either Source Terminal S can be used as the Source Terminal or the Kelvin Source (Gate Return) Terminal.

Symbol	Test Conditions		Maximum Ratings	
V_{DSS}	T_J = 25°C to 175°C		55	V
V_{DGR}	T_J = 25°C to 175°C, R_{GS} = 1MΩ		55	V
V_{GSS}	Continuous		±20	V
V_{GSM}	Transient		±30	V
I_{D25}	T_C = 25°C (Chip Capability)		550	A
$I_{L(RMS)}$	External Lead Current Limit		200	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}		1650	A
I_A	T_C = 25°C		200	A
E_{AS}	T_C = 25°C		3	J
P_D	T_C = 25°C		940	W
T_J			-55 ... +175	°C
T_{JM}			175	°C
T_{stg}			-55 ... +175	°C
T_L	1.6mm (0.062 in.) from Case for 10s		300	°C
T_{SOLD}	Plastic Body for 10s		260	°C
V_{ISOL}	50/60 Hz, RMS	t = 1 minute	2500	V~
	I_{ISOL} ≤ 1mA	t = 1 second	3000	V~
M_d	Mounting Torque		1.5/13	Nm/lb.in.
	Terminal Connection Torque		1.3/11.5	Nm/lb.in.
Weight			30	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 250μA	55			V
$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250μA	2.0		4.0	V
I_{GSS}	V_{GS} = ±20V, V_{DS} = 0V			±200	nA
I_{DSS}	V_{DS} = V_{DSS}, V_{GS} = 0V			10	μA
	T_J = 150°C			1	mA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 100A, Note 1		1.10	1.30	mΩ

Features

- International Standard Package
- miniBLOC, with Aluminium Nitride Isolation
- 175°C Operating Temperature
- Isolation Voltage 2500 V~
- High Current Handling Capability
- Fast Intrinsic Diode
- Avalanche Rated
- Low $R_{DS(on)}$

Advantages

- Easy to Mount
- Space Savings
- High Power Density

Applications

- DC-DC Converters and Off-Line UPS
- Primary-Side Switch
- High Speed Power Switching Applications

© 2009 IXYS CORPORATION, All Rights Reserved


Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10V, I_D = 60A, Note 1	90	150		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		40		nF
C_{oss}			4970		pF
C_{rss}			1020		pF
R_{Gi}	Gate Input Resistance		1.36		Ω
$t_{d(on)}$	**Resistive Switching Times** V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 200A R_G = 1Ω (External)		45		ns
t_r			40		ns
$t_{d(off)}$			90		ns
t_f			230		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{DSS}		595		nC
Q_{gs}			150		nC
Q_{gd}			163		nC
R_{thJC}				0.16	°C/W
R_{thCS}			0.05		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			550	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			1700	A
V_{SD}	I_F = 100A, V_{GS} = 0V, Note 1			1.2	V
t_{rr}	I_F = 100A, V_{GS} = 0V		100		ns
I_{RM}	-di/dt = 100A/μs		5		A
Q_{RM}	V_R = 27.5V		250		nC

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

SOT-227B (IXTN) Outline



(M4 screws (4x) supplied)

SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	1.240	1.255	31.50	31.88
B	.307	.323	7.80	8.20
C	.161	.169	4.09	4.29
D	.161	.169	4.09	4.29
E	.161	.169	4.09	4.29
F	.587	.595	14.91	15.11
G	1.186	1.193	30.12	30.30
H	1.496	1.505	38.00	38.23
J	.460	.481	11.68	12.22
K	.351	.378	8.92	9.60
L	.030	.033	0.76	0.84
M	.496	.506	12.60	12.85
N	.990	1.001	25.15	25.42
O	.078	.084	1.98	2.13
P	.195	.235	4.95	5.97
Q	1.045	1.059	26.54	26.90
R	.155	.174	3.94	4.42
S	.186	.191	4.72	4.85
T	.968	.987	24.59	25.07
U	-.002	.004	-0.05	0.1

PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,850,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC




Fig. 2. Extended Output Characteristics @ T_J = 25ºC




Fig. 3. Output Characteristics @ T_J = 150ºC




Fig. 4. Normalized $R_{DS(on)}$ vs. Junction Temperature




Fig. 5. Normalized $R_{DS(on)}$ vs. Drain Current





Fig. 6. Drain Current vs. Case Temperature



© 2009 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance




Fig. 12. Forward-Bias Safe Operating Area




Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature




Fig. 14. Resistive Turn-on Rise Time vs. Drain Current




Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance




Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature




Fig. 17. Resistive Turn-off Switching Times vs. Drain Current






Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance



© 2009 IXYS CORPORATION, All Rights Reserved

Fig. 19. Maximum Transient Thermal Impedance





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.