IXYS

Trench™ Power MOSFETs

IXTA56N15T
IXTP56N15T

V_{DSS} = 150V
I_{D25} = 56A
$R_{DS(on)}$ ≤ 36mΩ

N-Channel Enhancement Mode
Avalanche Rated
Fast Intrinsic Rectifier



TO-263 AA (IXTA)



TO-220AB (IXTP)



G = Gate D = Drain
S = Source Tab = Drain

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 175°C	150	V
V_{DGR}	T_J = 25°C to 175°C, R_{GS} = 1MΩ	150	V
V_{GSS}	Continuous	± 20	V
V_{GSM}	Transient	± 30	V
I_{D25}	T_C = 25°C	56	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	140	A
I_A	T_C = 25°C	5	A
E_{AS}	T_C = 25°C	500	mJ
dv/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 175°C$	3	V/ns
P_D	T_C = 25°C	300	W
T_J		-55 ... +175	°C
T_{JM}		175	°C
T_{stg}		-55 ... +175	°C
T_L	1.6mm (0.062in.) from Case for 10s	300	°C
T_{sold}	Plastic Body for 10 seconds	260	°C
M_d	Mounting Torque (TO-220)	1.13 / 10	Nm/lb.in.
Weight	TO-263	2.5	g
	TO-220	3.0	g

Symbol (T_J = 25°C Unless Otherwise Specified)	Test Conditions	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 250μA	150			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 250μA	3.0		5.0	V
I_{GSS}	V_{GS} = ± 20V, V_{DS} = 0V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			5	μA
	T_J = 150°C			200	μA
$R_{DS(on)}$	V_{GS} = 10V, $I_D = 0.5 \bullet I_{D25}$, Notes 1, 2			36	mΩ

Features

- International Standard Packages
- 175°C Operating Temperature
- High Current Handling Capability
- Avalanche Rated
- Fast Intrinsic Rectifier
- Dynamic dv/dt Rated
- Low $R_{DS(on)}$

Advantages

- Easy to Mount
- Space Savings
- High Power Density

Applications

- DC-DC Converters
- Battery Chargers
- Switch-Mode and Resonant-Mode Power Supplies
- DC Choppers
- AC Motor Drives
- Uninterruptible Power Supplies
- High Speed Power Switching Applications

© 2012 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
g_{fs}	V_{DS} = 10V, I_D = 0.5 • I_{D25}, Note 1	23	39		S
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		2250		pF
C_{oss}			330		pF
C_{rss}			50		pF
$t_{d(on)}$	**Resistive Switching Times**		16		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		17		ns
$t_{d(off)}$	R_G = 5Ω (External)		43		ns
t_f			18		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 25A		34		nC
Q_{gs}			10		nC
Q_{gd}			11		nC
R_{thJC}				0.50	°C/W
R_{thCH}	TO-220		0.50		°C/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
I_S	V_{GS} = 0V			56	A
I_{SM}	Repetitive, Pulse width limited by T_{JM}			160	A
V_{SD}	I_F = 25A, V_{GS} = 0V, Note 1			1.1	V
t_{rr}	I_F = 25A, V_{GS} = 0V -di/dt = 100A/μs, V_R = 50V		100		ns

Notes: 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.
2. On through-hole packages, $R_{DS(on)}$ Kelvin test contact location must be 5mm or less from the package body.

TO-263 Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.06	4.83	.160	.190
b	0.51	0.99	.020	.039
b2	1.14	1.40	.045	.055
c	0.40	0.74	.016	.029
c2	1.14	1.40	.045	.055
D	8.64	9.65	.340	.380
D1	8.00	8.89	.280	.320
E	9.65	10.41	.380	.405
E1	6.22	8.13	.270	.320
e	2.54	BSC	.100	BSC
L	14.61	15.88	.575	.625
L1	2.29	2.79	.090	.110
L2	1.02	1.40	.040	.055
L3	1.27	1.78	.050	.070
L4	0	0.13	0	.005

TO-220 Outline



Pins: 1 - Gate 2 - Drain
3 - Source

SYM	INCHES MIN	MAX	MILLIMETERS MIN	MAX
A	.170	.190	4.32	4.83
b	.025	.040	0.64	1.02
b1	.045	.065	1.15	1.65
c	.014	.022	0.35	0.56
D	.580	.630	14.73	16.00
E	.390	.420	9.91	10.66
e	.100 BSC		2.54 BSC	
F	.045	.055	1.14	1.40
H1	.230	.270	5.85	6.85
J1	.090	.110	2.29	2.79
k	0	.015	0	0.38
L	.500	.550	12.70	13.97
L1	.110	.230	2.79	5.84
ØP	.139	.161	3.53	4.08
Q	.100	.125	2.54	3.18

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123 B1 6,306,728 B1 6,404,065 B1 6,534,343 6,583,505 6,683,344 6,710,405 B2 6,710,463 6,727,585 6,759,692 6,771,478 B2 7,005,734 B2 7,063,975 B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25ºC



Fig. 2. Extended Output Characteristics @ T_J = 25ºC



Fig. 3. Output Characteristics @ T_J = 150ºC



Fig. 4. $R_{DS(on)}$ Normalized to I_D = 28A Value vs. Junction Temperature



Fig. 5. $R_{DS(on)}$ Normalized to I_D = 28A Value vs. Drain Current



Fig. 6. Drain Current vs. Case Temperature



© 2012 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance



Fig. 8. Transconductance



Fig. 9. Forward Voltage Drop of Intrinsic Diode



Fig. 10. Gate Charge



Fig. 11. Capacitance



Fig. 12. Maximum Transient Thermal Impedance



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Resistive Turn-on Rise Time vs. Junction Temperature



Fig. 14. Resistive Turn-on Rise Time vs. Drain Current



Fig. 15. Resistive Turn-on Switching Times vs. Gate Resistance



Fig. 16. Resistive Turn-off Switching Times vs. Junction Temperature



Fig. 17. Resistive Turn-off Switching Times vs. Drain Current



Fig. 18. Resistive Turn-off Switching Times vs. Gate Resistance



© 2012 IXYS CORPORATION, All Rights Reserved

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.