IXYS


X3-Class HiPerFET™ Power MOSFET

IXFP44N25X3M


V_{DSS} = 250V
I_{D25} = 44A
$R_{DS(on)}$ ≤ 40mΩ

(Electrically Isolated Tab)

N-Channel Enhancement Mode



OVERMOLDED TO-220



G = Gate D = Drain
S = Source

Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	250	V
V_{DGR}	T_J = 25°C to 150°C, R_{GS} = 1MΩ	250	V
V_{GSS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C, Limited by T_{JM}	44	A
I_{DM}	T_C = 25°C, Pulse Width Limited by T_{JM}	66	A
I_A	T_C = 25°C	22	A
E_{AS}	T_C = 25°C	400	mJ
dv/dt	$I_S \le I_{DM}$, $V_{DD} \le V_{DSS}$, $T_J \le 150°C$	50	V/ns
P_D	T_C = 25°C	34	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	Maximum Lead Temperature for Soldering	300	°C
T_{SOLD}	1.6 mm (0.062in.) from Case for 10s	260	°C
V_{ISOL}	50/60 Hz, 1 Minute	2500	V~
M_d	Mounting Torque	1.13 / 10	Nm/lb.in
Weight		2.5	g

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max.	
BV_{DSS}	V_{GS} = 0V, I_D = 1mA	250			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 1mA	2.5		4.5	V
I_{GSS}	V_{GS} = ±20V, V_{DS} = 0V			±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$, V_{GS} = 0V			15	μA
	T_J = 125°C			500	μA
$R_{DS(on)}$	V_{GS} = 10V, I_D = 22A, Note 1		31	40	mΩ

Features

- International Standard Package
- Plastic Overmolded Tab
- Low $R_{DS(ON)}$ and Q_G
- Avalanche Rated
- Low Package Inductance

Advantages

- High Power Density
- Easy to Mount
- Space Savings


Applications

- Switch-Mode and Resonant-Mode Power Supplies
- DC-DC Converters
- PFC Circuits
- AC and DC Motor Drives
- Robotics and Servo Controls

© 2019 IXYS CORPORATION, All Rights Reserved

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max	
g_{fs}	V_{DS} = 10V, I_D = 22A, Note 1	22	36		S
R_{Gi}	Gate Input Resistance		2.1		Ω
C_{iss}	V_{GS} = 0V, V_{DS} = 25V, f = 1MHz		2220		pF
C_{oss}			405		pF
C_{rss}			1		pF
	Effective Output Capacitance				
$C_{o(er)}$	Energy related: V_{GS} = 0V, V_{DS} = 0.8 • V_{DSS}		155		pF
$C_{o(tr)}$	Time related: V_{GS} = 0V, V_{DS} = 0.8 • V_{DSS}		615		pF
$t_{d(on)}$	**Resistive Switching Times**		18		ns
t_r	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 22A		23		ns
$t_{d(off)}$	R_G = 10Ω (External)		54		ns
t_f			12		ns
$Q_{g(on)}$	V_{GS} = 10V, V_{DS} = 0.5 • V_{DSS}, I_D = 22A		33		nC
Q_{gs}			9		nC
Q_{gd}			10		nC
R_{thJC}				3.7	°C/W
R_{thCS}			0.50		°C/W

OVERMOLDED TO-220 (IXFP...M)



Terminals: 1 - Gate
2 - Drain
3 - Source

SYM	INCHES MIN	INCHES MAX	MILLIMETERS MIN	MILLIMETERS MAX
A	.177	.193	4.50	4.90
A1	.092	.108	2.34	2.74
A2	.101	.117	2.56	2.96
b	.028	.035	0.70	0.90
b1	.050	.058	1.27	1.47
c	.018	.024	0.45	0.60
D	.617	.633	15.67	16.07
E	.392	.408	9.96	10.36
e	.100 BSC		2.54 BSC	
H	.255	.271	6.48	6.88
L	.499	.523	12.68	13.28
L1	.119	.135	3.03	3.43
ØP	.121	.129	3.08	3.28
Q	.126	.134	3.20	3.40

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, Unless Otherwise Specified)	Characteristic Values Min.	Typ.	Max	
I_S	V_{GS} = 0V			44	A
I_{SM}	Repetitive, Pulse Width Limited by T_{JM}			176	A
V_{SD}	I_F = I_S, V_{GS} = 0V, Note 1			1.4	V
t_{rr}	I_F = 22A, -di/dt = 100A/μs		87		ns
Q_{RM}	V_R = 100V		300		nC
I_{RM}			7		A

Note 1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,860,072 4,881,106 4,931,844 5,017,508 5,034,796 5,049,961 5,063,307 5,187,117 5,237,481 5,381,025 5,486,715 6,162,665 6,259,123B1 6,306,728B1 6,404,065B1 6,534,343 6,583,505 6,683,344 6,710,405B2 6,710,463 6,727,585 6,759,692 6,771,478B2 7,005,734B2 7,063,975B2 7,071,537 7,157,338B2

Fig. 1. Output Characteristics @ T_J = 25°C




Fig. 2. Extended Output Characteristics @ T_J = 25°C




Fig. 3. Output Characteristics @ T_J = 125°C




Fig. 4. $R_{DS(on)}$ Normalized to I_D = 22A Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_D = 22A Value vs. Drain Current





Fig. 6. Normalized Breakdown & Threshold Voltages vs. Junction Temperature



© 2019 IXYS CORPORATION, All Rights Reserved

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance





Fig. 12. Output Capacitance Stored Energy



IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

Fig. 13. Forward-Bias Safe Operating Area





Fig. 14. Maximum Transient Thermal Impedance



© 2019 IXYS CORPORATION, All Rights Reserved



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.