



XPT IGBT phaseleg ISOPLUS™ Surface Mount Power Device

$$\begin{aligned} I_{C25} &= 43 \text{ A} \\ V_{CES} &= 1200 \text{ V} \\ V_{CE(sat) \text{ typ}} &= 1.9 \text{ V} \end{aligned}$$



E72873

IGBTs S1, S2

Symbol	Conditions	Maximum Ratings	
V_{CES}	$T_{VJ} = 25^{\circ}\text{C to } 150^{\circ}\text{C}$	1200	V
V_{GES}		± 20	V
I_{C25}	$T_C = 25^{\circ}\text{C}$	43	A
I_{C80}	$T_C = 80^{\circ}\text{C}$	30	A
I_{CM}	$V_{GE} = 15 \text{ V}; R_G = 39 \Omega; T_{VJ} = 125^{\circ}\text{C}$ RBSOA, clamped inductive load; $L = 100 \mu\text{H}$	75	A
V_{CEK}		V_{CES}	
t_{SC} (SCSOA)	$V_{CE} = 900 \text{ V}; V_{GE} = \pm 15 \text{ V}; R_G = 39 \Omega; T_{VJ} = 125^{\circ}\text{C}$ none repetitive	10	μs
P_{tot}	$T_C = 25^{\circ}\text{C}$	150	W

Symbol Conditions Characteristic Values

(T_{VJ} = 25°C, unless otherwise specified)

		min.	typ.	max.	
$V_{CE(sat)}$	$I_C = 25 \text{ A}; V_{GE} = 15 \text{ V}; T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 125^{\circ}\text{C}$		1.9 2.2	2.2	V V
$V_{GE(th)}$	$I_C = 1 \text{ mA}; V_{GE} = V_{CE}$	5.4		6.5	V
I_{CES}	$V_{CE} = V_{CES}; V_{GE} = 0 \text{ V}; T_{VJ} = 25^{\circ}\text{C}$ $T_{VJ} = 125^{\circ}\text{C}$		200	2.1	mA μA
I_{GES}	$V_{CE} = 0 \text{ V}; V_{GE} = \pm 20 \text{ V}$			500	nA
$t_{d(on)}$	Inductive load; $T_{VJ} = 125^{\circ}\text{C}$ $V_{CE} = 600 \text{ V}; I_C = 25 \text{ A}$ $V_{GE} = \pm 15 \text{ V}; R_G = 39 \Omega$		70		ns
t_r			40		ns
$t_{d(off)}$			250		ns
t_f			100		ns
E_{on}			2.5		mJ
E_{off}			3.0		mJ
$E_{(rec)off}$			tbd		
C_{ies}	$V_{CE} = 25 \text{ V}; V_{GE} = 0 \text{ V}; f = 1 \text{ MHz}$		tbd		pF
Q_{Gon}	$V_{CE} = 600 \text{ V}; V_{GE} = 15 \text{ V}; I_C = 25 \text{ A}$		76		nC
R_{thJC}			0.85		K/W
R_{thJH}	with heatsink compound (IXYS test setup)		0.95	1.3	K/W

Features

• XPT IGBT

- low saturation voltage
- positive temperature coefficient for easy paralleling
- fast switching
- short tail current for optimized performance in resonant circuits

• Sonic™ diode

- fast reverse recovery
- low operating forward voltage
- low leakage current

• V_{CEsat} detection diode

- integrated into package
- very fast diode

• Package

- isolated back surface
- low coupling capacity between pins and heatsink
- PCB space saving
- enlarged creepage towards heatsink
- application friendly pinout
- low inductive current path
- high reliability

Applications

• Phaseleg

- buck-boost chopper

• Full bridge

- power supplies
- induction heating
- four quadrant DC drives
- controlled rectifier

• Three phase bridge

- AC drives
- controlled rectifier

Diodes D1, D2

Symbol	Conditions	Maximum Ratings				
I _{F25}	T _C = 25°C			40	A	
I _{F80}	T _C = 80°C			27	A	
Symbol	Conditions	Characteristic Values				
(T _{VJ} = 25°C, unless otherwise specified)						
			min.	typ.	max.	
V _F	I _F = 20 A	T _{VJ} = 25°C		1.9	2.4	V
		T _{VJ} = 125°C		1.9		V
I _{RM}	I _F = 20 A; R _G = 39 Ω; T _{VJ} = 125°C V _R = 600 V; V _{GE} = -15 V			30		A
t _{rr}				350		ns
E _{rec}				0.85		mJ
R _{thJC}	per diode				0.9	K/W
R _{thJH}	with heatsink compound (IXYS test setup)			1.2	1.5	K/W


Diodes D3, D4

Symbol	Conditions	Maximum Ratings				
V _R	T _C = 25°C to 150°C				1200	V
Symbol	Conditions	Characteristic Values				
(T _{VJ} = 25°C, unless otherwise specified)						
			min.	typ.	max.	
V _F	I _F = 1 A	T _{VJ} = 25°C		1.7	2.2	V
		T _{VJ} = 125°C		1.5		V
I _R	V _R = 1200 V	T _{VJ} = 25°C			2	μA
		T _{VJ} = 125°C		30		μA
I _{RM}	I _F = 1 A; di _F /dt = -100 A/μs; T _{VJ} = 25°C			2.3		A
t _{rr}				40		ns

Component

Symbol	Conditions	Maximum Ratings			
T_{VJ}			-55...+150		°C
T_{stg}			-55...+125		°C
V_{ISOL}	$I_{ISOL} \leq 1\text{ mA}; 50/60\text{ Hz}$		2500		V~
F_C	mounting force		40 ... 130		N
Symbol	Conditions	Characteristic Values			
		min.	typ.	max.	
C_P	coupling capacity between shorted pins and backside metal		90		pF
d_S, d_A	pin - pin	1.65			mm
d_S, d_A	pin - backside metal	4			mm
CTI		400			
Weight			8		g



Ordering	Ordering Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	IXA30PG1200DHGLB-TRR	IXA30PG1200DHGLB	Tape&Reel	200	511846

Equivalent Circuits for Simulation**Conduction**

IGBTs (typ. at $V_{GE} = 15\text{ V}; T_J = 125^\circ\text{C}$)
S1, S2 $V_0 = 1.1\text{ V}; R_0 = 60\text{ m}\Omega$

Diodes (typ. at $T_J = 125^\circ\text{C}$)
D1, D2 $V_0 = 1.3\text{ V}; R_0 = 28\text{ m}\Omega$

Dimensions in mm (1 mm = 0.0394")






Fig. 1 Typ. output characteristics




Fig. 2 Typ. output characteristics




Fig. 3 Typ. transfer characteristics




Fig. 4 Typ. turn-on gate charge




Fig. 5 Typ. switching energy vs. collector current




Fig. 6 Typ. switching energy vs. gate resistance

