


22 AWG, STRANDED CONDUCTOR,
SINGLE CONDUCTOR, UL1015 STYLE LEAD WIRES,
12.0" $\pm$ 1.0" LONG



RESISTANCE @ +25°C = 10,000 Ω $\pm$ 1%
RESISTANCE/TEMPERATURE CURVE = "J"
BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
MAXIMUM TEMPERATURE RATING = +105°C

MOISTURE RESISTANT PROBE ASSEMBLY

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	04/16/07	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com	
DRAWN BY	DAN DANKERT		
DATE	04/16/07		
REV.	NONE		
LAYER	0 OF 2	NTC THERMISTOR PROBE	
		P/N USP7765	