


RESISTANCE @ +25°C = 200 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = SEE GS201B1K R-T TABLE
BETA "β" (+25 TO +50°C) = 3,000°K NOMINAL
BETA "β" (+25 TO +85°C) = 3,047°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = -3.38%/°C NOMINAL
DISSIPATION CONSTANT = 0.7 mW/°C NOMINAL (AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (AIR)
MAXIMUM TEMPERATURE RATING = +300°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	03/18/14	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 03/18/14

REV. NONE

LAYER 0 OF 2

U.S. SENSOR CORP.

© COPYRIGHT

714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N GS201B1K