





RESISTANCE @ +25°C = 500,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "R"
 BETA " β " (0 TO +50°C) = 4,140°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.68%/°C NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = +220°C

*** ROHS COMPLIANT ***

PACKAGING: BULK

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	01/27/14	DD
"A"	CHANGED DIMENSIONS	01/27/14	DD

SCALE	NONE	U.S. SENSOR corp. www.ussensor.com 714-639-1000 © COPYRIGHT
DRAWN BY	DAN DANKERT	
DATE	10/04/01	NTC THERMISTOR
REV.	"A"	P/N SM504R1K
LAYER	0 OF 1	