


REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	10/20/03	DD

RESISTANCE @ +25°C = 1,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "F"
TEMPERATURE COEFFICIENT @ +25°C = −3.86%/°C NOMINAL
BETA "β" (0 TO +50°C) = 3,419°K NOMINAL
DISSIPATION CONSTANT = 1 mW/°C NOMINAL
THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)
THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +135°C

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 08/28/96

REV. NONE

LAYER 0 OF 1

© COPYRIGHT

U.S. SENSOR CORP.
714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N KC102F2K