


RESISTANCE @ +25°C = 2,252 Ω NOMINAL
ACCURACY (0 TO +70°C) = ± 0.10°C
RESISTANCE/TEMPERATURE CURVE = "J"
BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
MAXIMUM TEMPERATURE RATING = +105°C

MAXIMUM TEMPERATURE FOR BEST LONG TERM STABILITY = +75°C

*** ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	09/30/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE
DRAWN BY	DAN DANKERT
DATE	09/30/10
REV.	NONE
LAYER	0 OF 2

© COPYRIGHT

U.S. SENSOR CORP.
714-639-1000 www.ussensor.com

NTC THERMISTOR PROBE

P/N USP11493