




RESISTANCE @ $+25^{\circ}\text{C}$ = $4,700 \Omega \pm 10\%$
 RESISTANCE/TEMPERATURE CURVE = "F"
 BETA " β " (0 TO $+50^{\circ}\text{C}$) = 3,419°K NOMINAL
 TEMPERATURE COEFFICIENT @ $+25^{\circ}\text{C}$ = $-3.86\%/^{\circ}\text{C}$ NOMINAL
 DISSIPATION CONSTANT = 2 mW/ $^{\circ}\text{C}$ NOMINAL
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = $+220^{\circ}\text{C}$

*** ROHS COMPLIANT ***

PACKAGING: BULK

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	01/27/14	DD

SCALE	NONE	U.S. SENSOR CORP. www.ussensor.com 714-639-1000 © COPYRIGHT
DRAWN BY	DAN DANKERT	
DATE	01/27/14	NTC THERMISTOR
REV.	NONE	P/N SM472F1K
LAYER	0 OF 1	