




RESISTANCE @ +25°C = 10,000 Ω ± 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +125°C

MAXIMUM TEMPERATURE FOR BEST LONG-TERM STABILITY = +100°C

LEAD WIRE: 38 AWG (0.004" DIAMETER), TWO CONDUCTOR,
 SOLID CONDUCTOR, POLY-NYLON INSULATED

*** ROHS COMPLIANT ***

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	01/11/12	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT	
DRAWN BY	DAN DANKERT	U.S. SENSOR CORP.	
DATE	01/11/12	714-639-1000 www.ussensor.com	
REV	NONE	THERMISTOR PROBE	
LAYER	0 OF 2	P/N USP12837	