


REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	05/01/03	DD

RESISTANCE @ +25°C = 1,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "F"
TEMPERATURE COEFFICIENT @ +25°C = −3.86%/°C NOMINAL
BETA "β" (0 TO +50°C) = 3,419°K NOMINAL
DISSIPATION CONSTANT = 1 mW/°C NOMINAL
THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)
THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +150°C

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 05/01/03

REV. NONE

LAYER 0 OF 1

© COPYRIGHT

U.S. SENSOR CORP.

714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N TC102F2K