


RESISTANCE @ +25°C = 2,000 Ω ± 10%
RESISTANCE TEMPERATURE CURVE = "J"
BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −4.4%/°C NOMINAL
DISSIPATION CONSTANT = 3 mW/°C NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 8 SECONDS NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 2 SECONDS NOMINAL (STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +300°C

*** ROHS COMPLIANT ***

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	01/27/14	DD

SCALE	NONE
DRAWN BY	DAN DANKERT
DATE	01/27/14
REV.	NONE
LAYER	0 OF 2

© COPYRIGHT

U.S. SENSOR CORP.
714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N 202JH1K