




RESISTANCE @ +25°C = $1,000 \Omega \pm 10\%$
 RESISTANCE/TEMPERATURE CURVE = "F"
 BETA " β " (0 TO +50°C) = 3,419°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = $-3.86\%/^{\circ}\text{C}$ NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = +150°C

---	ISO RELEASE	10/11/05	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP.	
DRAWN BY	K. ALLEN		
DATE	11/29/93	714-639-1000 www.ussensor.com	
REV.	NONE	NTC CHIP THERMISTOR	
LAYER	0 OF 1	P/N BC102F1K	