



| REV | REVISION RECORD | DATE | APP |
|---|---|---|---|
| "A" | MAXIMUM DIAMETER WAS 0.125" | 10/01/97 | TW |
| --- | ISO RELEASE | 07/09/03 | DD |
| "B" | MAXIMUM DIAMETER WAS 0.140" | 11/03/11 | DD |

RESISTANCE @ +25°C = 1,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "F"
TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL
BETA "β" (0 TO +50°C) = 3,419°K NOMINAL
DISSIPATION CONSTANT = 3 mW/°C NOMINAL
THERMAL TIME CONSTANT = 15 SECONDS MAXIMUM (STILL AIR)
THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +150°C

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 05/23/96

REV. "B"

LAYER 0 OF 1

© COPYRIGHT

U.S. SENSOR CORP.
714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N DC102F2K