

# Standard Rectifier Module

$$V_{RRM} = 2 \times 1400 \text{ V}$$

$$I_{FAV} = 270 \text{ A}$$

$$V_F = 1,08 \text{ V}$$

Phase leg

Part number

**MDD255-14N1**



Backside: isolated

 E72873



## Features / Advantages:

- Package with DCB ceramic
- Improved temperature and power cycling
- Planar passivated chips
- Very low forward voltage drop
- Very low leakage current

## Applications:

- Diode for main rectification
- For single and three phase bridge configurations
- Supplies for DC power equipment
- Input rectifiers for PWM inverter
- Battery DC power supplies
- Field supply for DC motors

## Package: Y1

- Isolation Voltage: 4800 V~
- Industry standard outline
- RoHS compliant
- Height: 30 mm
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

## Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).



| Rectifier    |                                              |                                        |                                | Ratings |      |       |                   |
|--------------|----------------------------------------------|----------------------------------------|--------------------------------|---------|------|-------|-------------------|
| Symbol       | Definition                                   | Conditions                             |                                | min.    | typ. | max.  | Unit              |
| $V_{RSM}$    | max. non-repetitive reverse blocking voltage | $T_{VJ} = 25^{\circ}\text{C}$          |                                |         |      | 1500  | V                 |
| $V_{RRM}$    | max. repetitive reverse blocking voltage     | $T_{VJ} = 25^{\circ}\text{C}$          |                                |         |      | 1400  | V                 |
| $I_R$        | reverse current                              | $V_R = 1400\text{ V}$                  | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 500   | $\mu\text{A}$     |
|              |                                              | $V_R = 1400\text{ V}$                  | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 20    | mA                |
| $V_F$        | forward voltage drop                         | $I_F = 300\text{ A}$                   | $T_{VJ} = 25^{\circ}\text{C}$  |         |      | 1,19  | V                 |
|              |                                              | $I_F = 600\text{ A}$                   |                                |         |      | 1,40  | V                 |
|              |                                              | $I_F = 300\text{ A}$                   | $T_{VJ} = 125^{\circ}\text{C}$ |         |      | 1,08  | V                 |
|              |                                              | $I_F = 600\text{ A}$                   |                                |         |      | 1,35  | V                 |
| $I_{FAV}$    | average forward current                      | $T_C = 100^{\circ}\text{C}$            | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 270   | A                 |
| $I_{F(RMS)}$ | RMS forward current                          | 180° sine                              |                                |         |      | 450   | A                 |
| $V_{F0}$     | threshold voltage                            | } for power loss calculation only      | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 0,80  | V                 |
| $r_F$        | slope resistance                             |                                        |                                |         |      | 0,6   | m $\Omega$        |
| $R_{thJC}$   | thermal resistance junction to case          |                                        |                                |         |      | 0,14  | K/W               |
| $R_{thCH}$   | thermal resistance case to heatsink          |                                        |                                |         | 0,04 |       | K/W               |
| $P_{tot}$    | total power dissipation                      |                                        | $T_C = 25^{\circ}\text{C}$     |         |      | 890   | W                 |
| $I_{FSM}$    | max. forward surge current                   | t = 10 ms; (50 Hz), sine               | $T_{VJ} = 45^{\circ}\text{C}$  |         |      | 9,80  | kA                |
|              |                                              | t = 8,3 ms; (60 Hz), sine              | $V_R = 0\text{ V}$             |         |      | 10,6  | kA                |
|              |                                              | t = 10 ms; (50 Hz), sine               | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 8,33  | kA                |
|              |                                              | t = 8,3 ms; (60 Hz), sine              | $V_R = 0\text{ V}$             |         |      | 9,00  | kA                |
| $I^2t$       | value for fusing                             | t = 10 ms; (50 Hz), sine               | $T_{VJ} = 45^{\circ}\text{C}$  |         |      | 480,2 | kA <sup>2</sup> s |
|              |                                              | t = 8,3 ms; (60 Hz), sine              | $V_R = 0\text{ V}$             |         |      | 466,1 | kA <sup>2</sup> s |
|              |                                              | t = 10 ms; (50 Hz), sine               | $T_{VJ} = 150^{\circ}\text{C}$ |         |      | 346,9 | kA <sup>2</sup> s |
|              |                                              | t = 8,3 ms; (60 Hz), sine              | $V_R = 0\text{ V}$             |         |      | 336,6 | kA <sup>2</sup> s |
| $C_J$        | junction capacitance                         | $V_R = 400\text{ V}; f = 1\text{ MHz}$ | $T_{VJ} = 25^{\circ}\text{C}$  |         | 381  |       | pF                |

| Package Y1     |                                                              |                      | Ratings |      |      |      |
|----------------|--------------------------------------------------------------|----------------------|---------|------|------|------|
| Symbol         | Definition                                                   | Conditions           | min.    | typ. | max. | Unit |
| $I_{RMS}$      | RMS current                                                  | per terminal         |         |      | 600  | A    |
| $T_{VJ}$       | virtual junction temperature                                 |                      | -40     |      | 150  | °C   |
| $T_{op}$       | operation temperature                                        |                      | -40     |      | 125  | °C   |
| $T_{stg}$      | storage temperature                                          |                      | -40     |      | 125  | °C   |
| Weight         |                                                              |                      |         | 680  |      | g    |
| $M_D$          | mounting torque                                              |                      | 4,5     |      | 7    | Nm   |
| $M_T$          | terminal torque                                              |                      | 11      |      | 13   | Nm   |
| $d_{Spp/ App}$ | creepage distance on surface   striking distance through air | terminal to terminal | 16,0    |      |      | mm   |
| $d_{Spb/ Apb}$ |                                                              | terminal to backside | 16,0    |      |      | mm   |
| $V_{ISOL}$     | isolation voltage                                            | t = 1 second         | 4800    |      |      | V    |
|                |                                                              | t = 1 minute         | 4000    |      |      | V    |



Data Matrix: part no. (1-19), DC + PI (20-25), lot.no.# (26-31), blank (32), serial no.# (33-36)

| Ordering | Ordering Number | Marking on Product | Delivery Mode | Quantity | Code No. |
|----------|-----------------|--------------------|---------------|----------|----------|
| Standard | MDD255-14N1     | MDD255-14N1        | Box           | 3        | 464007   |

| Similar Part | Package | Voltage class |
|--------------|---------|---------------|
| MDD255-12N1  | Y1-CU   | 1200          |
| MDD255-16N1  | Y1-CU   | 1600          |
| MDD255-18N1  | Y1-CU   | 1800          |
| MDD255-20N1  | Y1-CU   | 2000          |

|             |       |      |
|-------------|-------|------|
| MDD255-22N1 | Y1-CU | 2200 |
|-------------|-------|------|

| Equivalent Circuits for Simulation                                                  |                    | * on die level | $T_{VJ} = 150^{\circ}\text{C}$ |
|-------------------------------------------------------------------------------------|--------------------|----------------|--------------------------------|
|  |                    | Rectifier      |                                |
| $V_{0 \max}$                                                                        | threshold voltage  | 0,8            | V                              |
| $R_{0 \max}$                                                                        | slope resistance * | 0,4            | mΩ                             |


Technical drawing of a mechanical part, showing front and top views with dimensions.

**Front View (Top):**

- Overall width: 115
- Overall height: 43
- Top flange width: 49
- Top flange thickness: 2
- Top flange hole diameter: 32 (+0/-1.9)
- Top flange hole spacing: 15 ± 1
- Top flange hole depth: 10
- Top flange hole diameter: 3x M8

**Top View (Bottom):**

- Overall width: 115
- Overall height: 50
- Left flange width: 18
- Left flange hole diameter: 18
- Left flange hole spacing: 20
- Left flange hole diameter: 22.5
- Left flange hole spacing: 35
- Left flange hole diameter: 28.5
- Left flange hole spacing: 45
- Left flange hole diameter: 67
- Left flange hole spacing: 38
- Left flange hole diameter: 6.2
- Left flange hole spacing: 80
- Left flange hole diameter: 92
- Left flange hole spacing: 115




**Rectifier**


Fig. 1 Surge overload current  
 $I_{FSM}$ : Crest value,  $t$ : duration




Fig. 2  $I^2t$  versus time (1-10 ms)




Fig. 3 Max. forward current  
 at case temperature




Fig. 4 Power dissipation vs. forward current & ambient temperature (per diode)




Fig. 5 Typ. peak reverse current  
 $I_{RM}$  versus  $-di_F/dt$




Fig. 6 Single phase rectifier bridge: Power dissipation vs. direct output current  
 & ambient temperature. R = resistive load, L = inductive load




Fig. 7 Typ. recovery time  $t_{rr}$   
 versus  $-di_F/dt$


**Rectifier**


Fig. 8 Three phase rectifier bridge: Power dissipation versus direct output current and ambient temperature




Fig. 9 Transient thermal impedance junction to case (per diode)

$R_{thJC}$  for various conduction angles  $d$ :

| $d$  | $R_{thJC}$ [K/W] |
|------|------------------|
| DC   | 0.139            |
| 180° | 0.148            |
| 120° | 0.156            |
| 60°  | 0.176            |
| 30°  | 0.214            |

Constants for  $Z_{thJC}$  calculation:

| $i$ | $R_{thi}$ [K/W] | $t_i$ [s] |
|-----|-----------------|-----------|
| 1   | 0.0066          | 0.00054   |
| 2   | 0.0358          | 0.09800   |
| 3   | 0.0831          | 0.54000   |
| 4   | 0.0129          | 12.0000   |




Fig. 10 Transient thermal impedance junction to heatsink (per diode)

$R_{thJK}$  for various conduction angles  $d$ :

| $d$  | $R_{thJK}$ [K/W] |
|------|------------------|
| DC   | 0.179            |
| 180° | 0.188            |
| 120° | 0.196            |
| 60°  | 0.216            |
| 30°  | 0.254            |

Constants for  $Z_{thJK}$  calculation:

| $i$ | $R_{thi}$ (K/W) | $t_i$ (s) |
|-----|-----------------|-----------|
| 1   | 0.0066          | 0.00054   |
| 2   | 0.0358          | 0.09800   |
| 3   | 0.0831          | 0.54000   |
| 4   | 0.0129          | 12.0000   |
| 5   | 0.0400          | 12.0000   |