





RESISTANCE @ +25°C = 15,000 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25C = -4.4%/°C NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL  
 MAXIMUM TEMPERATURE RATING = +220°C

| REV | REVISION RECORD                                                         | DATE     | APP |
|-----|-------------------------------------------------------------------------|----------|-----|
| --- | ISO RELEASE                                                             | 11/11/03 | DD  |
| "A" | TAB WAS 0.019"±0.004", LENGTH WAS 0.140"±0.010" & DIA WAS 0.065"±0.004" | 11/11/03 | DD  |

|                        |                                                                                                     |
|------------------------|-----------------------------------------------------------------------------------------------------|
| SCALE NONE             | U.S. SENSOR corp.<br>© COPYRIGHT<br>714-639-1000 www.ussensor.com<br>NTC THERMISTOR<br>P/N SM153J1K |
| DRAWN BY<br>R. DANKERT |                                                                                                     |
| DATE 11/28/94          |                                                                                                     |
| REV. "A"               |                                                                                                     |
| LAYER 0 OF 2           |                                                                                                     |